



QQGQ2.E137895

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

[See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component](#)

XPIQ INC

E137895

260 HOPPING BROOK RD

HOLLISTON, MA 01746 USA

	Rated Input			Max Output							
Model No.	Volts	Hz	SC	V	A	VA	OC	SP	EP	FC	GC
ACS40US03, ACS40US05, ACS40US09, ACS40US12, ACS40US15, ACS40US24, ACS40US30, ACS40US36, ACS40US48											
	100-240ac	47/63	0	-	-	-	-	1950	20B	-	-
ACS60US03, ACS60US05, ACS60US09, ACS60US12, ACS60US15, ACS60US24, ACS60US30, ACS60US36, ACS60US48											
	100-240ac	47/63	0	-	-	-	3	1950	20B	-	-
ASC40US(r)											
	100-240ac	47-63	0	-	-	-	3	1950	20B	0	0
ASC60US(r)											
	100-240ac	47-63	0	-	-	-	3	1950	20B	0	0
CDP1K2PS48#, CFP1K2PS48FE#											
	100-240ac	47-63	0	54.1	32	1731	3	60950-1	20B	0	1
CDP1K5PS48, CFP1K5PS48FE											
	100-250ac	47-63	0	58dc	38	1700	3	60950	50B	0	1
CDP3K-3U3R-N, CDP3K-3U3R-P											

				11.97	18.8	222.2	3				
				-12.2	4.2	41.8	3				
				5.04	2.7	10.5	3				
JPS350PQ46, JPS350PQ46C											
	100-250ac	47-63	0	3.26	38	117.7	3	60950-1	20B	0	0
				4.97	53.4	239.8	3				
				12.06	23.6	265.9	3				
				-11.92	5.2	53.3	3				
JPS350PQ47, JPS350PQ47C											
	100-250ac	47-63	0	4.99	52.3	243.1	3	60950-1	20B	0	0
				11.98	27.6	299.8	3				
				27.9	13.9	280.4	3				
				-12.25	4.05	42	3				
JPS350PQ48, JPS350PQ48C											
	100-250ac	47-63	0	5.01	52.6	247.3	3	60950-1	20B	0	0
				14.95	18	261	3				
				27.3	11.7	255.7	3				
				-15.13	4.1	44.6	3				
JPS350PS05, JPS350PS05C, JPS350PS12, JPS350PS12C, JPS350PS15, JPS350PS15C, JPS350PS24, JPS350PS24C, JPS350PS48, JPS350PS48C											
	100-250ac	47-63	0	5.29dc	74.64	347.84	3	60950	20B	0	0
				12.018dc	35.2	418.17	3				
				15.075dc	27.44	410	3				
				24.07dc	16.75	401.5	3				
				48.13dc	8.18	392.1	3				
JTA1024D01(q)											
	9-36 / 24dc	-	4	5dc	1	-	3	60950-1	6.3T	0	0
				-5dc	-1	-	3				

JTA1024D02(q)											
	9-36 / 24dc	-	4	12dc	0.42	-	3	60950- 1	6.3T	0	0
				-12dc	-0.42	-	3				
JTA1024D03(q)											
	9-36 / 24dc	-	4	15dc	0.333	-	3	60950- 1	6.3T	0	0
				-15dc	- 0.333	-	3				
JTA1024S05(q)											
	9-36 / 24dc	-	4	5dc	2	-	3	60950- 1	6.3T	0	0
JTA1024S12(q)											
	9-36 / 24dc	-	4	12dc	0.83	-	3	60950- 1	6.3T	0	0
JTA1024S15(q)											
	9-36 / 24dc	-	4	15dc	0.67	-	3	60950- 1	6.3T	0	0
JTA1024S3V3(q)											
	9-36 / 24dc	-	4	3.3dc	2	-	3	60950- 1	6.3T	0	0
JTA1048D01(q)											
	18-75 / 48dc	-	4	5dc	1	-	3	60950- 1	6.3T	0	0
				-5dc	-1	-	3				
JTA1048D02(q)											
	18-75 / 48dc	-	4	12dc	0.42	-	3	60950- 1	6.3T	0	0
				-12dc	-0.42	-	3				
JTA1048D03(q)											
	18-75 / 48dc	-	4	15dc	0.333	-	3	60950- 1	6.3T	0	0
				-15dc	- 0.333	-	3				

JTA1048S05(q)											
	18-75 / 48dc	-	4	5dc	2	-	3	60950- 1	6.3T	0	0
JTA1048S12(q)											
	18-75 / 48dc	-	4	12dc	0.83	-	3	60950- 1	6.3T	0	0
JTA1048S15(q)											
	18-75 / 48dc	-	4	15dc	0.67	-	3	60950- 1	6.3T	0	0
JTA1048S3V3(q)											
	18-75 / 48dc	-	4	3.3dc	2	-	3	60950- 1	6.3T	0	0
JTA1524D01(q)											
	9-36 / 24dc	-	4	5dc	1.5	-	3	60950- 1	6.3T	0	0
				-5dc	-1.5	-	3				
JTA1524D02(q)											
	9-36 / 24dc	-	4	12dc	0.625	-	3	60950- 1	6.3T	0	0
				-12dc	- 0.625	-	3				
JTA1524D03(q)											
	9-36 / 24dc	-	4	15dc	0.5	-	3	60950- 1	6.3T	0	0
				-15dc	-0.5	-	3				
JTA1524S05(q)											
	9-36 / 24dc	-	4	5dc	3	-	3	60950- 1	6.3T	0	0
JTA1524S12(q)											
	9-36 / 24dc	-	4	12dc	1.25	-	3	60950- 1	6.3T	0	0
JTA1524S15(q)											
	9-36 / 24dc	-	4	15dc	1	-	3	60950- 1	6.3T	0	0
JTA1524S3V3(q)											

	9-36 / 24dc	-	4	3.3dc	3	-	3	60950- 1	6.3T	0	0
JTA1548D01(q)											
	18-75 / 48dc	-	4	5dc	1.5	-	3	60950- 1	6.3T	0	0
				-5dc	-1.5	-	3				
JTA1548D02(q)											
	18-75 / 48dc	-	4	12dc	0.625	-	3	60950- 1	6.3T	0	0
				-12dc	- 0.625	-	3				
JTA1548D03(q)											
	18-75 / 48dc	-	4	15dc	0.5	-	3	60950- 1	6.3T	0	0
				-15dc	-0.5	-	3				
JTA1548S05(q)											
	18-75 / 48dc	-	4	5dc	3	-	3	60950- 1	6.3T	0	0
JTA1548S12(q)											
	18-75 / 48dc	-	4	12dc	1.25	-	3	60950- 1	6.3T	0	0
JTA1548S15(q)											
	18-75 / 48dc	-	4	15dc	1	-	3	60950- 1	6.3T	0	0
JTA1548S3V3(q)											
	JTA1548S3V3dc	-	4	3.3dc	3	-	3	60950- 1	6.3T	0	0
JTA2024D01(q)											
	9-36 / 24dc	-	4	5dc	2	-	3	60950- 1	6.3T	0	0
				-5dc	-2	-	3				
JTA2024D02(q)											
	9-36 / 24dc	-	4	12dc	0.83	-	3	60950- 1	6.3T	0	0
				-12dc	-0.83	-	3				

JTA2024D03(q)											
	9-36 / 24dc	-	4	15dc	0.67	-	3	60950- 1	6.3T	0	0
				-15dc	-0.67	-	3				
JTA2024S05(q)											
	9-36 / 24dc	-	4	5dc	4	-	3	60950- 1	6.3T	0	0
JTA2024S12(q)											
	9-36 / 24dc	-	4	12dc	1.67	-	3	60950- 1	6.3T	0	0
JTA2024S15(q)											
	9-36 / 24dc	-	4	15dc	1.33	-	3	60950- 1	6.3T	0	0
JTA2024S3V3(q)											
	9-36 / 24dc	-	4	3.3dc	4	-	3	60950- 1	6.3T	0	0
JTA2048D01(q)											
	18-75 / 48dc	-	4	5dc	2	-	3	60950- 1	6.3T	0	0
				-5dc	-2	-	3				
JTA2048D02(q)											
	18-75 / 48dc	-	4	12dc	0.83	-	3	60950- 1	6.3T	0	0
				-12dc	-0.83	-	3				
JTA2048D03(q)											
	18-75 / 48dc	-	4	15dc	0.67	-	3	60950- 1	6.3T	0	0
				-15dc	-0.67	-	3				
JTA2048S05(q)											
	18-75 / 48dc	-	4	5dc	4	-	3	60950- 1	6.3T	0	0
JTA2048S12(q)											
	18-75 / 48dc	-	4	12dc	1.67	-	3	60950- 1	6.3T	0	0

JTA2048S15(q)											
	18-75 / 48dc	-	4	15dc	1.33	-	3	60950- 1	6.3T	0	0
JTA2048S3V3(q)											
	18-75 / 48dc	-	4	3.3dc	4	-	3	60950- 1	6.3T	0	0
JWC00603S1V5, JWCC00603S1V8, JWC00603S2V0, JWC00603S2V5, JWC00605S1V5, JWC00605S1V8, JWC00605S2V0, JWC00605S2V5, JWC00605S3V3											
	5 or 3.3ac	-	0	3.47	7	25	3	1950	20B	0	1
JWC00603S1V5-L, JWC00603S1V8-L, JWC00603S2V0-L, JWC00603S2V5-L, JWC00603S1V5-L, JWC00603S1V8-L, JWC00603S2V0-L, JWC00603S2V5-L, JWC00603S3V3-L											
	5 or 3.3ac	-	0	3.47	7	25	3	1950	20B	0	1
JWC00603S1V8, JWC00605S1V5-L, JWC00605S1V8-L, JWC0060S2V0-L, JWC0060S2V5-L, JWC00603S3V3-L											
	5 or 3.3dc	-	0	3.47	7	25	3	1950	20B	0	1
KDQ Series@											
	48 to 60ac	-	0	3.47	35	122	3	1950	20B	0	1
KHE03048S05AL, KHE03048S05AH, KHE03048S2V5AL(s), KHE03048S2V5AH(s), KHE03048S3V3AL(s), KHE03048S3V3AH(s)											
	48 or 48 to 60dc	-	0	5.9	25	148	3	60950	5B	0	1
KHE03048S1V2AL(s), KHE03048S1V2AH(s), KHE03048S1V5AL(s), KHE03048S1V5AH(s), KHE03048S1V8AL(s), KHE03048S1V8AH(s)											
	48 or 48 to 60dc	-	0	1.9	32	61	3	60950	5B	0	1
KHH07048S1V2AH, KHH07048S1V2AH-IS											
	46-80dc	-	0	5.25	72	378	3	60950	10B	0	1
KHH07048S1V2AL, KHH07048S1V2AL-IS											
	46-80dc	-	0	5.25	72	378	3	60950	10B	0	1
KHH07048S1V2BH, KHH07048S1V2BH-IS											
	46-80dc	-	0	5.25	72	378	3	60950	10B	0	1
KHH07048S1V2BL, KHH07048S1V2BL-IS											
	46-80dc	-	0	5.25	72	378	3	60950	10B	0	1
KHH07048S1V5AH, KHH07048S1V5AH-IS											