

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply Series

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

Name and address of the factory

Note: When more than one factory, please report on page 2

XP POWER INC
990 BENCIA AVENUE
SUNNYVALE CA 94085
UNITED STATES Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

HPT5K0TSXXX-L Series, where X can be 0 to 9 which represents rated output voltage.

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 60950-1:2006 / A11:2009 / A1:2010 / A12:2011 / A2:2013; National Differences specified in the CB Test Report.

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60950-1:2005/AMD1:2009, IEC 60950-1:2005/AMD2:2013, IEC 60950-1:2005

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6090-CB-1 issued on 2020-02-06,
E139109-A6090-CB-1 issued on 2020-02-01

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2020-02-07

Signature:

Jolanta M. Wroblewska

For full legal entity names see www.ul.com/ncbnames



Ref. Certif. No.

US-35235-UL

Factories:

XP POWER (KUNSHAN) LTD
 230 BIN JIANG NAN RD
 ZHANGPU TOWN
 KUNSHAN
 JIANGSU 215321 CHINA

XP POWER (VIETNAM) CO LTD
 LOT D - 4 Q- CN
 MY PHUOC 3 INDUSTRIAL PARK
 BEN CAT DISTRICT
 BINH DUONG VIETNAM

XP POWER PLC
 HORESHOE PARK
 PANGBOURNE RG87 JW UNITED KINGDOM

Ratings:

Input:

3-Phase (3W+PE), 50/60 Hz
 200-240V, 10A MAX/PHASE, 3000W MAX
 380-480V, 10A MAX/PHASE, 5000W MAX

Output:

See Model Differences for Output Ratings per each Model.

Additional information (if necessary)



- UL (US), 333 Pfinqsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-02-07

Signature:

Jolanta M. Wroblewska