

Certificate



Certificate no.

CU 72161912 01

License Holder:

XP Power Limited
Haw Par Technocentre, Lobby B, #02-02
401 Commonwealth Drive
Singapore 149598
Singapore

Manufacturing Plant:

-AK-10056296 001

Test report no.: USA-AK 10056296 003

Client Reference:

Tested to: UL 60950-1:2007 R10.14

CAN/CSA-C22.2 NO.60950-1-07+A1:2011+A2:2014

Certified Product: DIN RAIL MOUNTABLE POWER SUPPLIES

License Fee - Units

Model Designation: DPC30USXXYZ
(XX=5, 12, 24; Y= -S, blank,
Z= 0-9, A-Z, a-z, "-", blank)

7

Rated Voltage : AC 100-240V, 47-63Hz
Rated Current : 750 mA
Output Ratings : see Appendix (Constr. Data Form)
Protection Class : I
Ambient temperature: 50°C max.

Special Remarks: To be installed according to the licensee's
installation instructions.

7

Licensed Test mark:



Date of Issue
(day/mo/yr)
15/08/2016



Appendix

(For TUV Rheinland of N.A., Inc. use only)

Certificate # CU72161912.01 File # 10056296 003

License Holder: XP Power Limited

Address: 401 Commonwealth Drive, Haw Par Technocentre, Lobby B, #02-02, 149598, Singapore

Type of Product: DIN RAIL MOUNTABLE POWER SUPPLIES

Model Number: DPC30USXYZ (XX = 05, 12 or 24; Y = -S or blank; Z = 0-9, A-Z, a-z, "-", blank)

Input and output ratings:

Input: 100-240 Vac, 47-63 Hz, 750 mA

Co XP Power Limited model	Output Voltage (Vdc)	Output Current (A)	Output Power (W)
DPC30US05-S	5	4	20
DPC30US05	5	4	20
DPC30US12-S	12	2	24
DPC30US12	12	2	24
DPC30US024-S	24	1.25	30
DPC30US24	24	1.25	30