External AC-DC Power Supplies Selector Guide

Wall Mount Adapters

5W to 10W

VFR05
- 5W
- 55.1 x 37.0 x 42.9mm
- Level VI & CoC Tier 2
- LPS approved
- Changeable input plugs

VFL05
- 5W
- 55.1 x 24.1 x 35.5mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost

ACM06
- 6W
- 73.5 x 30.7 x 42.5mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case

VEU10
- 2.1A USB A socket
- 50.8 x 37.0 x 22.0mm
- Level VI & CoC Tier 2
- Low cost
- Class II

12W

ACM12
- 12W
- 76.0 x 30.3 x 48.2mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case

VEL12
- 12W
- 76.0 x 29.5 x 39.4mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost

VER12
- 12W
- 76.5 x 41.0 x 37.6mm
- Level VI & CoC Tier 2
- LPS approved
- Changeable input plugs

18W

AMF18
- 18W
- 90.5 x 33.5 x 58.5mm
- Home healthcare approval
- 2 x MOPP
- IP22 rating

ACM18
- 18W
- 88.0 x 30.0 x 49.5mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case

VEL18
- 18W
- 90.0 x 34.0 x 47.5mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost

24W

AMF24
- 24W
- 90.5 x 33.5 x 58.5mm
- Home healthcare approval
- 2 x MOPP
- IP22 rating

ACM24
- 24W
- 88.0 x 30.0 x 57.0mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case

VEL24
- 24W
- 90.0 x 34.0 x 47.5mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost

VER24
- 24W
- 90.5 x 42.0 x 42.7mm
- Level VI & CoC Tier 2
- LPS approved
- Changeable input plugs

36W to 100W

AMF36
- 36W
- 90.5 x 33.5 x 58.5mm
- Home healthcare approval
- 2 x MOPP
- IP42 rating

ACM36
- 36W
- 96.7 x 33.0 x 59.5mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case

VEL36
- 36W
- 94.0 x 35.0 x 46.6mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost

VER36
- 36W
- 94.5 x 47.0 x 43.9mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost

AMF60
- 60W
- 90.5 x 58.5 x 33.5mm
- Home healthcare approval
- 2 x MOPP
- IP42 rating

PGW65
- 65W
- 90.5 x 58.5 x 33.5mm
- Power Delivery protocol
- Home healthcare approval
- IP42 rating

PGW100
- 100W
- 97.0 x 57.0 x 34.0mm
- Power Delivery protocol
- Home healthcare approval
- IP42 rating

Desktop

36W to 60W

AKM36
- 36W
- 108.0 x 50.0 x 33.8mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case

AEK40
- 40W
- 107.0 x 47.0 x 30.1mm
- Level VI & CoC Tier 2
- 5V to 48V outputs
- Class I

VEC40
- 40W
- 116.3 x 52.4 x 31.3mm
- Level VI & CoC Tier 2
- CCC qualified
- LPS approved

AKM45
- 45W
- 122.4 x 51.4 x 31.5mm
- Home healthcare approval
- 2 x MOPP
- Optional white case

VEC50
- 50W
- 116.3 x 52.4 x 31.3mm
- Level VI & CoC Tier 2
- CCC Qualified
- LPS approved

AEK60
- 60W
- 118.0 x 47.0 x 30.1mm
- Level VI & CoC Tier 2
- <0.15W standby power
- Class I

65W to 70W

AKM65
- 65W
- 125.0 x 62.3 x 34.0mm
- Home healthcare approval
- 2 x MOPP
- Optional white case

ALM65
- 65W
- 116.3 x 52.4 x 31.3mm
- Level VI
- 2 x MOPP
- Class I & II

VEC65
- 65W
- 116.3 x 52.4 x 31.3mm
- Level VI & CoC Tier 2
- CCC qualified
- LPS approved

AEJ70
- 70W
- 120.0 x 52.0 x 31.0mm
- Level VI & CoC Tier 2
- 65°C operation
- Class I

85W to 100W

ALM85
- 85W
- 116.3 x 52.4 x 31.3mm
- Level VI & CoC Tier 2
- 2 x MOPP
- IP32 rating

VES90
- 90W
- 139.0 x 58.0 x 31.0mm
- Level VI & CoC Tier 2
- CCC qualified
- Low cost

AKM90
- 90W
- 125.0 x 62.3 x 34.0mm
- CoC Tier 2, EU2019/1782
- 2 x MOPP
- Class I & II

AJM90
- 90W
- 140.0 x 71.0 x 22.0mm
- Level VI
- Slim profile
- Class II

AUM90
- 90W
- 144.0 x 62.0 x 32.0mm
- Level VI (level VII ready)
- 2 x MOPP
- Class I & II

PGD100
- 100W
- 114.5 x 56.5 x 32.0mm
- Power Delivery protocol
- Home healthcare approval
- IP42 rating

AEJ100
- 100W
- 141.0 x 58.0 x 39.5mm
- Level VI & CoC Tier 2
- 65°C operation
- Active PFC

120W to 160W

ALM120
- 120W
- 140.0 x 71.0 x 22.0mm
- Level VI & CoC Tier 2
- CCC qualified
- 2 x MOPP

VES120
- 120W
- 168.0 x 71.0 x 37.5mm
- Level VI & CoC Tier 2
- CCC qualified
- Low cost

PGD140
- 140W
- 121.0 x 65.8 x 32.0mm
- Power Delivery protocol
- Home healthcare approval
- IP42 rating

ALM150
- 150W
- 186.0 x 72.0 x 38.0mm
- Home healthcare approval
- IP32 rating
- Class I & II

AEJ160
- 160W
- 150.0 x 70.0 x 38.0mm
- Level VI & CoC Tier 2
- 65°C operation
- Active PFC

200W to 240W

AQM200
- 200W
- 166.5 x 54.2 x 33.0mm
- Home healthcare approval
- IP22 rating
- Class I & II

ALM200
- 200W
- 209.0 x 82.0 x 43.0mm
- Home healthcare approval
- IP32 rating
- Class I & II

APM240
- 240W
- 168.0 x 73.0 x 31.5mm
- Home healthcare approval
- Medical 2 x MOPP
- IP22 rating

250W

AQM250
- 250W
- 173.0 x 67.0 x 32.0mm
- Home healthcare approval
- IP22 rating
- Class I & II

AHM250
- 250W
- 223.0 x 88.5 x 38.6mm
- Level V
- IP22 rating
- Low profile

300W to 450W

AQM300
- 300W
- 183.0 x 85.0 x 35.0mm
- Home healthcare approval
- IP22 rating
- Class I & II

VES300
- 300W
- 197.4 x 88.9 x 39.0mm
- Level VI & CoC Tier 2
- CCC qualified
- Low cost

AQM450
- 450W
- 254 x 116 x 47mm
- Medical 2 x MOPP
- IP22 rating
- Class I

Recently introduced | Medical version available | Home healthcare approval

For full specifications visit: **www.xppower.com**

2026