



Ref. Certif. No.

DE 2-034041

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Medical Power Supply
Name and address of the applicant	XP Power LLC 15641 Red Hill Avenue, Suite 100 Tustin, CA92780, USA
Name and address of the manufacturer	XP Power LLC 15641 Red Hill Avenue, Suite 100 Tustin, CA92780, USA
Name and address of the factory	Di Feng Gong Ye Qu 2 Hao Xiasha Liuwu Village Shipai Town, Dong Guan City, 523350 Guang Dong Province, P.R. China
Ratings and principal characteristics	Input: AC 100-240V; 50-60Hz; 2.4-0.9A; Class II; for output ratings refer to report no CN21DVNZ 001 page 7
Trademark (if any)	XP
Customer's Testing Facility (CTF) Stage used	N/A
Model / Type Ref.	AQM200PSxxxxzyyyyyyyy (xx = 12, 15, 19, 24 or 48 to denot different output ratings; zz = C2 or C8, y = 0-9, a-z, A-Z blank or hyphen for marketing puropose)
Additional information (if necessary may also be reported on page 2)	Models differ in model designation, output rating, source of transformers (T2) and line filter (L2), ratings of components (C5, C28, C29), main board and SR board; for details see test report
A sample of the product was tested and found to be in conformity with	IEC 60601-1:2005+A1 IEC 60601-1-6:2010+A1 IEC 60601-1-11:2015 for national differences see test report
As shown in the Test Report Ref. No. which forms part of this Certificate	CN21DVNZ 001

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland LGA Products GmbH  
Tillystr. 2, 90431 Nürnberg, Germany  
Phone + 49 221 806-1371  
Fax + 49 221 806-3935  
Mail: cert-validity@de.tuv.com  
Web : www.tuv.com

Date: 2021-12-16

Signature:

Dipl.-Ing. W. Hsu