

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME**
**CB TEST CERTIFICATE**

Product

AC-DC Power Supply

Name and address of the applicant

XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780  
UNITED STATES

Name and address of the manufacturer

XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780  
UNITED STATES

Name and address of the factory

XP POWER INC  
990 BENECIA AVE SUNNYVALE CA 94085  
UNITED STATES

*Note: When more than one factory, please report on page 2*
☒ [Additional Information on page 2](#)

Ratings and principal characteristics

INPUT ~ 100-240VAC 50/60Hz 3.1A MAX  
Output: See test report for more details.

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

CHD250PSXX-YY  
See Page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modification.  
☒ [Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6033-CB-1 issued on 2019-04-04  
E139109-A6033-CB-1 issued on 2019-04-08

This CB Test Certificate is issued by the National Certification Body



- ☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☐ UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-04-09

Signature:

Original Issue Date: 2018-08-29

Jolanta M. Wroblewska



Ref. Certif. No.

US-32347-M2-UL

## Model Details:

CHD250PSXX-YY

Where XX is between 12-48, YY is SF or blank. May also be provided with additional suffixes "-S", "-C", "-L", and/or "A". All "-" are optional.

## Factories:

XP POWER (KUNSHAN) LTD  
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215321  
CHINA

XP POWER (VIETNAM) CO LTD  
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG  
VIETNAM

XP POWER PLC  
HORESHOE PARK PANGBOURNE RG87 JW  
UNITED KINGDOM

## Additional Information:

The original report was modified to include the following changes/additions:

- Test conditions for the heating test in the heating test table were corrected based on original datasheets.
- Standby output rating in Model Differences section was corrected.
- Input Test table was reformatted with new "Hz" column.

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

## Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/names](http://www.ul.com/names)

Date: 2019-04-09

Original Issue Date: 2018-08-29

Signature:

Jolanta M. Wroblewska