



Ref. Certif. No.

US-47049-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C
340 COMMERCE, SUITE 100 IRVINE, CA 92602
UNITED STATES

Name and address of the manufacturer

XP POWER L L C
340 COMMERCE, SUITE 100 IRVINE, CA 92602
UNITED STATES

Name and address of the factory

XP POWER LLC
455 E. TRIMBLE ROAD SAN JOSE, CA 95131
UNITED STATES

Note: When more than one factory, please report on page 2

☒ [Additional Information on page 2](#)

Ratings and principal characteristics

ECX40UYZ:
INPUT~ 100-240VAC 50/60Hz 1A

ECX60UYZZ:
INPUT~ 100-240VAC 50/60Hz 1.5A
☒ [Additional Information on page 2](#)

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

ECX40UYZZ, ECX60UYZZ,
Where X is C or M, Y is D or T, ZZ is 21, 22, 31-37. May be followed by 3X5.

Additional information (if necessary may also be reported on page 2)

Evaluated to National or Group Differences for
EU Group Differences, CA, CH, US
Evaluated to National Differences declared for:
EN IEC 62368-1:2024, EN IEC 62368-1:2024/A11:2024
☐ [Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2023

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6189-CB-1 issued on 2026-08-12

This CB Test Certificate is issued by the National Certification Body



☒ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
☐ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-08-12

Signature:

Kenny Liu



Ref. Certif. No.

US-47049-UL

Factory(ies):

XP POWER LIMITED
LIPO BLDG, #05-01, 621 ALJUNIED RD SINGAPORE 389834
SINGAPORE

XP POWER (VIETNAM) CO LTD
LOT D_4Q_CN, MY PHUOC 3 INDUSTRIAL PARK,
THOI HOA WARD HO CHI MINH CITY
VIETNAM

XP POWER PLC
16 HORESHOE PARK
PANGBOURNE READING BERKSHIRE
RG8 7JW
UNITED KINGDOM

XP POWER (MALAYSIA) SDN. BHD.
NO 1 PERSIARAN TEKNOLOGI 3
32610 SERI ISKANDAR, PERAK
MALAYSIA

Additional Ratings:

ECX40UYZ:

Total output max 40W.

Outputs (2 or 3 Provided) (Voltage ranges in parenthesis):

3.3 Vdc, 1.5A

3.3 Vdc, 6A

5 Vdc, 1.5A

5 Vdc, 6A

12 Vdc (10.1 to 13.5), 2A

-12 Vdc (-10.1 to -13.5), 0.5A

15 Vdc (13.6 to 17), 1.5A

-15 Vdc (-13.6 to -17), 0.5A

24 Vdc (21.1 to 26), 1A

ECX60UYZZ:

Total output max 60W.

Outputs (2 or 3 Provided) (Voltage ranges in parenthesis):

3.3 Vdc, 1.5A

3.3 Vdc, 8A

5 Vdc, 3A

5 Vdc, 8A

12 Vdc (10.1 to 13.5), 3A

-12 Vdc (-10.1 to -13.5), 0.5A

15 Vdc (13.6 to 17), 2.5A

-15 Vdc (-13.6 to -17), 0.5A

24 Vdc (21.1 to 26), 1.5A

Additional information (if necessary)



- ☒ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☐ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-08-12

Signature:

Kenny Liu