

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Switching power supply

Name and address of the applicant

XP POWER LLC
15641 RED HILL AVENUE
SUITE 100
TUSTIN, CA 92780, USA

Name and address of the manufacturer

XP POWER LLC
15641 RED HILL AVENUE
SUITE 100
TUSTIN, CA 92780, USA

Name and address of the factory

Note: When more than one factory, please report on page 2

ABES TECHNOLOGY CO LTD
No 78-1 Zhangma St. Xiushui Township Changhua County 504
TAIWAN

☒ Additional Information on page 2

Ratings and principal characteristics

Input Rated: 100-240 Vac, 50/60 Hz, 2.5 A
Output Rated: Refer to output ratings indicated in Model
Differences for additional details.

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

102323-XX, ECP150PSXX
See Page 2

Additional information (if necessary may also be
reported on page 2)

National Differences specified in the CB Test Report.

☒ Additional Information on page 2

A sample of the product was tested and found
to be in conformity with

IEC 60601-1(ed.3), IEC 60601-1(ed.3);am1

As shown in the Test Report Ref. No. which forms
part of this Certificate

E321744-D1003-1/A2/C0-CB issued on 2018-04-26

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-04-30

Original Issue Date: 2015-04-15

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-24995-M2-UL

Model Details:

ECP150PSXX (where XX can be any number between 12 and 48 designating the output voltage), may also be provided with suffix "SF".

102323-XX where XX can be 0-9 or blank

Factories:

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215321
CHINA

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIETNAM

Additional Information:

The original report was modified as Technical Amendment to include the following changes/additions:
To revise the altitude to 4000 m. See Test Report.

Additional information (if necessary)



☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

☐ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-04-30

Original Issue Date: 2015-04-15

Signature:

Jolanta M. Wroblewska