



Ref. Certif. No.

SG PSB-IV-09602M2

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IFCFF) CB SCHEMF

CB TEST CERTIFICATE

Product	Power supply (Switching Power Supply)
Name and address of the applicant	XP Power LLC. 340 Commerce, Suite 100 Irvine CA 92602 USA
Name and address of the manufacturer	XP Power LLC. 340 Commerce, Suite 100, Irvine CA 92602, USA
Name and address of the factory	No.66 Yuanying Rd., Liaobu Town, 523412 Dongguan City, PEOPLE'S REPUBLIC OF CHINA 8-1, Fu Kung Rd., Fu Hsing Park,, 506 Fu Hsing Hsiang, Chang Hua Hsien., TAIWAN
Ratings and principal characteristics Trademark / Brand (if any)	See page 2 for ratings. XP
Model/type Ref. Additional information (if necessary)	See page 2 for models. Certificate SG PSB-IV-09602M1 issued 2023-10-24 is replaced by this version due to technical changes. Complies to EN IEC 62368- 1:2020+A11:2020. See test report for National and Group Differences.
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2018
as shown in the Test Report Ref. No. which forms part of this certificate	7191331333-EEC24

Page 1 of 2

This CB Test Certificate is issued by the National Certification Body

CBS 057396 0954 Rev. 00

Date, 2024-05-08

(SEE WEE ANG)





Ref. Certif. No.

SG PSB-IV-09602M2

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IFCFF) CB SCHEMF

Trademark / Brand (Image)



Models (continued)

EHL20US03, EHL20US05, EHL20US09, EHL20US12, EHL20US15, EHL20US24, EHL20US48, EHL20US03-P, EHL20US05-P, EHL20US09-P, EHL20US12-P, EHL20US15-P, EHL20US24-P, EHL20US48-P

Additional Information (continued)

The power supplies were additionally tested to the requirements of IEC 60335-1:2010, A1:2013+ A2: 2016, only relevant clauses (with assumptions) that were applicable to these AC-DC power supply components have been considered.

Ratings

Input: 100-480V~, 0.45A, 50/60Hz
Output:
EHL20US03, EHL20US03-P: 3.3VDC, 4.55A
EHL20US05, EHL20US05-P: 5VDC, 4A
EHL20US09, EHL20US09-P: 9VDC, 2.22A
EHL20US12, EHL20US12-P: 12VDC, 1.67A
EHL20US15, EHL20US15-P: 15VDC, 1.33A
EHL20US24, EHL20US24-P: 24VDC, 0.83A
EHL20US48, EHL20US48-P: 48VDC, 0.42A

Page 2 of 2

This CB Test Certificate is issued by the National Certification Body

CBS 057396 0954 Rev. 00

Date, 2024-05-08

(SEE WEE ANG)

