

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product

Component Power Supply

Name and address of the applicant

XP Power LLC  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780 UNITED STATES

Name and address of the manufacturer

XP Power LLC  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780 UNITED STATES

Name and address of the factory

Note: When more than one factory, please report on page 2

XP POWER LLC  
990 BENEZIA AVE SUNNYVALE, CA 94085  
UNITED STATES Additional Information on page 2

Ratings and principal characteristics

Input: 100-240 Vac, 50/60 Hz, 6.5A  
Output: See Model Differences in Test Report for details

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

GSP500PS34-XG1042, GSP500PSXXY  
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 60601-1:2006/ A1:2013/ A12:2014;  
National Differences specified in the CB Test Report. Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005

As shown in the Test Report Ref. No. which forms part of this Certificate

E146893-D1030-1/A1/C0-ULCB issued on 2018-10-31

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2018-11-15

Original Issue Date: 2018-07-23

Signature:

Jolanta M. Wroblewska



Model Details:

GSP500PSXXY where XX = represents the output voltage between 12- 48, and Y = P or blank, maybe followed with addition suffix "-" followed by "EF" or/and "SF" and GSP500PS34-XG1042

Factories:

XP POWER (KUNSHAN) LTD  
230 BIN JIANG NAN ROAD, ZHANGPU TOWN KUNSHAN, JIANGSU, 215300  
CHINA

XP Power (Vietnam) Co., Ltd.  
Lot D 4Q-CN, My Phuoc 3 Industrial Park, Ben Cat District, Binh Duong Province  
VIETNAM

XP Power  
16 Horseshoe Park, PangbourneReading, Berkshire RG8 7JW  
UNITED KINGDOM

Additional Information:

The original report was modified as a Technical Amendment to include the following changes/additions:  
New model GSP500PS34-XG1042 is added to report.  
Two new manufacturing sites are added.  
Updated output ratings.  
Revised nomenclature in test table for power input test for GSP500PS34-XG1042.  
See Test Report for more details.

**Additional information (if necessary)**



- UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2018-11-15  
Original Issue Date: 2018-07-23

Signature:

Jolanta M. Wroblewska