


**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME****CB TEST CERTIFICATE**

Product	Switching Power Supply
Name and address of the applicant	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the factory	XP POWER (KUNSHAN) LTD 230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215300 CHINA <input checked="" type="checkbox"/> Additional Information on page 2
<i>Note: When more than one factory, please report on page 2</i>	
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	RCL175PXY See Page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include technical modifications. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E139109-A6061-CB-1 issued on 2019-06-06

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-06-07

Original Issue Date: 2018-11-29

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-32844-M1-UL

Model Details:

RCL175PXY, where X is S, D, T or Q, Y is 00 to 99 or AA-ZZ. Additional suffix is blank, U, C, or F.

Ratings:

Input: ~ 100 - 240Vac 50/60Hz 2.7A

Outputs Rated:

1 to 4 outputs provided; Max 175 W with Fan option and 120 W convection cooling.

See Miscellaneous enclosures for specific output ratings.

Factories:

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN
MY PHUOC 3 INDUSTRIAL PARK
BEN CAT DISTRICT
BINH DUONG BINH DUONG VIETNAM

XP POWER PLC
16 HORESHOE PARK
PANGBOURNE
RG8 7JW UNITED KINGDOM

XP POWER LIMITED
LIPO BLDG, #05-01
621 ALJUNIED RD
SINGAPORE 389834 SINGAPORE

XP POWER LLC
990 BENECIA AVE
SUNNYVALE CA 94085
UNITED STATES

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

Summary of Modifications:

Updated Technical Considerations, Tables, and Clauses.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-06-07

Original Issue Date: 2018-11-29

Signature:

Jolanta M. Wroblewska