



Product Service

CERTIFICATE

No. Z1A 065969 0246 Rev. 00

Factories: 049020

Model(s): **AFM60USzzC6, AFM60USzz**
(zz=09-27 indicates rated output voltage 9.0-27.0VDC with step of 1.0VDC)

Brand Name: **XP**



Parameters:

Rated Input: 100-240VAC, 50-60Hz, 1.5A

Rated Output: See below table for details

Protection Class: I

Degree of Protection: IP20

Model	Rated output voltage (VDC)	Rated output current (A)	Max. rated output power (W)
AFM60USzzC6, AFM60USzz	9.0-12.0	0.1-5.00	60.00
	13.0	0.1-4.62	60.06
	14.0	0.1-4.29	60.06
	15.0	0.1-4.00	60.00
	16.0	0.1-3.75	60.00
	17.0	0.1-3.53	60.01
	18.0	0.1-3.34	60.12
	19.0	0.1-3.16	60.04
	20.0	0.1-3.00	60.00
	21.0	0.1-2.86	60.06
	22.0	0.1-2.73	60.06
	23.0	0.1-2.61	60.03
	24.0-27.0	0.1-2.50	67.50