



Product Service

CERTIFICATE

No. Z1A 057396 1060 Rev. 00

Holder of Certificate: **XP Power LLC.**
340 Commerce, Suite 100
Irvine CA 92602
USA

Certification Mark:



Product: **Adaptors**
(SWITCHING POWER ADAPTOR)

Tested according to: EN IEC 62368-1:2020/A11:2020
AfPS GS 2019:01 PAK

With this certificate, in its capacity as a notified GS body, TÜV SÜD Product Service GmbH issues the GS Mark to the named certificate holder for the declared product with the named model designation in accordance with section 20 ProdSG (German Product Safety Act). The product meets the safety and health requirements of section 20 (3) ProdSG. The manufacturer is reminded of their obligations in accordance with section 24 ProdSG. The certification marks shown above can be affixed on the product. It is not permitted to alter the certification marks in any way. In addition, the certificate holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 652102534401

Valid until: 2027-02-15

Date, 2025-10-15

(Rickyet Wang)

ZERTIFIKAT ◆ CERTIFICATE ◆ 認證證書 ◆ CERTIFICADO ◆ CERTIFICAT

CERTIFICATE

No. Z1A 057396 1060 Rev. 00

Model(s):

APM240PSXXX-C6YYYYYYYY, APM240PSXXXYYYYYYYY, APM240PSXX-C6YYYYYYYY, APM240PSXXYYYYYYYY (XXX=110-150 or 171-260 or 351-400 or 471-540, which indicates rated output voltage range from 11.0VDC to 15.0VDC or 17.1VDC to 26.0VDC or 35.1VDC to 40.0VDC or 47.1VDC to 54.0VDC, and rises by step of 0.1VDC; XX=11-15 or 18-26 or 36-40 or 48-54, which indicates rated output voltage range from 11.0VDC to 15.0VDC or 18.0VDC to 26.0VDC or 36.0VDC to 40.0VDC or 48.0VDC to 54.0VDC, and rises by step of 1.0VDC; Y=0-9, a-z, blank or dash symbol '-', indicates different marketing purposes)

Brand Name:

XP Power



Parameters:

Rated Input: 100-240VAC, 50/60 or 50-60Hz, 3.5A

Rated Output: See below table for details

Protection Class: I

Degree of Protection: IP20



CERTIFICATE

No. Z1A 057396 1060 Rev. 00

Model	Rated output voltage (VDC)	Rated output current (A)	Max. rated output power (W)
APM240PSXXX-C6YYYYYYYYY, APM240PSXXXYYYYYYYYY, APM240PSXX-C6YYYYYYYYY, APM240PSXXYYYYYYYYY	11.0-12.0	18.00	216.0
	12.1-13.0	16.61	
	13.1-14.0	15.42	
	14.1-15.0	14.40	
	17.1-18.0	13.33	240.0
	18.1-19.0	12.63	
	19.1-20.0	12.00	
	20.1-21.0	11.42	
	21.1-22.0	10.90	240.0
	22.1-23.0	10.43	
	23.1-24.0	10.00	
	24.1-25.0	9.60	
	25.1-26.0	9.23	240.0
	35.1-36.0	6.66	
	36.1-37.0	6.48	
	37.1-38.0	6.31	
	38.1-39.0	6.15	240.0
	39.1-40.0	6.00	
	47.1-48.0	5.00	
	48.1-49.0	4.89	
49.1-50.0	4.80	240.0	
50.1-51.0	4.70		
51.1-52.0	4.61		
52.1-53.0	4.52		
53.1-54.0	4.44		