

Certificate



Certificate no.

TA 50526244 01

License Holder:

XP Power LLC
15641 Red Hill Avenue,
Suite 100 Tustin, CA92780
USA

Manufacturing Plant:

040-0002111731

Test report no.:

ZTW1- CN21DPCG 003

Client Reference: P00503289

Tested to:

IEC 60601-1:2005+A1
EN 60601-1:2006+A11+A1+A12
IEC 60601-1-11:2015+A1
EN 60601-1-11:2015
IEC 60601-1-6:2010+A1
EN 60601-1-6:2010+A1
IEC 62366:2007+A1
EN 62366:2008+A1

Certified Product: (Medical Power Supply)

License Fee - Units

Type Designation : AQM200PSxxzzzyyyyyyyy (XP)
xx stands for : 12, 15, 19, 24 or 48
zz stands for : C2 or C8
y stands for : 0-9, a-z, A-Z, blank or hyphen
Rated Voltage : AC 100-240V, 50-60Hz
Rated Current : 2.4-0.9A
Output : see Appendix
max. Ambient Temperature : 40°C
Protection Class : II

This certificate is valid for maximum 5 years.

Licensed Test mark:



TÜV Rheinland Taiwan Ltd

Signature

Dipl.-Ing. W. Hsu



Date of Issue
(day/mo/yr)

16/12/2021

Appendix to TÜV approved Certificate No.: TA 50526244

Certified Product : Medical Power Supply

Report Number : CN21DPCG 003

Type Designation : AQM200PSxxzzyyyyyyyy (XP)

(xx = 12, 15, 19, 24, 48; zz = C2 or C8; y = 0-9, a-z, A-Z, blank or hyphen)

Output Ratings:

XP Power	Output Voltage [VDC]	Output Current [A]	Max. Output Power [W]
AQM200PS12zzyyyyyyyy	+12	16	192.0
AQM200PS15zzyyyyyyyy	+15	13	195.0
AQM200PS19zzyyyyyyyy	+19	10.5	199.5
AQM200PS24zzyyyyyyyy	+24	8.3	199.2
AQM200PS48zzyyyyyyyy	+48	4.2	201.6

Date: 16 December, 2021

Certification Body

