

Certificate



Certificate no.

TA 50526235 01

License Holder:

XP Power LLC
15641 Red Hill Avenue,
Suite 100 Tustin, CA92780
USA

Manufacturing Plant:

040-0002111731

Test report no.: ZTW1- CN21ZYV5 002

Client Reference: P00503289

Tested to:

IEC 60601-1:2005+A1
EN 60601-1:2006+A11+A1+A12
IEC 60601-1-6:2010+A1
EN 60601-1-6:2010+A1
IEC 62366:2007+A1
EN 62366:2008+A1

Certified Product: (Medical Power Supply)

License Fee - Units

Type Designation : AQM200PSxxxxxxxxx (XP)
xx stands for : 12, 15, 19, 24 or 48
y stands for : 0-9, a-z, A-Z, blank or hyphen
Rated Voltage : AC 100-240V, 50-60Hz
Rated Current : 2.4-0.9A

| Output Voltage | Output Current | Max. Output Power | |
|----------------|----------------|-------------------|-----------|
| DC +12V | 16A | 192.0W | (xx = 12) |
| DC +15V | 13A | 195.0W | (xx = 15) |
| DC +19V | 10.5A | 199.5W | (xx = 19) |
| DC +24V | 8.3A | 199.2W | (xx = 24) |
| DC +48V | 4.2A | 201.6W | (xx = 48) |

max. Ambient Temperature : 40°C

Protection Class : I

This certificate is valid for maximum 5 years.

Licensed Test mark:



TÜV Rheinland Taiwan Ltd

Signature

Dipl.-Ing. W. Hsu



Date of Issue

(day/mo/yr)

16/12/2021