

Certificate



Certificate no.

TA 50518881 01

License Holder:

XP Power LLC
15641 Red Hill Avenue,
Suite 100 Tustin, CA92780
USA

Manufacturing Plant:

040-0002111731

Test report no.:

ZTW1- CN21X980 002

Client Reference: P00180022

Tested to:

IEC 60601-1:2005+A1
EN 60601-1:2006+A11+A1+A12
IEC 60601-1-6:2010+A1
EN 60601-1-6:2010+A1
IEC 62366:2007+A1
EN 62366:2008+A1

Certified Product: (Medical Power Supply)

License Fee - Units

Type Designation : AQM250PSxxxxxyyyyyy (XP)
xx stands for : 12, 19, 24 or 48
y stands for : 0-9, a-z, A-Z, blank or hyphen
Rated Voltage : AC 100-240V, 50-60Hz
Rated Current : 2.9 - 1.3A
Output : DC 12V/19A, 228.0W (xx = 12)
DC 19V/13.2A, 250.8W (xx = 19)
DC 24V/10.4A, 249.6W (xx = 24)
DC 48V/5.2A, 249.6W (xx = 48)
max. Ambient Temperature : 40°C
Protection Class : I

Remark: This certificate is valid for maximum 5 years.


Licensed Test mark:



TÜV Rheinland Taiwan Ltd

Signature

Dipl.-Ing. W. Hsu



Date of Issue

(day/mo/yr)

21/10/2021