



CERTIFICATE

No. B 065969 0277 Rev. 00

Holder of Certificate: XP Power Limited

401 Commonwealth Drive Haw Par Technocentre, Lobby B, #02-02 Singapore 149598 SINGAPORE

Certification Mark:



Product:

Power supplies (DIN RAIL MOUNTABLE POWER SUPPLIES)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.:

6121020060201

Valid until:

2024-05-12

Date, 2020-10-07

wen Im

(Owen Hsu)



CERTIFICATE

No. B 065969 0277 Rev. 00

Model(s):

DNR120AS12-I, DNR120AS12 #, DNR120AS12-ID, DNR120AS24-I, DNR120AS24 #, DNR120AS24-ID, DNR120AS48-I, DNR120AS48 #, DNR120AS48-ID

Brand Name:

XP



Parameters:

See below Rated inputs: Rated outputs: Protection class: Т Max. ambient temperature:

See below 50 °C

Remarks:

- 1. When installing, all requirements of below mentioned test standards must be fulfilled.
- 2. The equipment is evaluated for operating in altitude up to 5,000 m above the sea level.

The ratings & model description of the models are as below:

Model	Input ratings	Output Voltage (Vdc)	Output Wattage (W)
DNR120AS12-I, DNR120AS12 #, DNR120AS12-ID	115/230 Vac, 47-63 Hz, 2.8/1.4 A	12 Vdc	120 W
DNR120AS24-I, DNR120AS24 #, DNR120AS24-ID		24 Vdc	120 W
DNR120AS48-I, DNR120AS48 #, DNR120AS48-ID		48 Vdc	120 W

Tested according to:

EN 62368-1:2014

Production Facility(ies): 004727, 004978