



Product Service

CERTIFICATE

No. B 065969 0291 Rev. 00

Holder of Certificate: **XP Power Limited**

401 Commonwealth Drive
Haw Par Technocentre, Lobby B, #02-02
Singapore 149598
SINGAPORE

Certification Mark:



Product:

**Power supplies
(Din Rail Mountable Power Supplies)**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6121020060901

Valid until: 2024-06-02

Date, 2020-10-07

(Owen Hsu)

CERTIFICATE

No. B 065969 0291 Rev. 00

Model(s): DPC70US12-S, DPC70US12, DPC70US24-S
DPC70US24, DPC70US48-S, DPC70US48

Brand Name: XP



Parameters: Rated inputs: See below
Rated outputs: See below
Protection class: I
Max. ambient temperature: 50 °C

Remarks:

- 1) When installing, all requirements of below mentioned test standards must be fulfilled.
- 2) The equipment is evaluated for operating in altitude up to 5,000 m above the sea level.

The ratings & model description of the models are as below:

Model	Input rating	Output Voltage	Output Current	Output Power
DPC70US12-S, DPC70US12	100-240 Vac, 47-63 Hz, 1700 mA	12 Vdc	5.5 A	66 W
DPC70US24-S, DPC70US24		24 Vdc	3 A	72 W
DPC70US48-S, DPC70US48		48 Vdc	1.5 A	72 W

Tested according to: EN 62368-1:2014/A11:2017

Production Facility(ies): 004727, 004978