

# Certificate



Certificate no.

TA 50391516 01

**License Holder:**

XP Power Limited  
401 Commonwealth Drive,  
Haw Par Technocentre,  
Lobby B, #02-02, 149598  
Singapore

**Manufacturing Plant:**

030-0000346191

**Test report no.:** ZTW1-LinPr 10051751 001 **Client Reference:** AB-21092017-JPS130PS

**Tested to:** IEC 60601-1:2005+A1  
EN 60601-1:2006+A11+A1+A12

**Certified Product:** (Switching Power Supply) **License Fee - Units**

Type Designation	: JPS130PSX-M (XP)	5
X stands for	: 05, 12, 15, 24, 28 or 48	1
Rated Voltage	: AC 100-250V, 47-63Hz	
Rated Current	: 2-1A	
Output Voltage	: see Appendix	
Output Current	: see Appendix	
max. Ambient Temperature:	50°C	
Protection Class	: I	

This certificate is valid for maximum 5 years.

6

**Licensed Test mark:**



IEC 60601-1  
EN 60601-1

www.tuv.com  
ID 1419052191

**TÜV Rheinland Taiwan Ltd**  
Signature

Dipl.-Ing. W. Hsu



**Date of Issue**  
(day/mo/yr)  
24/10/2017

# Certificate



Certificate no.

TA 50391516 02

**License Holder:**

XP Power Limited  
401 Commonwealth Drive,  
Haw Par Technocentre,  
Lobby B, #02-02, 149598  
Singapore

**Manufacturing Plant:**

030-0000346191

**Test report no.:** ZTW1-LinPr 10051751 001 **Client Reference:** AB-21092017-JPS130PS

**Tested to:** IEC 60601-1:2005+A1  
EN 60601-1:2006+A11+A1+A12

**Certified Product:** (Switching Power Supply)

**License Fee - Units**

as page 01

Addition

Type Designation	: JPS130PTY-M (XP)	1
Y stands for	: 31, 32 or 34	1

This certificate is valid for maximum 5 years.

2

**Licensed Test mark:**



IEC 60601-1  
EN 60601-1

www.tuv.com  
ID 1419052191

**TÜV Rheinland Taiwan Ltd**

Signature

Dipl.-Ing. W. Hsu



**Date of Issue**  
(day/mo/yr)

24/10/2017

Appendix to TÜV approved Certificate No.: TA 50391516

Certified Product : Switching Power Supply  
 Report Number : 10051751 001  
 Type Designation : JPS130PSX-M, JPS130PTY-M (XP)  
 (X=05, 12, 15, 24, 28 or 48; Y=31, 32 or 34)

Output ratings

Model	Output Rating (Vdc)	Output Rating (Vdc)
JPS130PT31-M	5V/10A, +12V/3A, -12V/0.8A	5V/15A, +12V/4.1A, -12V/1.1A
JPS130PT32-M	5V/10A, +15V/2.5A, -15V/0.8A	5V/15A, +15V/4.1A, -15V/1.1A
JPS130PT34-M	5V/2.5A, +24V/2.8A, +12V/0.7A	5V/4A, +24V/4A, +12V/1.0A
JPS130PS05-M	5V/20A	5V/26A
JPS130PS12-M	12V/9A	12V/11A
JPS130PS15-M	15V/7A	15V/8.7A
JPS130PS24-M	24V/4.5A	24V/5.4A
JPS130PS28-M	28V/3.8A	28V/4.65A
JPS130PS48-M	48V/2.3A	48V/2.7A

Date: 24th October, 2017

Certification Body

Dipl.-Ing. W. Hsu

