



Product Service

CERTIFICATE

No. B 057396 0650 Rev. 00

Holder of Certificate: **XP Power LLC.**

15641 Red Hill Avenue, Suite 100
Tustin CA 92780
USA

Certification Mark:



Product:

**AC-DC and DC-DC converters
(AC-DC converter)**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 64210210090001A

Valid until: 2026-05-24

Date, 2021-06-04

(Richard Zhu)

CERTIFICATE

No. B 057396 0650 Rev. 00

Model(s):

LCW200PS12, LCW200PS12-E,
LCW200PS12-x, LCW200PS12-E-x,
LCW200PS12-xx, LCW200PS12-E-xx,
LCW200PS12-xxx, LCW200PS12-E-xxx,
LCW200PS15, LCW200PS15-E,
LCW200PS15-x, LCW200PS15-E-x,
LCW200PS15-xx, LCW200PS15-E-xx,
LCW200PS15-xxx, LCW200PS15-E-xxx,
LCW200PS24, LCW200PS24-E,
LCW200PS24-x, LCW200PS24-E-x,
LCW200PS24-xx, LCW200PS24-E-xx,
LCW200PS24-xxx, LCW200PS24-E-xxx,
LCW200PS48, LCW200PS48-E,
LCW200PS48-x, LCW200PS48-E-x,
LCW200PS48-xx, LCW200PS48-E-xx,
LCW200PS48-xxx, LCW200PS48-E-xxx

Brand Name:

XP Power



Parameters:

Rated Input: 100-277VAC, 3.0A, 50/60Hz

Rated Output: See below table for details

Protection Class: I

Degree of Protection: IPX0

Remark:

- The products are built-in type equipment, suitable enclosure should be provided by end system.

Tested according to: EN 62368-1:2014/A11:2017

CERTIFICATE

No. B 057396 0650 Rev. 00

| Model | Output voltage (V) | Output current (A) | Max. output power (W) |
|--|--------------------|--------------------|-----------------------|
| LCW200PS12 LCW200PS12-E LCW200PS12-x LCW200PS12-E-x LCW200PS12-xx LCW200PS12-E-xx LCW200PS12-xxx LCW200PS12-E-xxx | 12 | 16.7 | 200.4 |
| LCW200PS15 LCW200PS15-E LCW200PS15-x LCW200PS15-E-x LCW200PS15-xx LCW200PS15-E-xx LCW200PS15-xxx LCW200PS15-E-xxx | 15 | 13.4 | 201.0 |
| LCW200PS24 LCW200PS24-E LCW200PS24-x LCW200PS24-E-x LCW200PS24-xx LCW200PS24-E-xx LCW200PS24-xxx LCW200PS24-E-xxx | 24 | 8.4 | 201.6 |
| LCW200PS48 LCW200PS48-E LCW200PS48-x LCW200PS48-E-x LCW200PS48-xx LCW200PS48-E-xx LCW200PS48-xxx LCW200PS48-E-xxx | 48 | 4.2 | 201.6 |
| Remark: x=0-9, A-Z stands for different marketing purpose. | | | |