

Certificate



Certificate no.

USA / T 2273579 01

Applicant:

XPiQ, Inc.

260 Hopping Brook Road

Holliston, MA 01746

USA

Manufacturer:

USA - HJS/mmww C 2272574 . 01

Test report no.: USA -HJS/mmww C 2272574 . 02 Client Reference: Sean Ross

Tested to: EN 60601-1:1990+A1+A2
IEC 60601-1:1988+A1+A2

Test object: Switching Power Supply (open frame)

License Fee-Units

Model Design. Max Power Vnom. (V1) Imax (V1)

PBM65US05XY	51W	5.1V	10A
PBM65US12XY	65W	12V	5.5A
PBM65US15XY	65W	15V	4.4A
PBM65US18XY	65W	18V	3.7A
PBM65US24XY	65W	24V	2.8A
PBM65US28XY	65W	28V	2.4A

7

(X=A-Z or blank; Y=0-9 or blank)

Rated Voltage: AC 100-240V, 47-63Hz

Rated Current: 1.6A

Protection Class: I

7

Licensed Test mark:



IEC 60601-1

Signatures

Stephan Schmitt *Dipl.-Ing. Raap*

Stephan Schmitt
President

Dipl.-Ing. Raap
QA Certification Officer

Date of Issue

(day/mo/yr)

02/12/2002