

Certificate



Certificate no.

TA 50411202 01

License Holder:

XP Power Limited
401 Commonwealth Drive,
Haw Par Technocentre,
Lobby B, #02-02, 149598
Singapore

Manufacturing Plant:

030-0000330828

Test report no.: ZTW1- 50047933 002

Client Reference: WZ-16052018-XP

Tested to: IEC 60601-1:2005+A1
EN 60601-1:2006+A11+A1+A12

Certified Product: (Switching Power Supply)		License Fee - Units
Type Designation	: PBR650PSxyf (XP)	5
x stands for	: 12, 15, 18, 24, 28, 30, 32, 34, 36, 48, 57 or 58	1
y stands for	: B or C	1
f stands for	: Blank or '-SP'	1
Rated Voltage	: AC 100-240V, 47-63Hz	
Rated Current	: 8.4-4.2A	
Output Voltage	: see Appendix	
Output Current	: see Appendix	
max. Ambient Temperature:	50°C at o/p loaded to full rated 70°C at o/p loaded to half rated	
Protection Class	: I	

This certificate is valid for maximum 5 years.

8

Licensed Test mark:



TÜV Rheinland Taiwan Ltd
Signature

Dipl.-Ing. W. Hsu



Date of Issue
(day/mo/yr)
04/07/2018

Appendix to TÜV approved Certificate No.: TA 50411202

Certified Product : Switching Power Supply
Report Number : 50047933 002
Type Designation : PBR650PSxyf (XP)
 (x = 12, 15, 18, 24, 28, 30, 32, 34, 36, 48, 57 or 58; y = B or C;
 f = blank or “-SP”)

Output ratings:

Model	Output Voltage	Output Current (Max.)	Output Power (Max.)
PBR650PS12yf	12Vdc	50A	600W
PBR650PS15yf	15Vdc	40A	600W
PBR650PS18yf	18Vdc	36.12A	650W
PBR650PS24yf	24Vdc	27.09A	650W
PBR650PS28yf	28Vdc	23.22A	650W
PBR650PS30yf	30Vdc	21.67A	650W
PBR650PS32yf	32Vdc	20.32A	650W
PBR650PS34yf	34Vdc	19.12A	650W
PBR650PS36yf	36Vdc	18.06A	650W
PBR650PS48yf	48Vdc	13.55A	650W
PBR650PS57yf	57Vdc	11.41A	650W
PBR650PS58yf	58Vdc	11.21A	650W

Date: 4th July, 2018

Certification Body


 Dipl.-Ing. W. Hsu

