



Product Service

CERTIFICATE

No. B 057396 0582 Rev. 00

Holder of Certificate: **XP Power LLC.**
15641 Red Hill Avenue, Suite 100
Tustin CA 92780
USA

Certification Mark:



Product: **Adaptors**
(Open Frame Power Supply)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

Test report no.: 6121019063801

Valid until: 2024-05-26

Date, 2020-01-02

Watson Yang
(Watson Yang)



Product Service

CERTIFICATE

No. B 057396 0582 Rev. 00

Model(s): UCH600PSxx
("xx" can be 12, 24, 36 or 48
to denote different output voltage)

Brand Name: XP Power



Parameters:

Rated input voltage:	100-240 Vac
Rated input current:	7-2.7 A
Rated frequency:	50-60 Hz
Rated outputs:	See below
Protection class:	I
Max. ambient temperature:	50 °C
Degree of protection against ingress of liquids:	IPX0

Remark:
The equipment is evaluated for operating in
altitude up to 5,000 m above the sea level.

The output rating of the models are as below:

Models-#	Rated Outputs
UCH600PS12	12 Vdc, 50 A
	12 Vdc, 0.6 A (for Fan)
	5 Vdc, 1.0 A
UCH600PS24	24 Vdc, 25 A
	12 Vdc, 0.6 A (for Fan)
	5 Vdc, 1.0 A
UCH600PS36	36 Vdc, 16.6 A
	12 Vdc, 0.6 A (for Fan)
	5 Vdc, 1.0 A
UCH600PS48	48 Vdc, 12.5 A
	12 Vdc, 0.6 A (for Fan)
	5 Vdc, 1.0 A

Tested according to: EN 62368-1:2014

**Production
Facility(ies):** 082809

Wat J