



Product Service

# CERTIFICATE

No. Z1A 15 08 65969 151

**Holder of Certificate:** **XP Power Limited**  
401 Commonwealth Drive,  
Haw Par Technocentre, Lobby B, #02-02 149598  
SINGAPORE

**Factory(ies):** 73018

**Certification Mark:**



**Product:** **Adaptors  
(AC ADAPTER)**

**Model(s):** **VEL12USxxx-zz-JA-H, VEL12USxxx-zz-JA, VER12USxxx-JA  
(xxx, zz are variables, see page 2-6 for details.)**

**Parameters:**

Rated Input :	100-240VAC or 200-240VAC, 50/60Hz, 0.3A
Rated Output :	See page 2-6 for details
Protection Class :	II
Degree of Protection :	IP20

**Tested according to:** EN 60950-1:2006/A2:2013  
EN 60065:2002/A12:2011  
BS EN 60950-1:2006/A2:2013  
BS EN 60065:2002/A12:2011  
AfPS GS 2014:01 PAK

The product meets the safety and health requirements of the German Product Safety Act section 20 to 22 ProdSG. The certification marks shown above can be affixed on the product. It is not permitted to alter the certification marks in any way. In addition the certificate holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. See also notes overleaf.

**Test report no.:** 64210140461904A

**Valid until:** 2016-08-09

**Date,** 2015-08-12

  
(Richard Zhu)



Page 1 of 6

**CERTIFICATE**  
**No. Z1A 15 08 65969 151**



Product Service

Model Number	Rated output Voltage (Vd.c.)	Rated output Current (mA)
VEL12US050-zz-JA-H, VEL12US050-zz-JA, VER12US050-JA	5.0	2100
VEL12US051-zz-JA-H, VEL12US051-zz-JA, VER12US051-JA	5.1	2060
VEL12US052-zz-JA-H, VEL12US052-zz-JA, VER12US052-JA	5.2	2100
VEL12US053-zz-JA-H, VEL12US053-zz-JA, VER12US053-JA	5.3	2060
VEL12US054-zz-JA-H, VEL12US054-zz-JA, VER12US054-JA	5.4	2020
VEL12US055-zz-JA-H, VEL12US055-zz-JA, VER12US055-JA	5.5	1980
VEL12US056-zz-JA-H, VEL12US056-zz-JA, VER12US056-JA	5.6	1950
VEL12US057-zz-JA-H, VEL12US057-zz-JA, VER12US057-JA	5.7	1910
VEL12US058-zz-JA-H, VEL12US058-zz-JA, VER12US058-JA	5.8	1880
VEL12US059-zz-JA-H, VEL12US059-zz-JA, VER12US059-JA	5.9	1850
VEL12US060-zz-JA-H, VEL12US060-zz-JA, VER12US060-JA	6.0	1880
VEL12US061-zz-JA-H, VEL12US061-zz-JA, VER12US061-JA	6.1	1850
VEL12US062-zz-JA-H, VEL12US062-zz-JA, VER12US062-JA	6.2	1820
VEL12US063-zz-JA-H, VEL12US063-zz-JA, VER12US063-JA	6.3	1790
VEL12US064-zz-JA-H, VEL12US064-zz-JA, VER12US064-JA	6.4	1770
VEL12US065-zz-JA-H, VEL12US065-zz-JA, VER12US065-JA	6.5	1740
VEL12US066-zz-JA-H, VEL12US066-zz-JA, VER12US066-JA	6.6	1710
VEL12US067-zz-JA-H, VEL12US067-zz-JA, VER12US067-JA	6.7	1690

**CERTIFICATE**  
**No. Z1A 15 08 65969 151**



Product Service

VEL12US068-zz-JA-H, VEL12US068-zz-JA, VER12US068-JA	6.8	1660
VEL12US069-zz-JA-H, VEL12US069-zz-JA, VER12US069-JA	6.9	1640
VEL12US070-zz-JA-H, VEL12US070-zz-JA, VER12US070-JA	7.0	1610
VEL12US071-zz-JA-H, VEL12US071-zz-JA, VER12US071-JA	7.1	1590
VEL12US072-zz-JA-H, VEL12US072-zz-JA, VER12US072-JA	7.2	1570
VEL12US073-zz-JA-H, VEL12US073-zz-JA, VER12US073-JA	7.3	1550
VEL12US074-zz-JA-H, VEL12US074-zz-JA, VER12US074-JA	7.4	1530
VEL12US075-zz-JA-H, VEL12US075-zz-JA, VER12US075-JA	7.5	1510
VEL12US090-zz-JA-H, VEL12US090-zz-JA, VER12US090-JA	9.0	1280
VEL12US091-zz-JA-H, VEL12US091-zz-JA, VER12US091-JA	9.1	1260
VEL12US092-zz-JA-H, VEL12US092-zz-JA, VER12US092-JA	9.2	1250
VEL12US093-zz-JA-H, VEL12US093-zz-JA, VER12US093-JA	9.3	1240
VEL12US094-zz-JA-H, VEL12US094-zz-JA, VER12US094-JA	9.4	1220
VEL12US095-zz-JA-H, VEL12US095-zz-JA, VER12US095-JA	9.5	1210
VEL12US096-zz-JA-H, VEL12US096-zz-JA, VER12US096-JA	9.6	1200
VEL12US097-zz-JA-H, VEL12US097-zz-JA, VER12US097-JA	9.7	1190
VEL12US098-zz-JA-H, VEL12US098-zz-JA, VER12US098-JA	9.8	1170
VEL12US099-zz-JA-H, VEL12US099-zz-JA, VER12US099-JA	9.9	1160

**CERTIFICATE**  
**No. Z1A 15 08 65969 151**



Product Service

VEL12US100-zz-JA-H, VEL12US100-zz-JA, VER12US100-JA	10.0	1150
VEL12US101-zz-JA-H, VEL12US101-zz-JA, VER12US101-JA	10.1	1140
VEL12US102-zz-JA-H, VEL12US102-zz-JA, VER12US102-JA	10.2	1130
VEL12US103-zz-JA-H, VEL12US103-zz-JA, VER12US103-JA	10.3	1120
VEL12US104-zz-JA-H, VEL12US104-zz-JA, VER12US104-JA	10.4	1110
VEL12US105-zz-JA-H, VEL12US105-zz-JA, VER12US105-JA	10.5	1100
VEL12US106-zz-JA-H, VEL12US106-zz-JA, VER12US106-JA	10.6	1080
VEL12US107-zz-JA-H, VEL12US107-zz-JA, VER12US107-JA	10.7	1070
VEL12US108-zz-JA-H, VEL12US108-zz-JA, VER12US108-JA	10.8	1060
VEL12US109-zz-JA-H, VEL12US109-zz-JA, VER12US109-JA	10.9	1060
VEL12US110-zz-JA-H, VEL12US110-zz-JA, VER12US110-JA	11.0	1050
VEL12US111-zz-JA-H, VEL12US111-zz-JA, VER12US111-JA	11.1	1040
VEL12US112-zz-JA-H, VEL12US112-zz-JA, VER12US112-JA	11.2	1030
VEL12US113-zz-JA-H, VEL12US113-zz-JA, VER12US113-JA	11.3	1020
VEL12US114-zz-JA-H, VEL12US114-zz-JA, VER12US114-JA	11.4	1010
VEL12US115-zz-JA-H, VEL12US115-zz-JA, VER12US115-JA	11.5	1000
VEL12US116-zz-JA-H, VEL12US116-zz-JA, VER12US116-JA	11.6	990
VEL12US117-zz-JA-H, VEL12US117-zz-JA, VER12US117-JA	11.7	980

**CERTIFICATE**  
**No. Z1A 15 08 65969 151**



Product Service

VEL12US118-zz-JA-H, VEL12US118-zz-JA, VER12US118-JA	11.8	970
VEL12US119-zz-JA-H, VEL12US119-zz-JA, VER12US119-JA	11.9	970
VEL12US120-zz-JA-H, VEL12US120-zz-JA, VER12US120-JA	12.0	1000
VEL12US121-zz-JA-H, VEL12US121-zz-JA, VER12US121-JA	12.1	990
VEL12US122-zz-JA-H, VEL12US122-zz-JA, VER12US122-JA	12.2	980
VEL12US123-zz-JA-H, VEL12US123-zz-JA, VER12US123-JA	12.3	980
VEL12US124-zz-JA-H, VEL12US124-zz-JA, VER12US124-JA	12.4	970
VEL12US125-zz-JA-H, VEL12US125-zz-JA, VER12US125-JA	12.5	960
VEL12US126-zz-JA-H, VEL12US126-zz-JA, VER12US126-JA	12.6	950
VEL12US127-zz-JA-H, VEL12US127-zz-JA, VER12US127-JA	12.7	940
VEL12US128-zz-JA-H, VEL12US128-zz-JA, VER12US128-JA	12.8	940
VEL12US129-zz-JA-H, VEL12US129-zz-JA, VER12US129-JA	12.9	930
VEL12US130-zz-JA-H, VEL12US130-zz-JA, VER12US130-JA	13.0	920
VEL12US131-zz-JA-H, VEL12US131-zz-JA, VER12US131-JA	13.1	920
VEL12US132-zz-JA-H, VEL12US132-zz-JA, VER12US132-JA	13.2	910
VEL12US133-zz-JA-H, VEL12US133-zz-JA, VER12US133-JA	13.3	900
VEL12US134-zz-JA-H, VEL12US134-zz-JA, VER12US134-JA	13.4	900
VEL12US135-zz-JA-H, VEL12US135-zz-JA, VER12US135-JA	13.5	890

**CERTIFICATE**  
**No. Z1A 15 08 65969 151**



Product Service

VEL12US136-zz-JA-H, VEL12US136-zz-JA, VER12US136-JA	13.6	880
VEL12US137-zz-JA-H, VEL12US137-zz-JA, VER12US137-JA	13.7	870
VEL12US138-zz-JA-H, VEL12US138-zz-JA, VER12US138-JA	13.8	870
VEL12US139-zz-JA-H, VEL12US139-zz-JA, VER12US139-JA	13.9	860
VEL12US140-zz-JA-H, VEL12US140-zz-JA, VER12US140-JA	14.0	860
VEL12US141-zz-JA-H, VEL12US141-zz-JA, VER12US141-JA	14.1	850
VEL12US142-zz-JA-H, VEL12US142-zz-JA, VER12US142-JA	14.2	850
VEL12US143-zz-JA-H, VEL12US143-zz-JA, VER12US143-JA	14.3	840
VEL12US144-zz-JA-H, VEL12US144-zz-JA, VER12US144-JA	14.4	830
VEL12US145-zz-JA-H, VEL12US145-zz-JA, VER12US145-JA	14.5	830
VEL12US146-zz-JA-H, VEL12US146-zz-JA, VER12US146-JA	14.6	820
VEL12US147-zz-JA-H, VEL12US147-zz-JA, VER12US147-JA	14.7	820
VEL12US148-zz-JA-H, VEL12US148-zz-JA, VER12US148-JA	14.8	810
VEL12US149-zz-JA-H, VEL12US149-zz-JA, VER12US149-JA	14.9	810
VEL12US150-zz-JA-H, VEL12US150-zz-JA, VER12US150-JA	15.0	800

Notes:

1. xxx = 050-075, 090-150 denotes rated output voltage from 5.0-7.5VDC or 9.0-15.0VDC with step 0.1V;
2. zz = EU, UK denotes different plug type:
  - a. zz= EU, for Europe plug,
  - b. zz= UK, for United Kingdom plug.