



## QQHM2.E321744 Power Supplies, Medical and Dental - Component

[Page Bottom](#)

### Power Supplies, Medical and Dental - Component

[See General Information for Power Supplies, Medical and Dental - Component](#)**XP POWER LTD**

E321744

401 COMMONWEALTH DR  
HAW PAR TECHNOCENTRE  
LOBBY B, #02-02  
SINGAPORE, 149598 SINGAPORE

Model No.	Rated Input		SC	Output			OC	SP	EP	FC	GC
	V	Hz		Max V	Max A	Max VA					
AMM150PSxyyyzzzz	100-240	47-63	0	12(d)	11(d)	132(d)	9	60601-1	20B	0	1
AMM150PSxyyyzzzz	100-240	47-63	0	15(d)	9(d)	135(d)	9	60601-1	20B	0	1
AMM150PSxyyyzzzz	100-240	47-63	0	19(d)	7.9(d)	150(d)	9	60601-1	20B	0	1
AMM150PSxyyyzzzz	100-240	47-63	0	24(d)	6.25(d)	150(d)	9	60601-1	20B	0	1
AMM150PSxyyyzzzz	100-240	47-63	0	27(d)	5.56(d)	150(d)	9	60601-1	20B	0	1
AMM150PSxyyyzzzz	100-240	47-63	0	48(d)	3.13(d)	150(d)	9	60601-1	20B	0	1
AEM60US05	120-240 Vac	47-63	0	5.26	9.3	39.5	9	60601-1	20B	6	2
AEM60US12	120-240 Vac	47-63	0	12.17	7.35	86.5	9	60601-1	20B	6	2
AEM60US15@	120-240 Vac	47-63	0	15	4	60	9	60601-1	20B	6	2
AEM60US18@	120-240 Vac	47-63	0	18	3.33	60	9	60601-1	20B	6	2
AEM60US19	120-240 Vac	47-63	0	19.1	5.37	99.45	9	60601-1	20B	6	2
AEM60US24@	120-240 Vac	47-63	0	24	2.5	60	9	60601-1	20B	6	2
AEM60US36@	120-240 Vac	47-63	0	36	1.66	60	9	60601-1	20B	6	2
AEM60US48	120-240 Vac	47-63	0	47.73	1.87	88.83	9	60601-1	20B	6	2
AMM150PSxCyyyzzzz	100-240	47-63	0	12(d)	11(d)	132(d)	9	60601-1	20B	0	0
AMM150PSxCyyyzzzz	100-240	47-63	0	15(d)	9(d)	135(d)	9	60601-1	20B	0	0
AMM150PSxCyyyzzzz	100-240	47-63	0	19(d)	7.9(d)	150(d)	9	60601-1	20B	0	0
AMM150PSxCyyyzzzz	100-240	47-63	0	24(d)	6.25(d)	150(d)	9	60601-1	20B	0	0
AMM150PSxCyyyzzzz	100-240	47-63	0	27(d)	5.56(d)	150(d)	9	60601-1	20B	0	0
AMM150PSxCyyyzzzz	100-240	47-63	0	48(d)	3.13(d)	150(d)	9	60601-1	20B	0	0

x= 12, 15, 19, 24, 27, 48.

y= A-Z incl., 0-9 incl., hyphen or blank.

(d) Rated values given.

@ Output values are rated not Max.

Marking: Company name and model designation.

Last Updated on 2008-11-03

[Questions?](#)[Notice of Disclaimer](#)[Page Top](#)

Copyright © 2008 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

