



QQQ.E191640

Power Supplies, Information Technology Equipment Including Electrical Business Equipment

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment

XP PLC

E191640

DEACON WAY, UNIT B2
TILEHURST, READING
BERKSHIRE
RG30 6AZ ENGLAND, UNITED KINGDOM

Adapters, Model(s) AEP25US(a).

Power supplies, Model(s) 45UM21YY, 45UM22YY, 80UM40YY (34YY), ACL150PM40, ACL150PM42, ACL150PM45, ACL150PM46, ACL200P203, ACL200PM23, ACL200PM25, ACL200PM26, ACL200PM31, ACL200PM32, ACL200PM40, ACL200PM45, ACL200PM46, ACL200PS05, ACL200PS12, ACL200PS15, ACL200PS24, ACL200PS48, ACL300PM23, ACL300PM25, ACL300PM26, ACL300PM31, ACL300PM32, ACL300PM40, ACL300PM45, ACL300PM46, ACL300PS03, ACL300PS05, ACL300PS12, ACL300PS15, ACL300PS24, ACL300PS48, AED06US05, AED06US055, AED06US06, AED06US07, AED06US08, AED06US084, AED06US088, AED06US09, AED06US10, AED06US12, AED06US65, AED06US68, AED06US75, AED10US(a), AED15US(a), AED25US(a), AED36US05YY, AED36US09YY, AED36US12YY, AED36US13YY, AED36US15YY, AED36US18YY, AED36US24YY, AED36US48YY, AED45US05YY, AED45US12YY, AED45US15YY, AED45US18YY, AED45US19YY, AED45US24YY, AED45US45YY, AED70US12YY, AED70US15YY, AED70US18YY, AED70US19YY, AED70US24YY, AED70US48YY, AEH15US03YY, AEH15US05YY, AEH15US07YY, AEH15US10YY, AEH15US12YY, AEH15US15YY, AEH15US18YY, AEH15US24YY, AEH15US30YY, AEH15US36YY, AEH15US48YY, AEH24US05YY, AEH24US07YY, AEH24US10YY, AEH24US12YY, AEH24US15YY, AEH24US18YY, AEH24US24YY, AEH24US30YY, AEH24US36YY, AEH24US48YY, AEH45UM23YY, AEH45UM25YY, AEH45UM26YY, AEH45UM27, AEH45UM28, AEH45UM29, AEH45UM31YY, AEH45UM32YY, AEH45UM33YY, AEH45UM34YY, AEH45UM35YY, AEH45UM38YY, AEH45UM39YY, AEH45US02YY, AEH45US03YY, AEH45US05YY, AEH45US07YY, AEH45US10YY, AEH45US12YY, AEH45US15YY, AEH45US18YY, AEH45US24YY, AEH45US30YY, AEH45US36YY, AEH60US05, AEH60US07YY, AEH60US10YY, AEH60US12YY, AEH60US15YY, AEH60US18YY, AEH60US24YY, AEH60US30YY, AEH60US36YY, AEH60US40YY, AEH60US48YY, AEH80UM23YY, AEH80UM25YY, AEH80UM26YY, AEH80UM27YY, AEH80UM28YY, AEH80UM29YY, AEH80UM31YY, AEH80UM32YY,

AEH80UM33YY, AEH80UM38YY, AEH80UM39YY, AEH80UM40YY, AEH80US03YY,
AEH80US05YY, AEH80US07YY, AEH80US10YY, AEH80US12YY, AEH80US15YY,
AEH80US18YY, AEH80US24YY, AEH80US30YY, AEH80US36YY, AEH80US48YY,
AEHUS05YY, AEP04US042, AEP04US05, AEP04US06, AEP06US05, AEP06US055, AEP06US06,
AEP06US065, AEP06US068, AEP06US07, AEP06US075, AEP06US08, AEP06US084, AEP06US088,
AEP06US09, AEP06US10, AEP06US12, AEP10US(a), AEP15US(a).

(a) - Followed by a 1 to 3 digit number.

Last Updated on 2005-04-07

This page and all contents are Copyright © 2005 by Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2005 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

