

QQGQ7.E317867

Power Supplies, Information Technology Equipment Including Electrical Business Equipment Certified for Canada

[Page Bottom](#)

Power Supplies, Information Technology Equipment Including Electrical Business Equipment Certified for Canada

[See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment Certified for Canada](#)

XP POWER LTD

E317867

401 COMMONWEALTH DR
 HAW PAR TECHNOCENTRE
 LOBBY B, #02-02
 SINGAPORE, 149598 SINGAPORE

AC Adaptor, Model(s) AML180PS18yyzzzz(&), AML180PS19yyzzzz(&), AML180PS24yyzzzz(&), AML180PS48yyzzzz (&), AML180PS18C6zzzz(&), AML180PS19C6zzzz(&), AML180PS24C6zzzz(&), AML180PS48C6zzzz(&).

Power supplies, Model(s) AMM150PSxCyzzzzzz (a).

Power Supply Adapter, Model(s) AEB36US05, AEB36US09, AEB36US12, AEB36US13, AEB36US15, AEB36US18, AEB36US24, AEB36US48.

Switching Power Adapters, Model(s) AEB70US12, AEB70US15, AEB70US18, AEB70US19, AEB70US24, AEB70US48, AMD150PS24yyzzzz(&), AMD150PS24C6zzzz(&), AMD150PS19yyzzzz(&), AMD150PS19C6zzzz (&), AMD150PS12yyzzzz(&), AMD150PS12C6zzzz(&).

Switching power supplies, Model(s) AEH130PD01, AEH130PD01/#20030-01, AEH130PD01/#20031-01, AEH130PD02, AEH130PD03, AEH130PD04, AEH130PS05, AEH130PS05>2581, AEH130PS07, AEH130PS07/#30014-01, AEH130PS09, AEH130PS09#10021-01, AEH130PS12, AEH130PS12/#10060-01, AEH130PS12/#10078-01, AEH130PS15, AEH130PS18, AEH130PS24, AEH130PS24>2108, AEH130PS24>2569, AEH130PS28, AEH130PS28/#30035-01, AEH130PS28>2160, AEH130PS36, AEH130PS36/#20011-01, AEH130PS3V3, AEH130PS3V3>2136, AEH130PS48, AEH130PS48/#30001-01, AEH130PS48/#30018-01, AEH130PS48>2652, AEH130PS54.

Switching Power Supply, Model(s) AEH130PD01, AEH130PD01/#20030-01, AEH130PD01/#20031-01, AEH130PD02, AEH130PD03, AEH130PD04, AEH130PS05, AEH130PS05>2581, AEH130PS07, AEH130PS07/#30014-01, AEH130PS09, AEH130PS09#10021-01, AEH130PS12, AEH130PS12/#10060-01, AEH130PS12/#10078-01, AEH130PS15, AEH130PS18, AEH130PS24, AEH130PS24>2108, AEH130PS24>2569, AEH130PS28, AEH130PS28/#30035-01, AEH130PS28>2160, AEH130PS36, AEH130PS36/#20011-01, AEH130PS3V3, AEH130PS3V3>2136, AEH130PS48, AEH130PS48/#30001-01, AEH130PS48/#30018-01, AEH130PS48>2652, AEH130PS54, AEL15USzC6XY, AEL15USzXY, AEL80US11-XY, AEL80US12-XY, AEL80US13-XY, AEL80US14-XY, AEL80US15-XY, AEL80US16-XY, AEL80US17-XY, AEL80US18-XY, AEL80US19-XY, AEL80US20-XY, AEL80US21-XY, AEL80US22-XY, AEL80US23-XY (f1).

Switching power supply, Model(s) VEH60US12xy, VEH60US15xy, VEH60US16xy, VEH60US18xy, VEH60US19xy, VEH60US20xy, VEH60US24xy, VEH60US30xy.

Model(s) AEL80US24-XY, AEL80US25-XY, AEL80US26-XY, AEL80US27-XY, AEL80US28-XY, AEL80US29-XY, AEL80US30-XY, AEL80US31-XY, AEL80US32-XY, AEL80US33-XY, AEL80US34-XY, AEL80US35-XY, AEL80US36-XY, AEL80US37-XY, AEL80US38-XY, AEL80US39-XY, AEL80US40-XY, AEL80US41-XY, AEL80US42-XY, AEL80US43-XY, AEL80US44-XY, AEL80US45-XY, AEL80US46-XY, AEL80US47-XY and AEL80US48-XY (f1).

(&) - Where y= C6 or blank; where Z=blank,0-9, or A-Z for marketing purposes

(a) - x= 12, 15, 19, 24, 27, 48; y= A-Z, 0-9, hyphen or blank

(f1) - Where X = 0-9, A-Z or blank, and Y = 0-9, A-Z or blank

x&y - 0-9,A-Z,blank

z - where z can be 03 to 48; X and Y can be blank, 0-9 or A - Z

[Last Updated](#) on 2008-10-28

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2008 Underwriters Laboratories Inc.](#)[Copyright © 2008 Underwriters Laboratories Inc.](#)[Copyright © 2008 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions:
1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"