

# Certificate



Certificate no.

CU 72161911 01

**License Holder:**

XP Power Limited  
Haw Par Technocentre, Lobby B, #02-02  
401 Commonwealth Drive  
Singapore 149598  
Singapore

**Manufacturing Plant:**

-AK-10056311 001

Test report no.: USA-AK 10056311 003

Client Reference:

Tested to: UL 60950-1:2007 R10.14  
CAN/CSA-C22.2 NO.60950-1-07+A1:2011+A2:2014

Certified Product: DIN RAIL MOUNTABLE POWER SUPPLIES

License Fee - Units

Model Designation: DPC70USXXYZ  
(XX=12, 24, 48; Y= -S, blank,  
Z=0-9, A-Z, a-z, "-", blank)

7

Rated Voltage : AC 100-240V, 47-63Hz  
Rated Current : 1700 mA  
Output Ratings : see Appendix (Constr. Data Form)  
Protection Class : I  
Ambient temperature: 50°C max.

Special Remarks: To be installed according to the licensee's  
installation instructions.

7

Licensed Test mark:



Date of Issue  
(day/mo/yr)  
15/08/2016



# Appendix

(For TUV Rheinland of N.A., Inc. use only)

Certificate # CU72161911.01 File # 10056311 003

**License Holder:** XP Power Limited

**Address:** 401 Commonwealth Drive, Haw Par Technocentre, Lobby B, #02-02, 149598, Singapore

**Type of Product:** DIN RAIL MOUNTABLE POWER SUPPLIES

**Model Number:** DPC70USXYZ (XX = 12, 24 or 48; Y = -S or blank; Z = 0-9, A-Z, a-z, "-", blank)

## Input and output ratings:

Input: 100-240 Vac, 47-63 Hz, 1700 mA

Co XP Power Limited model	Output Voltage (Vdc)	Output Current (A)	Output Power (W)
DPC70US12-S	12	5.5	66
DPC70US12	12	5.5	66
DPC70US24-S	24	3	72
DPC70US24	24	3	72
DPC70US048-S	48	1.5	72
DPC70US48	48	1.5	72