

Certificate no. 137994-01

Demko Certificate

Product: Power Supply, Built-In AC /DC
Manufacturer: 30619
Production site: 29572
Certified by request of: XPiQ Inc.
260 Hopping Brook Rd., Holliston, MA 01746, USA
Trademark: XP
Model/Type ref.: See appendix
Rated current or power: 2.2A
Rated voltage: 100-240 V ac, 50/60 Hz
Insulation Class: Class I
Degree of protection: IPX0
Additional information: Max output Power: 165W

Variants covered by this certificate are specified in the attached appendix.
Detailed specification of the certified product(s) is listed in the appendix.

A sample of the product has been tested and found in conformity with EN 60950:2000, as shown in the Test Report from Underwriters Laboratories with ref. No. E211115-A2-CB-1 dated 2004-04-07 and amendment 1 dated 2004-08-03

Furthermore, the product complies with the national deviations in Denmark.

Date of expiry: 2006-07-01

UL International Demko A/S is a body notified to the Member States and Commission of the European Communities according to the provisions of Article 8 of the Low Voltage Directive.

The Manufacturer complies with the Production Surveillance Requirements.

Products included in this certificate are allowed to carry the registered approval marks of UL International Demko A/S, ® or for cables <DEMKO>. The name of UL International Demko A/S can be used in the marketing of the products as well.

This certificate is only valid for products, which are identical to the certified product, and manufactured at the above mentioned production site(s). UL International Demko A/S has to be informed in writing about any changes, in accordance with the "UL International Demko A/S Standard Terms and Conditions" for UL International Demko A/S services.

Herlev, 2004-08-20


Karina Christiansen
Certification Manager

UL International Demko A/S

Lyskaer 8, P.O. Box 514
DK-2730 Herlev, Denmark
Telephone: +45 44856565
Fax: +45 44856500



An Affiliate of
**Underwriters
Laboratories Inc.®**

Certificate no. 137994-01

Appendix to Demko Certificate No. 137994-01

The Certificate covers the following:

137994-01-0001; IFC165PQ40;

Output:

+3.3 V dc, 16 A (1)

+5.0 V dc, 20 A (1)

+12.0 V dc, 6 A

-12 Vdc, 1.0 A

137994-01-0002; IFC165PS05;

Output:

+5.0 V dc, 33 A

+12.0 Vdc, 1.0 A

137994-01-0003; IFC165PS12;

Output:

+12.0 V dc, 13.7 A

-12 Vdc, 1.0 A

137994-01-0004; IFC165PS24;

Output:

+24.0 V dc, 6.9 A

+12 Vdc, 1.0 A

137994-01-0005; IFC165PS48;

Output:

+48 V dc, 3.4 A

+12 Vdc, 1.0 A

137994-01-0006; IFC165PT31;

Output:

+5 V dc, 21 A (1)

+12.0 V dc, 6 A

-12 Vdc, 1.0 A

Herlev, 2004-08-20


Karina Christiansen
Certification Manager

UL International Demko A/S

Lyskaer 8, P.O. Box 514
DK-2730 Herlev, Denmark
Telephone: +45 44856565
Fax: +45 44856500



An Affiliate of
**Underwriters
Laboratories Inc.®**

Certificate no. 137994-01

Appendix to Demko Certificate No. 137994-01

(1) The V1 output alone or V1 and V2 outputs together have been evaluated for a maximum combined output power of 100 W with 10 CFM

The certificate has been issued on the basis of CB certificate (CB Test certificate) No. US/8039A/UL, issued by Underwriters Laboratories, dated 2004-08-05.

Herlev, 2004-08-20


Karina Christiansen
Certification Manager

UL International Demko A/S

Lyskaer 8, P.O. Box 514
DK-2730 Herlev, Denmark
Telephone: +45 44856565
Fax: +45 44856500



An Affiliate of
**Underwriters
Laboratories Inc.®**