


CERTIFICATE OF COMPLIANCE

Certificate Number E317867
Report Reference E317867-20140717
Issue Date 2019-DECEMBER-11

ITX0515SA-R, ITX0524SA-R, ITX0505S-R, ITX0512S-R, ITX0515S-R, ITX1203SA-R, ITX1205SA-R, ITX1209SA-R, ITX1212SA-R, ITX1215SA-R, ITX1224SA-R, ITX1205S-R, ITX1212S-R, ITX1215S-R, ITX2403SA-R, ITX2405SA-R, ITX2409SA-R, ITX2412SA-R, ITX2415SA-R, ITX2424SA-R, ITX2405S-R, ITX2412S-R, ITX2415S-R, ITX4803SA-R, ITX4805SA-R, ITX4809SA-R, ITX4812SA-R, ITX4815SA-R, ITX4824SA-R, ITX4805S-R, ITX4812S-R, ITX4815S-R, ITX0503SA-HR, ITX0505SA-HR, ITX0509SA-HR, ITX0512SA-HR, ITX0515SA-HR, ITX0524SA-HR, ITX0505S-HR, ITX0512S-HR, ITX0515S-HR, ITX1203SA-HR, ITX1205SA-HR, ITX1209SA-HR, ITX1212SA-HR, ITX1215SA-HR, ITX1224SA-HR, ITX1205S-HR, ITX1212S-HR, ITX1215S-HR, ITX2403SA-HR, ITX2405SA-HR, ITX2409SA-HR, ITX2412SA-HR, ITX2415SA-HR, ITX2424SA-HR, ITX2405S-HR, ITX2412S-HR, ITX2415S-HR, ITX4803SA-HR, ITX4805SA-HR, ITX4809SA-HR, ITX4812SA-HR, ITX4815SA-HR, ITX4824SA-HR, ITX4805S-HR, ITX4812S-HR, ITX4815S-HR, ITQ2403SA, ITQ2405SA, ITQ2409SA, ITQ2412SA, ITQ2415SA, ITQ2424SA, ITQ2405S, ITQ2412S, ITQ2415S, ITQ4803SA, ITQ4805SA, ITQ4809SA, ITQ4812SA, ITQ4815SA, ITQ4824SA, ITQ4805S, ITQ4812S, ITQ4815S, ITQ2403SA-H, ITQ2405SA-H, ITQ2409SA-H, ITQ2412SA-H, ITQ2415SA-H, ITQ2424SA-H, ITQ2405S-H, ITQ2412S-H, ITQ2415S-H, ITQ4803SA-H, ITQ4805SA-H, ITQ4809SA-H, ITQ4812SA-H, ITQ4815SA-H, ITQ4824SA-H, ITQ4805S-H, ITQ4812S-H, ITQ4815S-H, JTL6024S05, JTL6024S12, JTL6024S15, JTL6048S05, JTL6048S12, JTL6048S15, JTL6024D12, JTL6024D15, JTL6048D12, JTL6048D15, JTL6024S05-HK, JTL6024S12-HK, JTL6024S15-HK, JTL6048S05-HK, JTL6048S12-HK, JTL6048S15-HK, JTL6024D12-HK, JTL6024D15-HK, JTL6048D12-HK, JTL6048D15-HK, JTF0824S3V3, JTF0824S05, JTF0824S12, JTF0824S15, JTF0824D05, JTF0824D12, JTF0824D15, JTF0848S3V3, JTF0848S05, JTF0848S12, JTF0848S15, JTF0848D05, JTF0848D12, JTF0848D15, JTF1024S3V3, JTF1024S05, JTF1024S12, JTF1024S15, JTF1024D05, JTF1024D12, JTF1024D15, JTF1048S3V3, JTF1048S05, JTF1048S12, JTF1048S15, JTF1048D05, JTF1048D12, JTF1048D15, JTF1224S3V3, JTF1224S05, JTF1224S12, JTF1224S15, JTF1224D05, JTF1224D12, JTF1224D15, JTF1248S3V3, JTF1248S05, JTF1248S12, JTF1248S15, JTF1248D05, JTF1248D12, JTF1248D15, JTD2024S3V3, JTD2024S05, JTD2024S12, JTD2024S15, JTD2048S3V3, JTD2048S05, JTD2048S12, JTD2048S15, JTD2024D05, JTD2024D12, JTD2024D15, JTD2048D05, JTD2048D12, JTD2048D15, JTD2024S3V3-HK, JTD2024S05-HK, JTD2024S12-HK, JTD2024S15-HK, JTD2048S3V3-HK, JTD2048S05-HK, JTD2048S12-HK, JTD2048S15-HK, JTD2024D05-HK, JTD2024D12-HK, JTD2024D15-HK, JTD2048D05-HK, JTD2048D12-HK, JTD2048D15-HK, JTD1524S3V3, JTD1524S05, JTD1524S12, JTD1524S15, JTD1548S3V3, JTD1548S05, JTD1548S12, JTD1548S15, JTD1524D05, JTD1524D12, JTD1524D15, JTD1548D05, JTD1548D12, JTD1548D15, JTD1524S3V3-HK, JTD1524S05-HK, JTD1524S12-HK, JTD1524S15-HK, JTD1548S3V3-HK, JTD1548S05-HK, JTD1548S12-HK, JTD1548S15-HK, JTD1524D05-HK, JTD1524D12-HK, JTD1524D15-HK, JTD1548D05-HK, JTD1548D12-HK, JTD1548D15-HK, IW0503SA, IW0505SA, IW0507SA, IW0509SA, IW0512SA, IW0515SA, IW0518SA, IW0524SA, IW1203SA, IW1205SA, IW1207SA, IW1209SA, IW1212SA, IW1215SA, IW1218SA, IW1224SA, IW2403SA, IW2405SA, IW2407SA, IW2409SA, IW2412SA, IW2415SA, IW2418SA, IW2424SA, IW4803SA, IW4805SA, IW4807SA, IW4809SA, IW4812SA, IW4815SA, IW4818SA, IW4824SA, IW0503SA-H, IW0505SA-H, IW0507SA-H, IW0509SA-H, IW0512SA-H, IW0515SA-H, IW0518SA-H, IW0524SA-H, IW1203SA-H, IW1205SA-H, IW1207SA-H, IW1209SA-H, IW1212SA-H, IW1215SA-H, IW1218SA-H, IW1224SA-H, IW2403SA-H, IW2405SA-H, IW2407SA-H, IW2409SA-H, IW2412SA-H, IW2415SA-H, IW2418SA-H, IW2424SA-H, IW4803SA-H, IW4805SA-H, IW4807SA-H, IW4809SA-H, IW4812SA-H, IW4815SA-H, IW4818SA-H, IW4824SA-H, IW0503SA-R, IW0505SA-R, IW0507SA-R, IW0509SA-R, IW0512SA-R, IW0515SA-R, IW0518SA-R,



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

