

Certificate of Compliance

Certificate Number:
E317867

Report Reference:
E317867-20241113

Issue Date:
2025-01-10

Issued to:

XP POWER L L C
340 Commerce, Suite 100 Irvine, CA 92602
United States

This certificate confirms that representative samples of:

Power Supplies for Use with Audio/Video, Information and Communication Technology Equipment - Component

See Addendum Page for Product Designation(s).

Have been evaluated by UL in accordance with the component requirements in the Standard(s) indicated on this Certificate. UL Recognized components are incomplete in certain constructional features or restricted in performance capabilities and are intended for installation in complete equipment submitted for investigation to UL LLC.

UL 62368-1& CAN/CSA C22.2 No. 62368-1:19 - Audio/video, information and communication technology equipment Part 1: Safety requirements

Additional Information:

See the UL Online Certifications Directory at <https://iq.ulprospector.com> for additional information.

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Recognized Component Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



A handwritten signature in black ink, appearing to read 'David Piecuch'.

David Piecuch
UL Mark Certification Program Owner

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.

Certificate of Compliance

Certificate Number: E317867
Report Reference: E317867-20241113
Issue Date: 2025-01-10

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

DC to DC Converter:

#SFT03C05D12#, #SFT03C05D15#, #SFT03C05S05#, #SFT03C05S12#, #SFT03C05S15#,
#SFT03C05S3V3#, #SGT01C05D12#, #SGT01C05D15#, #SGT01C05S05#, #SGT01C05S12#,
#SGT01C05S15#, #SGT01C05S3V3#, #SFT01T24S3V3#, #SFT01T24S05#, #SFT01T24S12#,
#SFT01T24S15#, #SFT01T24D05#, #SFT01T24D12#, #SFT01T24D15#, #SFT03T24S3V3#,
#SFT03T24S05#, #SFT03T24S12#, #SFT03T24S15#, #SFT03T24D05#, #SFT03T24D12#,
#SFT03T24D15#

Note: where “#” can be up to 8 characters or blank.

DC to DC Converter:

#SDT01F03S3V3#, #SDT01F03S05#, #SDT01F03S09#, #SDT01F03S12#, #SDT01F03S15#,
#SDT01F03V3D3V3#, #SDT01F03V3D05#, #SDT01F03V3D09#, #SDT01F03V3D12#, #SDT01F03V3D15#,
#SDT01F05S3V3#, #SDT01F05S05#, #SDT01F05S09#, #SDT01F05S12#, #SDT01F05S15#,
#SDT01F05D3V3#, #SDT01F05D05#, #SDT01F05D09#, #SDT01F05D12#, #SDT01F05D15#,
#SDT01F12S3V3#, #SDT01F12S05#, #SDT01F12S09#, #SDT01F12S12#, #SDT01F12S15#,
#SDT01F12D3V3#, #SDT01F12D05#, #SDT01F12D09#, #SDT01F12D12#, #SDT01F12D15#,
#SDT01F24S3V3#, #SDT01F24S05#, #SDT01F24S09#, #SDT01F24S12#, #SDT01F24S15#,
#SDT01F24D3V3#, #SDT01F24D05#, #SDT01F24D09#, #SDT01F24D12#, #SDT01F24D15#

Note: where “#” can be up to 8 characters or blank.

DC to DC Converter – Models, #PBT01F03S3V3# [a], #PBT01F03S05# [a], #PBT01F03S12# [a],
#PBT01F03S15# [a], #PBT01F03D3V3# [a], #PBT01F03D05# [a], #PBT01F03D09# [a], #PBT01F03D12# [a],
#PBT01F03D15# [a], #PBT01F05S3V3# [a], #PBT01F05S05# [a], #PBT01F05S09# [a], #PBT01F05S12# [a],
#PBT01F05S15# [a], #PBT01F05D3V3# [a], #PBT01F05D05# [a], #PBT01F05D09# [a], #PBT01F05D12# [a],
#PBT01F05D15# [a], #PBT01F12S3V3# [a], #PBT01F12S05# [a], #PBT01F12S09# [a], #PBT01F12S12# [a],
#PBT01F12S15# [a], #PBT01F12D3V3# [a], #PBT01F12D05# [a], #PBT01F12D09# [a], #PBT01F12D12# [a],
#PBT01F12D15# [a], #PBT01F15S05# [a], #PBT01F03S3V3# [a], #PBT01F03S05# [a], #PBT01F03S12# [a],
#PBT01F03S15# [a], #PBT01F03D3V3# [a], #PBT01F03D05# [a], #PBT01F03D09# [a], #PBT01F03D12# [a],
#PBT01F03D15# [a], #PBT01F05S3V3# [a], #PBT01F05S05# [a], #PBT01F05S09# [a], #PBT01F05S12# [a],
#PBT01F05S15# [a], #PBT01F05D3V3# [a], #PBT01F05D05# [a], #PBT01F05D09# [a], #PBT01F05D12# [a],
#PBT01F05D15# [a], #PBT01F12S3V3# [a], #PBT01F12S05# [a], #PBT01F12S09# [a], #PBT01F12S12# [a],
#PBT01F12S15# [a], #PBT01F12D3V3# [a], #PBT01F12D05# [a], #PBT01F12D09# [a], #PBT01F12D12# [a],
#PBT01F12D15# [a], #PBT01F15S05# [a].



Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.