

QQGQ2.E317867

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

[Page Bottom](#)

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

[See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component](#)

XP POWER LTD

E317867

401 COMMONWEALTH DR
 HAW PAR TECHNOCENTRE
 LOBBY B, #02-02
 SINGAPORE, 149598 SINGAPORE

Model No.	Rated Input			Max Output			OC	SP	EP	FC	GC
	Volts	Hz	SC	V	A	VA					
"Switching Power Supply".											
VCP15US03-E-XXXXXXX[*r]											
	100-240Vac	50/60	0	3dc	0.01-2.0	-	3	60950-1	20B	0	2
VCP15US03-XXXXXXX[*r]											
	100-240Vac	50/60	0	3dc	0.01-2.0	-	3	60950-1	20B	0	2
VCP15US033-E-XXXXXXX[*r]											
	100-240Vac	50/60	0	3.3dc	0.01-2.0	-	3	60950-1	20B	0	2
VCP15US033-XXXXXXX[*r]											
	100-240Vac	50/60	0	3.3dc	0.01-2.0	-	3	60950-1	20B	0	2
VCP15US036-E-XXXXXXX[*r]											
	100-240Vac	50/60	0	3.6dc	0.01-2.0	-	3	60950-1	20B	0	2
VCP15US036-XXXXXXX[*r]											
	100-240Vac	50/60	0	3.6dc	0.01-2.0	-	3	60950-1	20B	0	2
VCP15US04-E-XXXXXXX[*r]											

JPS350PQ47, JPS350PQ47C											
100-250ac	47-63	0	4.99	52.3	243.1	3	60950-1	20B	0	0	
			11.98	27.6	299.8	3					
			27.9	13.9	280.4	3					
			-12.25	4.05	42	3					

JPS350PQ48, JPS350PQ48C											
100-250ac	47-63	0	5.01	52.6	247.3	3	60950-1	20B	0	0	
			14.95	18	261	3					
			27.3	11.7	255.7	3					
			-15.13	4.1	44.6	3					

JPS350PS05, JPS350PS05C, JPS350PS12, JPS350PS12C, JPS350PS15, JPS350PS15C, JPS350PS24, JPS350PS24C, JPS350PS48, JPS350PS48C, JPS350PS05-E, JPS350PS12-E, JPS350PS15-E, JPS350PS24-E, JPS350PS48-E											
100-250ac	47-63	0	5.29dc	74.64	347.84	3	60950-1, 2nd	20B	0	0	
			12.018dc	35.2	418.17	3					
			15.075dc	27.44	410	3					
			24.07dc	16.75	401.5	3					
			48.13dc	8.18	392.1	3					

PUL300-42-3											
100-240ac	50/60	0	5.77	36	124.7	3	1950	20B	2,6	1	
			3.81	81.7	102.3	3					
			24.4	34.3	266.4	3					
			-12.1	1.47	11.02	3					

QSB15024S05											
9-36, 24Vdc	-	4	4.98	35.2	169.4	4	60950-1	20B	3, 4	0	

QSB15024S12[*r]											
9-36, 24Vdc	-	4	12	12.5	-	4	60950-1	20B	3, 4	0	

QSB15024S15[*r]											
9-36, 24Vdc	-	4	15	10	-	4	60950-1	20B	3, 4	0	

QSB15024S24											
9-36, 24Vdc	-	4	24.02	8.26	183.5	4	60950-1	20B	3, 4	0	

QSB15024S3V3[*r]											
	9-36, 24Vdc	-	4	3.3	30	-	4	60950-1	20B	3, 4	0
QSB15048S05											
	18-75, 48Vdc	-	4	4.97	34.9	163	4	60950-1	20B	3, 4	0
QSB15048S12[*r]											
	18-75, 48Vdc	-	4	12	12.5	-	4	60950-1	20B	3, 4	0
QSB15048S15[*r]											
	18-75, 48Vdc	-	4	15	10	-	4	60950-1	20B	3, 4	0
QSB15048S24											
	18-75, 48Vdc	-	4	23.98	8.1	190	4	60950-1	20B	3, 4	0
QSB15048S3V3[*r]											
	18-75, 48Vdc	-	4	3.3	30	-	4	60950-1	20B	3, 4	0
QSB20024S05											
	10-36, 24dc	-	4	4.99	52.16	244.1	3	60950-1	6.3T	0	0
QSB20024S12											
	10-36, 24dc	-	4	12.01	19.34	230	3	60950-1	6.3T	0	0
QSB20024S15[*r]											
	10-36, 24dc	-	4	15	13.3	-	3	60950-1	6.3T	0	0
QSB20024S24											
	10-36, 24dc	-	4	24.03	11.19	125.91	3	60950-1	6.3T	0	0
QSB20024S3V3[*r]											
	10-36, 24dc	-	4	3.3	40	-	3	60950-1	6.3T	0	0
QSB20048S05											
	18-75, 48dc	-	4	4.98	47.36	222	3	60950-1	6.3T	0	0
QSB20048S12											
	18-75, 48dc	-	4	11.98	21.03	249.5	3	60950-1	6.3T	0	0
QSB20048S15[*r]											
	18-75, 48dc	-	4	15	13.3	-	3	60950-1	6.3T	0	0
QSB20048S24											

	18-75, 48dc	-	4	23.97	9.81	234.7	3	60950-1	6.3T	0	0
QSB20048S3V3[*r]											
	18-75, 48dc	-	4	3.3	40	-	3	60950-1	6.3T	0	0
SDC320PD0512-zz, SDC320PD0512-Czz, SDC320PD0512-Ezz, SDC320PD0512-Fzz (b)											
	100-240ac	47/63	0	5	30	250	3	60950-1	20B	5, 8	1
				12	16.67	250	3				
SDC320PD0512-zz, SDC320PD0512-Czz, SDC320PD0512-Ezz, SDC320PD0512-Fzz (b) without fan											
	100-240ac	47/63	0	5	15	125	3	60950-1	20B	5, 8	1
				12	10.42	125	3				
SDC320PD0524-zz, SDC320PD0524-Czz, SDC320PD0524-Ezz, SDC320PD0524-Fzz (b)											
	100-240ac	47/63	0	5	30	250	3	60950-1	20B	5, 8	1
				12	16.67	250	3				
SDC320PD0524-zz, SDC320PD0524-Czz, SDC320PD0524-Ezz, SDC320PD0524-Fzz (b) without fan											
	100-240ac	47/63	0	5	15	125	3	60950-1	20B	5, 8	1
				24	5.2	125	3				
SDC320PD0548-zz, SDC320PD0548-Czz, SDC320PD0548-Ezz, SDC320PD0548-Fzz (b) without fan											
	100-240ac	47/63	0	5	15	125	3	60950-1	20B	5, 8	1
				48	2.6	125	3				
SDC320PD0548-zz, SDC320PD0548-Czz, SDC320PD0548-Ezz, SDC320PD0548-Fzz (b)											
	100-240ac	47/63	0	5	30	250	3	60950-1	20B	5, 8	1
				48	4.16	250	3				
SDC320PD1224-zz, SDC320PD1224-Czz, SDC320PD1224-Ezz, SDC320PD1224-Fzz (b)											
	100-240ac	47/63	0	12.02	24.67	249	3	60950-1	20B	5, 8	1
				24.31	13.33	313.7	3				
SDC320PD1224-zz, SDC320PD1224-Czz, SDC320PD1224-Ezz, SDC320PD1224-Fzz (b) without fan											
	100-240ac	47/63	0	12	12.5	125	3	60950-1	20B	5, 8	1
				24	6.25	125	3				
SDC320PS02-zz, SDC320PS02-Czz, SDC320PS02-Ezz, SDC320PS02-Fzz (b)											
	100-240ac	47/63	0	6.01	58	278	3	60950-1	20B	5, 8	1