



QQGQ.E317867

Power Supplies, Information Technology Equipment Including Electrical Business Equipment

Page Bottom

Power Supplies, Information Technology Equipment Including Electrical Business Equipment

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment

XP POWER L L C

E317867

15641 RED HILL AVE, SUITE 100
TUSTIN, CA 92780 USA



Trademark and/or Tradename:

AC Adapter, Model(s) AEB100PS36

VEH120PS12, VEH120PS19, VEH120PS24

VEH150PS12, VEH150PS15, VEH150PS16, VEH150PS19, VEH150PS24, VEL12USxxx-US-JA(p), VEL12USxxx-US-JA-H(p)

VEL18US087-US-JA, VEL18US088-US-JA, VEL18US089-US-JA, VEL18US090-US-JA, VEL18US091-US-JA, VEL18US092-US-JA, VEL18US093-US-JA, VEL18US094-US-JA, VEL18US095-US-JA, VEL18US096-US-JA, VEL18US097-US-JA, VEL18US098-US-JA, VEL18US099-US-JA, VEL18US100-US-JA, VEL18US101-US-JA, VEL18US102-US-JA, VEL18US103-US-JA, VEL18US104-US-JA, VEL18US105-US-JA, VEL18US106-US-JA, VEL18US107-US-JA, VEL18US108-US-JA, VEL18US109-US-JA, VEL18US110-US-JA, VEL18US111-US-JA, VEL18US112-US-JA, VEL18US113-US-JA, VEL18US114-US-JA, VEL18US115-US-JA, VEL18US116-US-JA, VEL18US117-US-JA, VEL18US118-US-JA, VEL18US119-US-JA, VEL18US120-US-JA, VEL18US121-US-JA, VEL18US122-US-JA, VEL18US123-US-JA, VEL18US124-US-JA, VEL18US125-US-JA, VEL18US126-US-JA, VEL18US127-US-JA, VEL18US128-US-JA, VEL18US129-US-JA, VEL18US130-US-JA, VEL18US131-US-JA, VEL18US132-US-JA, VEL18US133-US-JA, VEL18US134-US-JA, VEL18US135-US-JA, VEL18US136-US-JA, VEL18US137-US-JA, VEL18US138-US-JA, VEL18US139-US-JA, VEL18US140-US-JA, VEL18US141-US-JA, VEL18US142-US-JA, VEL18US143-US-JA, VEL18US144-US-JA, VEL18US145-US-JA, VEL18US146-US-JA, VEL18US147-US-JA, VEL18US148-US-JA, VEL18US149-US-JA, VEL18US150-US-JA, VEL18US151-US-JA, VEL18US152-US-JA, VEL18US153-US-JA, VEL18US154-US-JA, VEL18US155-US-JA, VEL18US156-US-JA, VEL18US157-US-JA, VEL18US158-US-JA, VEL18US159-US-JA, VEL18US160-US-JA, VEL18US161-US-JA, VEL18US162-US-JA, VEL18US163-US-JA, VEL18US164-US-JA, VEL18US165-US-JA, VEL18US166-US-JA, VEL18US167-US-JA, VEL18US168-US-JA, VEL18US169-US-JA, VEL18US170-US-JA, VEL18US171-US-JA, VEL18US172-US-JA, VEL18US173-US-JA, VEL18US174-US-JA, VEL18US175-US-JA, VEL18US176-US-JA, VEL18US177-US-JA, VEL18US178-US-JA, VEL18US179-US-JA, VEL18US180-US-JA, VEL18US181-US-JA, VEL18US182-US-JA, VEL18US183-US-JA, VEL18US184-US-JA, VEL18US185-US-JA, VEL18US186-US-JA, VEL18US187-US-JA, VEL18US188-US-JA, VEL18US189-US-JA, VEL18US190-US-JA, VEL18US191-US-JA, VEL18US192-US-JA, VEL18US193-US-JA, VEL18US194-US-JA, VEL18US195-US-JA, VEL18US196-US-JA, VEL18US197-US-JA

VEL18US111-US-JA-H, VEL18US112-US-JA-H, VEL18US113-US-JA-H, VEL18US114-US-JA-H, VEL18US115-US-JA-H, VEL18US116-US-JA-H, VEL18US117-US-JA-H, VEL18US118-US-JA-H, VEL18US119-US-JA-H, VEL18US120-US-JA-H, VEL18US121-US-JA-H, VEL18US122-US-JA-H, VEL18US123-US-JA-H, VEL18US124-US-JA-H, VEL18US125-US-JA-H, VEL18US126-US-JA-H, VEL18US127-US-JA-H, VEL18US128-US-JA-H, VEL18US129-US-JA-H, VEL18US130-US-JA-H, VEL18US131-US-JA-H, VEL18US132-US-JA-H, VEL18US133-US-JA-H, VEL18US134-US-JA-H, VEL18US135-US-JA-H, VEL18US136-US-JA-H, VEL18US137-US-JA-H, VEL18US138-US-JA-H, VEL18US139-US-JA-H, VEL18US140-US-JA-H, VEL18US141-US-JA-H, VEL18US142-US-JA-H, VEL18US143-US-JA-H, VEL18US144-US-JA-H, VEL18US145-US-JA-H, VEL18US146-US-JA-H, VEL18US147-US-JA-H, VEL18US148-US-JA-H, VEL18US149-US-JA-H, VEL18US150-US-JA-H, VEL18US151-US-JA-H, VEL18US152-US-JA-H, VEL18US153-US-JA-H, VEL18US154-US-JA-H, VEL18US155-US-JA-H, VEL18US156-US-JA-H, VEL18US157-US-JA-H, VEL18US158-US-JA-H, VEL18US159-US-JA-H, VEL18US160-US-JA-H, VEL18US161-US-JA-H, VEL18US162-US-JA-H, VEL18US163-US-JA-H, VEL18US164-US-JA-H, VEL18US165-US-JA-H, VEL18US166-US-JA-H, VEL18US167-US-JA-H, VEL18US168-US-JA-H, VEL18US169-US-JA-H, VEL18US170-US-JA-H, VEL18US171-US-JA-H, VEL18US172-US-JA-H, VEL18US173-US-JA-H, VEL18US174-US-JA-H, VEL18US175-US-JA-H, VEL18US176-US-JA-H, VEL18US177-US-JA-H, VEL18US178-US-JA-H, VEL18US179-US-JA-H, VEL18US180-US-JA-H, VEL18US181-US-JA-H, VEL18US182-US-JA-H, VEL18US183-US-JA-H, VEL18US184-US-JA-H, VEL18US185-US-JA-H, VEL18US186-US-JA-H, VEL18US187-US-JA-H, VEL18US188-US-JA-H, VEL18US189-US-JA-H, VEL18US190-US-JA-H, VEL18US191-US-JA-H, VEL18US192-US-JA-H, VEL18US193-US-JA-H, VEL18US194-US-JA-H, VEL18US195-US-JA-H, VEL18US196-US-JA-H, VEL18US197-US-JA-H, VEL18US198-US-JA-H, VEL18US199-US-JA-H, VEL18US200-US-JA-H, VEL18US201-US-JA-H, VEL18US202-US-JA-H, VEL18US203-US-JA-H, VEL18US204-US-JA-H, VEL18US205-US-JA-H, VEL18US206-US-JA-H, VEL18US207-US-JA-H, VEL18US208-US-JA-H, VEL18US209-US-JA-H, VEL18US210-US-JA-H

VEL18US198-US-JA, VEL18US199-US-JA, VEL18US200-US-JA, VEL18US201-US-JA, VEL18US202-US-JA, VEL18US203-US-JA, VEL18US204-US-JA, VEL18US205-US-JA, VEL18US206-US-JA, VEL18US207-US-JA, VEL18US208-US-JA, VEL18US209-US-JA, VEL18US210-US-JA, VEL18US211-US-JA, VEL18US212-US-JA, VEL18US213-US-JA, VEL18US214-US-JA, VEL18US215-US-JA, VEL18US216-US-JA, VEL18US217-US-JA, VEL18US218-US-JA, VEL18US219-US-JA, VEL18US220-US-JA, VEL18US221-US-JA, VEL18US222-US-JA, VEL18US223-US-JA, VEL18US224-US-JA, VEL18US225-US-JA, VEL18US226-US-JA, VEL18US227-US-JA, VEL18US228-US-JA, VEL18US229-US-JA, VEL18US230-US-JA, VEL18US231-US-JA, VEL18US232-US-JA, VEL18US233-US-JA, VEL18US234-US-JA, VEL18US235-US-JA, VEL18US236-US-JA, VEL18US237-US-JA, VEL18US238-US-JA, VEL18US239-US-JA, VEL18US240-US-JA, VEL18US050-US-JA-H, VEL18US051-US-JA-H, VEL18US052-US-JA-H, VEL18US053-US-JA-H, VEL18US054-US-JA-H, VEL18US055-US-JA-H, VEL18US056-US-JA-H, VEL18US057-US-JA-H, VEL18US058-US-JA-H, VEL18US059-US-JA-H, VEL18US060-US-JA-H, VEL18US061-US-JA-H, VEL18US062-US-JA-H, VEL18US063-US-JA-H, VEL18US064-US-JA-H, VEL18US065-US-JA-H, VEL18US066-US-JA-H, VEL18US067-US-JA-H, VEL18US068-US-JA-H, VEL18US069-US-JA-H, VEL18US070-US-JA-H, VEL18US071-US-JA-H, VEL18US072-US-JA-H, VEL18US073-US-JA-H, VEL18US074-US-JA-H, VEL18US075-US-JA-H, VEL18US076-US-JA-H, VEL18US077-US-JA-H, VEL18US078-US-JA-H, VEL18US079-US-JA-H, VEL18US080-US-JA-H, VEL18US081-US-JA-H, VEL18US082-US-JA-H,

AEL40US14-XY, AEL40US15-XY, AEL40US16-XY, AEL40US17-XY, AEL40US18-XY, AEL40US19-XY, AEL40US20-XY, AEL40US21-XY, AEL40US22-XY, AEL40US23-XY, AEL40US24-XY, AEL40US24-XE0001B, AEL40US25-XY, AEL40US26-XY, AEL40US27-XY, AEL40US28-XY, AEL40US29-XY, AEL40US30-XY, AEL40US31-XY, AEL40US32-XY, AEL40US33-XY, AEL40US34-XY, AEL40US35-XY, AEL40US36-XY, AEL40US37-XY, AEL40US38-XY, AEL40US39-XY, AEL40US40-XY, AEL40US41-XY, AEL40US42-XY, AEL40US43-XY, AEL40US44-XY, AEL40US45-XY, AEL40US46-XY, AEL40US47-XY, AEL40US48-XY, AEL40US49-XY, AEL40US50-XY (-)

Switching power supply adapters, Model(s) AEH24US05YY(b), AEH24US07YY(b), AEH24US10YY(b), AEH24US12YY(b), AEH24US15YY(b), AEH24US18YY(b), AEH24US24YY(b), AEH24US30YY(b), AEH24US36YY(b), AEH24US48YY(b)

AEH80US03YY(b), AEH80US05YY(b), AEH80US07YY(b), AEH80US10YY(b), AEH80US12YY(b), AEH80US15YY(b), AEH80US18YY(b), AEH80US24YY(b), AEH80US30YY(b), AEH80US36YY(b), AEH80US48YY(b), AEH80UM27YY(b), AEH80UM23YY(b), AEH80UM26YY(b), AEH80UM25YY(b), AEH80UM28YY(b), AEH80UM29YY(b), AEH80UM37YY(b), AEH80UM33YY(b), AEH80UM31YY(b), AEH80UM32YY(b), AEH80UM38YY(b), AEH80UM39YY(b), AEH80UM40YY(34YY)*(b)

HUP80-45

Switching Power Supply Unit, Model(s) AFM120PS12, AFM120PS12C6, AFM120PS135, AFM120PS135C6, AFM120PS138, AFM120PS138C6, AFM120PS15, AFM120PS15C6, AFM120PS16, AFM120PS16C6, AFM120PS17, AFM120PS17C6, AFM120PS18, AFM120PS18C6, AFM120PS19, AFM120PS19C6, AFM120PS20, AFM120PS20C6, AFM120PS22, AFM120PS22C6, AFM120PS24, AFM120PS24C6, AFM120PS26, AFM120PS26C6, AFM120PS28, AFM120PS28C6, AFM120PS295, AFM120PS295C6, AFM120PS30, AFM120PS30C6, AFM120PS33, AFM120PS33C6, AFM120PS36, AFM120PS36C6, AFM120PS48, AFM120PS48C6, AFM30US09, AFM30US09C2, AFM30US09C6, AFM30US10, AFM30US10C2, AFM30US10C6, AFM30US11, AFM30US11C2, AFM30US11C6, AFM30US12, AFM30US12C2, AFM30US12C6, AFM30US13, AFM30US13C2, AFM30US13C6, AFM30US14, AFM30US14C2, AFM30US14C6, AFM30US15, AFM30US15C2, AFM30US15C6, AFM30US16, AFM30US16C2, AFM30US16C6, AFM30US17, AFM30US17C2, AFM30US17C6, AFM30US18, AFM30US18C2, AFM30US18C6, AFM30US19, AFM30US19C2, AFM30US19C6, AFM30US20, AFM30US20C2, AFM30US20C6, AFM30US21, AFM30US21C2, AFM30US21C6, AFM30US22, AFM30US22C2, AFM30US22C6, AFM30US23, AFM30US23C2, AFM30US23C6, AFM30US24, AFM30US24C2, AFM30US24C6, AFM45US09, AFM45US09C2, AFM45US09C6, AFM45US10, AFM45US10C2, AFM45US10C6, AFM45US11, AFM45US11C2, AFM45US11C6, AFM45US12, AFM45US12C2, AFM45US12C6, AFM45US13, AFM45US13C2, AFM45US13C6, AFM45US14, AFM45US14C2, AFM45US14C6, AFM45US15, AFM45US15C2, AFM45US15C6, AFM45US16, AFM45US16C2, AFM45US16C6, AFM45US17, AFM45US17C2, AFM45US17C6, AFM45US18, AFM45US18C2, AFM45US18C6, AFM45US19, AFM45US19C2, AFM45US19C6, AFM45US20, AFM45US20C2, AFM45US20C6, AFM45US21, AFM45US21C2, AFM45US21C6, AFM45US22, AFM45US22C2, AFM45US22C6, AFM45US23, AFM45US23C2, AFM45US23C6, AFM45US24, AFM45US24C2, AFM45US24C6, AFM60US09, AFM60US09C2, AFM60US09C6, AFM60US10, AFM60US10C2, AFM60US10C6, AFM60US11, AFM60US11C2, AFM60US11C6, AFM60US12, AFM60US12C2, AFM60US12C6, AFM60US13, AFM60US13C2, AFM60US13C6, AFM60US14, AFM60US14C2, AFM60US14C6, AFM60US15, AFM60US15C2, AFM60US15C6, AFM60US16, AFM60US16C2, AFM60US16C6, AFM60US17, AFM60US17C2, AFM60US17C6, AFM60US18, AFM60US18C2, AFM60US18C6, AFM60US19, AFM60US19C2, AFM60US19C6, AFM60US20, AFM60US20C2, AFM60US20C6, AFM60US21, AFM60US21C2, AFM60US21C6, AFM60US22, AFM60US22C2, AFM60US22C6, AFM60US23, AFM60US23C2, AFM60US23C6, AFM60US24, AFM60US24C2, AFM60US24C6, AFM60US25, AFM60US25C2, AFM60US25C6, AFM60US26, AFM60US26C2, AFM60US26C6, AFM60US27, AFM60US27C2, AFM60US27C6, VEP15US03-XXXXXXX (X), VEP15US033-XXXXXXX (X), VEP15US036-XXXXXXX (X), VEP15US04-XXXXXXX (X), VEP15US042-XXXXXXX (X), VEP15US045-XXXXXXX (X), VEP15US05-XXXXXXX (X), VEP15US052-XXXXXXX (X), VEP15US055-XXXXXXX (X), VEP15US059-XXXXXXX (X), VEP15US06-XXXXXXX (X), VEP15US065-XXXXXXX (X), VEP15US07-XXXXXXX (X), VEP15US075-XXXXXXX (X), VEP15US08-XXXXXXX (X), VEP15US085-XXXXXXX (X), VEP15US09-XXXXXXX (X), VEP15US10-XXXXXXX (X), VEP15US105-XXXXXXX (X), VEP15US12-XXXXXXX (X), VEP15US138-XXXXXXX (X), VEP15US15-XXXXXXX (X), VEP15US16-XXXXXXX (X), VEP15US175-XXXXXXX (X), VEP15US18-XXXXXXX (X), VEP15US19-XXXXXXX (X)

Switching Power Supply Unit(s), Model(s) VEP15US20-XXXXXXX (X), VEP15US22-XXXXXXX (X), VEP15US23-XXXXXXX (X), VEP15US24-XXXXXXX (X)

Switching power supply units, Model(s) AFM120PS12, AFM120PS12C6, AFM120PS135, AFM120PS135C6, AFM120PS138, AFM120PS138C6, AFM120PS15, AFM120PS15C6, AFM120PS16, AFM120PS16C6, AFM120PS17, AFM120PS17C6, AFM120PS18, AFM120PS18C6, AFM120PS19, AFM120PS19C6, AFM120PS20, AFM120PS20C6, AFM120PS22C6, AFM120PS28, AFM120PS28C6, AFM120PS295, AFM120PS295C6, AFM120PS30, AFM120PS30C6, AFM120PS33, AFM120PS33C6, AFM120PS36, AFM120PS36C6, AFM120PS48, AFM120PS48C6

! - (X=0-9,A-Z,"-",or blank)

(!) - where yyyy=0005-0090, indicates rated output current range 50-900mA

(\$ - Z=05-50, XY=blank, 0-9 or A-Z

(%) - refers to where z=0-9, A-Z, hyphen or blank. z: For marketing purposes

(&&) - &&=F, J, K, L, N, Q, R, M

(&) - Where y maybe C6 or blank; where Z maybe 0-9, A-Z or blank for marketing purposes.

(-) - Where X= blank, 0-9 or A-Z and Y= blank, 0-9 or A-Z

(a) - Where x maybe 12, 15, 19, 24, 27 or 48; where y maybe A-Z, 0-9, hyphen or blank.

(b) - Where YY maybe any alphanumeric character or blank.

(c) - Where XX maybe any alphanumeric character or blank.

(d) - Where x and y maybe any alphanumeric character or blank.

(e) - Where X maybe A, B, C or D to indicate equipment Class I for A and C series or Class II for B and D series.

(f1) - Where X maybe 0-9, A-Z or blank; where Y maybe 0-9, A-Z or blank.

(f2) - (Where X= blank, 0-9 or A-Z and Y= blank, 0-9 or A-Z)

(f3) - where z can be 03 to 48; X and Y can be blank, 0-9 or A-Z.

(h) - Followed by any alpha-numeric character; may be followed by S

(i) - ZZ may be any alpha-numeric character or blank; S may be S or blank

(j) - Y may be A-Z, 0-9, or blank; Z may be S or blank

(k) - X will be 2, 3, 3-1, 4, 6, 7, 8; Y may be A-Z, 0-9, or blank; Z may be S or blank

(n) - Where X = 105, 106, 107, 108, 109, 110, or 111.

(p) - Where xxx = 050-075

(w) - X can be blank, 0-9 or A-Z; Y can be blank, 0-9 or A-Z.

(X) - Where (X) maybe any alphanumeric character or a blank.

(^) - refers to where z = 0-9, A-Z, or blank, z: For marketing purposes

1 - (xxx=090-240; yyyy=0005-0500; m=B, W, G, L; n=A-Z or 0-9)

2 - (xxx=090-240; yyyy=0005-0500; m=B, W, G, L; n=A-Z or 0-9)

@ - Z= 05, 06, 11-16, 21-33, 40-48; X, Y=0-9, A-Z or blank

a - Where X=1 stands for Class II products, X=2,3 stands for Class I products

x & y - Where x and y maybe 0-9, A-Z or blank to indicate alternative output connectors.

x&y - Where x and y maybe 0-9, A-Z or blank.

XXX - 3 digits of numbers from 030 to 120 represents the output voltage from DC 3 V to 12 V.

YYY - 3 digits of numbers from 001 to 090 represents the output current from 0.01 A to 0.90 A.

yyyy - 0005 - 0250 indicates rated output current range 50 - 2500mA

z - Where z maybe 03 to 48; where X and Y maybe 0-9, A - Z or blank.

Last Updated on 2016-03-28

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2016 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2016 UL LLC".