

PCB Mount

0.25W to 1W	2W	3W	4W to 5W	6W	8W to 9W	10W to 12W	15W	20W to 25W	30W	40W to 60W	75W to 750W
IK  • 0.25 Watt • ±10% Input • Unregulated • SIP4 & DIP8 Packages • 1kV Isolation, 3kV Option	IL  • ±10% Input • Unregulated • SIP4 Package • 1kV Isolation • 3kV Isolation Option	ITR03  • ±10% Input • Unregulated • SIP4 Package • 3kV Isolation • 85°C Operating Temp	JCA04  • 2:1 Input • 25.4 x 20.3mm DIP24 • 1.5kV Basic Isolation • ITE Safety Approvals • Single & Dual Outputs	ITX  • 2:1 Input • SIP8 Package • 1.5kV Isolation, 3kV Option • ITE Safety Approvals • Single & Dual Outputs	JSE08  • 2:1 Input • DIP16 Package • 1.5kV Isolation • ITE Safety Approvals • Single & Dual Outputs	JCA10  • 2:1 Input • 25.4 x 20.3mm DIP24 • 1.5kV Basic Isolation • UL & TUV Approved • Single & Dual Outputs	JCM15  • 2:1 Input • 25.4 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JCM20  • 2:1 Input • 25.4 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JCM30  • 2:1 Input • 25.4 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JCK40  • 2:1 Input • 50.8 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	QSB75-350  • 2:1 & 4:1 Input • ¼ & ½ Brick Packages • 1.5kV Isolation • Remote On/Off • Remote Sense
IE  • ±10% Input • Unregulated • SIP4 & DIP8 Packages • 1kV Isolation, 3kV Option • Single Outputs	 IHL02  • ±10% Input • Unregulated • SIP7 Package • 5.2kV Isolation • Single & Dual Outputs	IR  • ±10% Input • Semi-regulated • SIP7 Package • 1kV Isolation, 3kV Option • Single & Dual Outputs	JCD04  • 2:1 Input • DIP24 Package • 1.6kV Isolation, 3.5kV Option • ITE Safety Approvals • Single & Dual Outputs	JCA06  • 2:1 Input • 25.4 x 20.3mm DIP24 • 1.5kV Basic Isolation • ITE Safety Approvals • Single & Dual Outputs	JCJ08  • 2:1 Input • DIP24 Package • 1.5kV Isolation • ITE Safety Approvals • Single & Dual Outputs	JSM10  • 2:1 Input • 25.4 x 25.4mm Package • 1.5kV Isolation • Heatsink Option • Single & Dual Outputs	JCG15  • 2:1 Input • DIP24 Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JCK20  • 2:1 Input • 50.8 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JCK30  • 2:1 Input • 50.8 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	 BCT40  • 4:1 Input • 25.4 x 25.4mm Package • 2.25kV Isolation • Remote On/Off • Single & Dual Outputs	QSC150  • 4:1 Input • ¼ Brick Package • 2.25kV Isolation • Remote On/Off • Remote Sense
 SCT01  • ±10 Input • Unregulated • SIP4 Package • 1kV Isolation, 2kV Option • Single Outputs	IH  • ±10% Input • Unregulated • SIP7 & DIP14 Package • Up to 6kV Isolation • Dual Outputs	IZ  • 2:1 Input • Regulated • SIP8 Package • 1.6kV Isolation, 3kV Option • Single & Dual Outputs	JTC04  • 4:1 Input • DIP24 Package • 1.5kV Isolation, 3.5kV Option • Short Circuit Protection • Single & Dual Outputs	JCE06  • 2:1 Input • DIP24 Package • 1.5kV Isolation, 3kV Option • ITE Safety Approvals • Single & Dual Outputs	JWE08  • 4:1 Input • DIP16 Package • 1.5kV Isolation • ITE Safety Approvals • Single & Dual Outputs	JCJ10  • 2:1 Input • DIP24 Package • 1.5kV Isolation • Short Circuit Protection • Single & Dual Outputs	JCK15  • 2:1 Input • 50.8 x 25.4mm Package • 1.6kV Isolation, 3.5kV Option • Short Circuit Protection • Single & Dual Outputs	JTK20  • 4:1 Input • 25.4 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JTK30  • 4:1 Input • 25.4 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JWL40  • 4:1 Input • 50.8 x 25.4mm Package • 1.5kV Isolation • Heatsink Option • Single & Dual Outputs	QSB400  • 4:1 Input • Full Brick Package • 1.5kV Isolation • Remote On/Off • Remote Sense
IA/ITA  • ±10% Input • Unregulated SIP7 • High Operating Temperature • 1kV & 1.5kV Isolation • Dual Outputs	IU  • 2:1 Input • Regulated • SIP8 & DIP16 Package • 1kV Isolation, 3kV Option • Single & Dual Outputs	JCA03  • 2:1 Input • Regulated • 25.4 x 20.3mm DIP24 • 1.5kV Basic Isolation • Single & Dual Outputs	IEQ05  • 4:1 Input • SIP8 Package • 1.5kV Isolation • Remote On/Off • Single & Dual Outputs	JCD06  • 2:1 Input • DIP24 Package • 1.6kV Isolation, 3.5kV Option • ITE Safety Approvals • Single & Dual Outputs	JTF08  • 4:1 Input • DIP24 Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JTR10  • 4:1 Input • DIP16 Package • 1.5kV Isolation • ITE Safety Approvals • Single & Dual Outputs	JTK15  • 4:1 Input • 25.4 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JTD20  • 4:1 Input • 40.6 x 25.4mm Package • 3kV Isolation • Remote On/Off • Single & Dual Outputs	JTL30  • 4:1 Input • 50.8 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single, Dual & Triple O/P	JTL40  • 4:1 Input • 50.8 x 50.8mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	QSB600  • 2:1 Input • Full Brick Package • 1.5kV Isolation • Remote On/Off • Remote Sense
 SDT01  • ±10 Input • Unregulated • SIP7 Package • 1.5kVDC Isolation • Single & Dual Outputs	IEU02  • 2:1 Input • Regulated • DIP8 Package • 1.5kV Isolation • Single & Dual Outputs	JCE03  • 2:1 Input • Regulated • DIP24 Package • 1.5kV Isolation, 3kV Option • Single & Dual Outputs	JCD05  • 2:1 Input • DIP24 Package • 1.6kV Isolation, 3.5kV Option • ITE Safety Approvals • Single & Dual Outputs	ITQ  • 4:1 Input • SIP8 Package • 1.5kV Isolation, 3kV Option • ITE Safety Approvals • Single & Dual Outputs	ICZ09  • 2:1 Input • SIP8 Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JWK10  • 4:1 Input • 25.4 x 25.4mm Package • 1.5kV Isolation • Heatsink Option • Single & Dual Outputs	JTF15  • 4:1 Input • DIP24 Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JSM25  • 2:1 Input • 25.4 x 25.4mm Package • 1.5kV Isolation • Heatsink Option • Single & Dual Outputs		JCK50  • 2:1 Input • 50.8 x 25.4mm Package • 1.6kV Isolation • Heatsink Option • Remote On/Off	QHL75  • 180 - 450VDC Input • ¼ Brick Package • 3kVAC Isolation • Remote On/Off • Remote Sense
 IHA01  • ±10% Input • Unregulated • SIP7 Package • 6kV Isolation • Single & Dual Outputs	JCA02  • 2:1 Input • Regulated • 25.4 x 20.3mm DIP24 • 1.5kV Basic Isolation • Single & Dual Outputs	 SFT03  • 2:1 & 4:1 Input • Regulated • SIP8 Package • 2kVDC Isolation • Single & Dual Outputs		JWE06  • 4:1 Input • DIP16 Package • 1.5kV Isolation • ITE Safety Approvals • Single & Dual Outputs	ITZ  • 4:1 Input • SIP8 Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JTF10/12  • 4:1 Input • DIP24 Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	JTD15  • 4:1 Input • 40.6 x 25.4mm Package • 3kV Isolation • Remote On/Off • Single & Dual Outputs	JWK25  • 4:1 Input • 25.4 x 25.4mm Package • 1.5kV Isolation • Heatsink Option • Single & Dual Outputs		JWL50  • 4:1 Input • 50.8 x 25.4mm Package • 1.5kV Isolation • Heatsink Option • Remote On/Off	QHL150/300  • 180 - 425VDC Input • ¼ & ½ Brick Packages • 3kVAC Isolation • Remote On/Off • Remote Sense
ITV/IV  • ±10% Input • Unregulated • SIP7 & DIP14 Packages • Up to 6kV Isolation • Single & Dual Outputs	IM  • 4:1 Input • Regulated • SIP9 Package • 1.5kV Isolation • Single & Dual Outputs	ITP03  • 4:1 Input • Regulated • SIP6 Package • 1.6kV Isolation • Single & Dual Outputs		JTE06  • 4:1 Input • DIP24 Package • 1.5kV Isolation, 3kV Option • ITE Safety Approvals • Single & Dual Outputs		JCG12  • 2:1 Input • DIP24 Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs				JCK60  • 2:1 Input • 50.8 x 50.8mm Package • 1.6kV Isolation • Short Circuit Protection • Remote On/Off	QHL600  • 180 - 425VDC Input • Full Brick Package • 3kVAC Isolation • Remote On/Off • Current Share
IF  • ±10% Input • Regulated • SIP7 & DIP14 Package • 1kV Isolation • 3kV Isolation Option		ITU03  • 4:1 Input • Regulated • DIP8 Package • 1.6kV Isolation • Single & Dual Outputs								JTL60  • 4:1 Input • 50.8 x 25.4mm Package • 1.6kV Isolation • Remote On/Off • Single & Dual Outputs	QHL750  • 200 - 425VDC Input • Full Brick Package • 3kVAC Isolation • Remote On/Off • Current Share
ITW/IW  • 2:1 Input • Regulated • SIP & DIP Package • Up to 3kV Isolation • Single & Dual Outputs		JTE03  • 4:1 Input • Regulated • DIP24 Package • 1.5kV Isolation, 3kV Option • Single & Dual Outputs									

 Recently introduced

 MOSFET & IGBT applications

For full specifications visit: www.xnpower.com

2025

SMD

1W	2W to 6W
PBT01  ±10% Input - Unregulated - SMD8/10 DIP Package 1kV Isolation, 2kV, 3kV Options - Single & Dual Outputs	PBT02  ±10% Input - Unregulated - SMD8/10 DIP Package 1kV Isolation, 3kV Option - Single & Dual Outputs
ISM01  ±10% Input - Unregulated - SMD14 Package 4kVAC Isolation 2 x MOPP at 250VAC	ISM02  ±10% Input - Unregulated - SMD16 Package 4kVAC Isolation 1 x MOPP at 300VAC
ISB01  2:1 Input - Regulated - SMD14 Package 1.5kV Isolation - Single & Dual Outputs	ISU02  4:1 Input - Regulated - SMD14 Package 1.5kV Isolation - Single & Dual Outputs
	ISU03  4:1 Input - Regulated - SMD14 Package 1.5kV Isolation - Single & Dual Outputs
ISC03  4:1 Input - Regulated - SMD16 Package 1.5kV Isolation - Single & Dual Outputs	
ISX06  4:1 Input - Regulated - SMD16 Package 1.5kV Isolation - Single & Dual Outputs	

Medical

1W to 2W	3W to 6W	10W to 30W
ISM01  ±10% Input - Unregulated - SMD14 Package 4kVAC Isolation 2 x MOPP at 250VAC	JHL03  4:1 Input Range 10 - 17VDC Input 20 - 30VDC Input - DIP24 Package 4kVAC Isolation 2 x MOPP at 250VAC	JHM10  2:1 Input - Regulated - DIP24 Package 4kVAC Isolation 2 x MOPP at 250VAC
IMA01  ±10% Input - Unregulated - SIP7 Package 4kVAC Isolation 1 x MOPP at 250VAC	JMR03  4:1 Input Range - Regulated - DIP16 Package 5kVAC Isolation 2 x MOPP at 250VAC	JMR10  4:1 Input - Regulated - DIP24 Package 5kVAC Isolation 2 x MOPP at 250VAC
IMB01  ±10% Input - Unregulated - SIP7 Package 4kVAC Isolation 2 x MOPP at 300VAC	IMM05  2:1 Input - Regulated - SIP9 Package 1.5kVAC Isolation 1 x MOPP at 250VAC	JHM15  2:1 Input - Regulated 40.6 x 25.4mm Package 4kVAC Isolation 2 x MOPP at 250VAC
IMM01  2:1 Input - Regulated - SIP7 Package 1.5kVAC Isolation 1 x MOPP at 250VAC	JHL06  10 - 17VDC Input 20 - 30VDC Input - DIP24 Package 4kVAC Isolation 2 x MOPP at 250VAC	JHM20  2:1 Input - Regulated 50.8 x 25.4mm Package 4kVAC Isolation 2 x MOPP at 250VAC
ISM02  ±10% Input - Unregulated - SMD16 Package 4kVAC Isolation 1 x MOPP at 300VAC	JHM06  2:1 Input - Regulated - DIP24 Package 4kVAC Isolation 2 x MOPP at 250VAC	JMR20  4:1 Input - Regulated 40.6 x 25.4 x 10.2mm 5kVAC Isolation 2 x MOPP at 250VAC
IML02  ±10% Input - Unregulated - SIP7 Package 4kVAC Isolation 1 x MOPP at 300VAC		JHM30  2:1 Input - Regulated 50.8 x 25.4 x 10.2mm 4kVAC Isolation 2 x MOPP at 250VAC
IMM02  2:1 Input - Regulated - SIP8 Package 1.5kVAC Isolation 1 x MOPP at 250VAC		

Non-Isolated Switching Regulators

0.5 Amps	1 to 2 Amps
STH05  0.5A Regulator - Input Range up to 72VDC - Low Profile - SMD10 Package ±10% Output Trim	STS10  1.0A Regulator - Input Range up to 36VDC - Low Profile - SMD10 Package ±10% Output Trim
RBT05  0.5A Regulator - Input Range up to 36VDC - SIP3 package 78 Series pin compatible - Short Circuit Protection	RBT10  1.0A Regulator - Input Range up to 36VDC - SIP3 package 78 Series pin compatible - Short Circuit Protection
SRH05  0.5A Regulator - Input Range up to 72VDC - SIP3 package 78 Series pin compatible - Short Circuit Protection	RBT20  2.0A Regulator - Input Range up to 36VDC - SIP3 package 78 Series pin compatible - Short Circuit Protection

Chassis/DIN Rail Mount

6W to 20W	30W to 60W
DTE06  4:1 Input - DIN Rail Option 3kVDC Isolation - Remote On/Off - Single & Dual Outputs	DDC30  4:1 Input - Low Profile Design 1.5kVDC Isolation - ITE Safety Approvals - UL508 Approved
DTE10  4:1 Input - DIN Rail Option 3kVDC Isolation - Remote On/Off - Single & Dual Outputs	DDC40  3:1 Input - Low Profile Design 1.5kVDC Isolation - ITE Safety Approvals - UL508 Approved
DTJ15  4:1 Input 3kVDC Isolation - ITE Safety Approvals ±10% Output Trim - Single & Dual Outputs	DTE40  4:1 Input - DIN Rail Option 2.5kVDC Isolation - Remote On/Off - ITE Safety Approvals
DDC15  4:1 Input - Low Profile Design 1.5kVDC Isolation - ITE Safety Approvals - UL508 Approved	DTE60  4:1 Input - DIN Rail Option 2.5kVDC Isolation - Remote On/Off - ITE Safety Approvals
DTJ20  4:1 Input 3kVDC Isolation - ITE Safety Approvals ±10% Output Trim - Single & Dual Outputs	
DTE20  4:1 Input - DIN Rail Option 2.5kVDC Isolation - Remote On/Off - ITE Safety Approvals	

Railway & Renewable Energy

3W to 50W	75W to 600W
RDE03  4:1, 9 - 36VDC Input 4:1, 18 - 75VDC Input 4:1, 40 - 160VDC Input - EN50155 Compliant - Single & Dual Outputs	RCQ75  2:1, 43 - 101VDC Input 3:1, 66 - 160VDC Input ¾ Brick Package - EN50155 Compliant - Remote On/Off
RDD08  5:1, 13 - 70VDC Input 4:1, 42 - 176VDC Input - DIP24 Package - EN50155 Compliant - Single & Dual Outputs	RDE75  8:1, 9 - 75VDC Input ¾ Brick Package - EN50155 Compliant - Remote On/Off - Remote Sense
RDE20  5:1, 13 - 70VDC Input 4:1, 42 - 176VDC Input 25.4 x 25.4mm Package - EN50155 Compliant - Single & Dual Outputs	RDF150  12:1, 14 - 160VDC ¾ Brick Package 3kVAC Isolation - EN50155 Compliant - Remote On/Off
RDF25  10:1, 16 - 160VDC 50.8 x 25.4mm Package 3kVDC Isolation - EN50155 Compliant - Remote On/Off	RDQ150  3:1, 66 - 160VDC Input ¾ Brick Package - EN50155 Compliant - Remote On/Off - Remote Sense
RDF50  12:1, 14 - 160VDC Input ¾ Brick Package 3kVDC Isolation - EN50155 Compliant - Baseplate-cooled	QSC150  4:1, 9 - 36VDC Input 4:1, 18 - 75VDC Input 4:1, 43 - 160VDC Input ¾ Brick Package - EN50155 Compliant
	RDF200  12:1, 16 - 160VDC ¾ Brick Package 3kVAC Isolation - EN50155 Compliant - Remote On/Off
	RDH300/600  4:1, 43 - 160VDC Input ¾ & Full Brick Packages - EN50155 Compliant - Remote On/Off - Remote Sense