

Wall Mount Adapters

Desktop

5W to 10W	12W	18W	24W	36W to 100W	36W to 60W	65W to 70W	85W to 100W	120W to 160W	200W	250W	300W to 450W
 VFR05 • 5W • 55.1 x 37.0 x 42.9mm • Level VI & CoC Tier 2 • LPS approved • Changeable input plugs	 ACM12 • 12W • 76.0 x 30.3 x 48.2mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case	 AMF18 • 18W • 90.5 x 33.5 x 58.5mm • Home healthcare approval • 2 x MOPP • Optional white case	 AMF24 • 24W • 90.5 x 33.5 x 58.5mm • Home healthcare approval • 2 x MOPP • Optional white case	 AMF36 • 36W • 90.5 x 33.5 x 58.5mm • Home healthcare approval • 2 x MOPP • Optional white case	 AKM36 • 36W • 108.0 x 50.0 x 33.8mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case	 AKM65 • 65W • 125.0 x 62.3 x 34.0mm • Home healthcare approval • 2 x MOPP • Optional white case	 ALM85 • 85W • 116.3 x 52.4 x 31.3mm • Level VI & CoC Tier 2 • 2 x MOPP • IP32 rating	 ALM120 • 120W • 140.0 x 71.0 x 22.0mm • Level VI & CoC Tier 2 • CCC qualified • 2 x MOPP	 AQM200 • 200W • 166.5 x 54.2 x 33.0mm • Home healthcare approval • IP22 rating • Class I & II	 AQM250 • 250W • 173.0 x 67.0 x 32.0mm • Home healthcare approval • IP22 rating • Class I & II	 AQM300 • 300W • 183.0 x 85.0 x 35.0mm • Home healthcare approval • IP22 rating • Class I & II
 VFL05 • 5W • 55.1 x 24.1 x 35.5mm • Level VI & CoC Tier 2 • LPS approved • Low cost	 VEL12 • 12W • 76.0 x 29.5 x 39.4mm • Level VI & CoC Tier 2 • LPS approved • Low cost	 ACM18 • 18W • 88.0 x 30.0 x 49.5mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case	 ACM24 • 24W • 88.0 x 30.0 x 57.0mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case	 ACM36 • 36W • 96.7 x 33.0 x 59.5mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case	 AEK40 • 40W • 107.0 x 47.0 x 30.1mm • Level VI & CoC Tier 2 • 5V to 48V outputs • Class I	 ALM65 • 65W • 116.3 x 52.4 x 31.3mm • Level VI • 2 x MOPP • Class I & II	 VES90 • 90W • 139.0 x 58.0 x 31.0mm • Level VI & CoC Tier 2 • CCC qualified • Low cost	 VES120 • 120W • 168.0 x 71.0 x 37.5mm • Level VI & CoC Tier 2 • CCC qualified • Low cost	 ALM200 • 200W • 209.0 x 82.0 x 43.0mm • Home healthcare approval • IP32 rating • Class I & II	 AHM250 • 250W • 223.0 x 88.5 x 38.6mm • Level V • IP22 rating • Low profile	 VES300 • 300W • 197.4 x 88.9 x 39.0mm • Level VI & CoC Tier 2 • CCC qualified • Low cost
 ACM06 • 6W • 73.5 x 30.7 x 42.5mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case	 VER12 • 12W • 76.5 x 41.0 x 37.6mm • Level VI & CoC Tier 2 • LPS approved • Changeable input plugs	 VEL18 • 18W • 90.0 x 34.0 x 47.5mm • Level VI & CoC Tier 2 • LPS approved • Low cost	 VEL24 • 24W • 90.0 x 34.0 x 47.5mm • Level VI & CoC Tier 2 • LPS approved • Low cost	 VEL36 • 36W • 94.0 x 35.0 x 46.6mm • Level VI & CoC Tier 2 • LPS approved • Low cost	 VEC40 • 40W • 116.3 x 52.4 x 31.3mm • Level VI & CoC Tier 2 • CCC qualified • LPS approved	 VEC65 • 65W • 116.3 x 52.4 x 31.3mm • Level VI & CoC Tier 2 • CCC qualified • LPS approved	 AKM90 • 90W • 125.0 x 62.3 x 34.0mm • CoC Tier 2, EU2019/1782 • 2 x MOPP • Class I & II	 PGD140 • 140W • 121.0 x 65.8 x 32.0mm • Power Delivery protocol • Home healthcare approval • IP22 rating			 AQM450 • 450W • 254 x 116 x 47mm • Medical 2x MOPP • IP22 rating • Class I
 VEU10 • 2.1A USB A socket • 50.8 x 37.0 x 22.0mm • Level VI & CoC Tier 2 • Low cost • Class II			 VER24 • 24W • 90.5 x 42.0 x 42.7mm • Level VI & CoC Tier 2 • LPS approved • Changeable input plugs	 VER36 • 36W • 94.5 x 47.0 x 43.9mm • Level VI & CoC Tier 2 • LPS approved • Low cost	 AKM45 • 45W • 122.4 x 51.4 x 31.5mm • Home healthcare approval • 2 x MOPP • Optional white case	 AEJ70 • 70W • 120.0 x 52.0 x 31.0mm • Level VI & CoC Tier 2 • 65°C operation • Class I	 AJM90 • 90W • 140.0 x 71.0 x 22.0mm • Level VI • Slim profile • Class II	 ALM150 • 150W • 186.0 x 72.0 x 38.0mm • Home healthcare approval • IP32 rating • Class I & II			
			 PGW65 • 65W • 90.5 x 58.5 x 33.5mm • Power Delivery protocol • Home healthcare approval • IP22 rating	 VEC50 • 50W • 116.3 x 52.4 x 31.3mm • Level VI & CoC Tier 2 • CCC Qualified • LPS approved		 PGD100 • 100W • 114.5 x 56.5 x 32.0mm • Power Delivery protocol • Home healthcare approval • IP22 rating	 AEJ160 • 160W • 150.0 x 70.0 x 38.0mm • Level VI & CoC Tier 2 • 65°C operation • Active PFC				
			 PGW100 • 100W • 97.0 x 57.0 x 34.0mm • Power Delivery protocol • Home healthcare approval • IP22 rating	 AEK60 • 60W • 118.0 x 47.0 x 30.1mm • Level VI & CoC Tier 2 • <0.15W standby power • Class I		 AEJ100 • 100W • 141.0 x 58.0 x 39.5mm • Level VI & CoC Tier 2 • 65°C operation • Active PFC					