

CERTIFICATE OF COMPLIANCE

Certificate Number E317867
Report Reference E317867-20200828
Issue Date 2020-December-02

Issued to: XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN, CA 92780 USA

**This certificate confirms that
representative samples of**

Power Supplies for Use with Audio/Video, Information and
Communication Technology Equipment
See Addendum Page

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety:

UL 62368-1 and CAN/CSA C22.2 No. 62368-1-14 -
Audio/video, information and communication technology
equipment Part 1: Safety requirements


Additional Information:

See the UL Online Certifications Directory at
<https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Mark. Only the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number E317867
Report Reference E317867-20200828
Issue Date 2020-December-02

VEL30US090-US-JA, VEL30US091-US-JA, VEL30US092-US-JA, VEL30US093-US-JA, VEL30US094-US-JA, VEL30US095-US-JA, VEL30US096-US-JA, VEL30US097-US-JA, VEL30US098-US-JA, VEL30US099-US-JA, VEL30US100-US-JA, VEL30US101-US-JA, VEL30US102-US-JA, VEL30US103-US-JA, VEL30US104-US-JA, VEL30US105-US-JA, VEL30US106-US-JA, VEL30US107-US-JA, VEL30US108-US-JA, VEL30US109-US-JA, VEL30US110-US-JA, VEL30US111-US-JA, VEL30US112-US-JA, VEL30US113-US-JA, VEL30US114-US-JA, VEL30US115-US-JA, VEL30US116-US-JA, VEL30US117-US-JA, VEL30US118-US-JA, VEL30US119-US-JA, VEL30US120-US-JA, VEL30US121-US-JA, VEL30US122-US-JA, VEL30US123-US-JA, VEL30US124-US-JA, VEL30US125-US-JA, VEL30US126-US-JA, VEL30US127-US-JA, VEL30US128-US-JA, VEL30US129-US-JA, VEL30US130-US-JA, VEL30US131-US-JA, VEL30US132-US-JA, VEL30US133-US-JA, VEL30US134-US-JA, VEL30US135-US-JA, VEL30US136-US-JA, VEL30US137-US-JA, VEL30US138-US-JA, VEL30US139-US-JA, VEL30US140-US-JA, VEL30US141-US-JA, VEL30US142-US-JA, VEL30US143-US-JA, VEL30US144-US-JA, VEL30US145-US-JA, VEL30US146-US-JA, VEL30US147-US-JA, VEL30US148-US-JA, VEL30US149-US-JA, VEL30US150-US-JA, VEL30US180-US-JA, VEL30US181-US-JA, VEL30US182-US-JA, VEL30US183-US-JA, VEL30US184-US-JA, VEL30US185-US-JA, VEL30US186-US-JA, VEL30US187-US-JA, VEL30US188-US-JA, VEL30US189-US-JA, VEL30US190-US-JA, VEL30US191-US-JA, VEL30US192-US-JA, VEL30US193-US-JA, VEL30US194-US-JA, VEL30US195-US-JA, VEL30U2170-US-JA, VEL30US196-US-JA, VEL30US197-US-JA, VEL30US198-US-JA, VEL30US199-US-JA, VEL30US200-US-JA, VEL30US201-US-JA, VEL30US202-US-JA, VEL30US203-US-JA, VEL30US204-US-JA, VEL30US205-US-JA, VEL30US206-US-JA, VEL30US207-US-JA, VEL30US208-US-JA, VEL30US209-US-JA, VEL30US210-US-JA, VEL30US211-US-JA, VEL30US212-US-JA, VEL30US213-US-JA, VEL30US214-US-JA, VEL30US215-US-JA, VEL30US216-US-JA, VEL30US218-US-JA, VEL30US219-US-JA, VEL30US220-US-JA, VEL30US221-US-JA, VEL30US222-US-JA, VEL30US223-US-JA, VEL30US224-US-JA, VEL30US225-US-JA, VEL30US226-US-JA, VEL30US227-US-JA, VEL30US228-US-JA, VEL30US229-US-JA, VEL30US230-US-JA, VEL30US231-US-JA, VEL30US232-US-JA, VEL30US233-US-JA, VEL30US234-US-JA, VEL30US235-US-JA, VEL30US236-US-JA, VEL30US237-US-JA, VEL30US238-US-JA, VEL30US239-US-JA, VEL30US240-US-JA, VEL30US090-US-JA-H, VEL30US091-US-JA-H, VEL30US092-US-JA-H, VEL30US093-US-JA-H, VEL30US094-US-JA-H, VEL30US095-US-JA-H, VEL30US096-US-JA-H, VEL30US097-US-JA-H, VEL30US098-US-JA-H, VEL30US099-US-JA-H, VEL30US100-US-JA-H, VEL30US101-US-JA-H, VEL30US102-US-JA-H, VEL30US103-US-JA-H, VEL30US104-US-JA-H, VEL30US105-US-JA-H, VEL30US106-US-JA-H, VEL30US107-US-JA-H, VEL30US108-US-JA-H, VEL30US109-US-JA-H, VEL30US110-US-JA-H, VEL30US111-US-JA-H, VEL30US112-US-JA-H, VEL30US113-US-JA-H, VEL30US114-US-JA-H, VEL30US115-US-JA-H, VEL30US116-US-JA-H, VEL30US117-US-JA-H, VEL30US118-US-JA-H, VEL30US119-US-JA-H, VEL30US120-US-JA-H, VEL30US121-US-JA-H, VEL30US122-US-JA-H, VEL30US123-US-JA-H, VEL30US124-US-JA-H, VEL30US125-US-JA-H, VEL30US126-US-JA-H, VEL30US127-US-JA-H, VEL30US128-US-JA-H, VEL30US129-US-JA-H, VEL30US130-US-JA-H, VEL30US131-US-JA-H, VEL30US132-US-JA-H, VEL30US133-US-JA-H, VEL30US134-US-JA-H, VEL30US135-US-JA-H, VEL30US136-US-JA-H, VEL30US137-US-JA-H, VEL30US138-US-JA-H, VEL30US139-US-JA-H, VEL30US140-US-JA-H,

B. Mahrenholz

Bruce Mahrenholz, Director North American Certification Program

UL LLC


Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number E317867
Report Reference E317867-20200828
Issue Date 2020-December-02

VEL30US141-US-JA-H, VEL30US142-US-JA-H, VEL30US143-US-JA-H, VEL30US144-US-JA-H,
VEL30US145-US-JA-H, VEL30US146-US-JA-H, VEL30US147-US-JA-H, VEL30US148-US-JA-H,
VEL30US149-US-JA-H, VEL30US150-US-JA-H, VEL30US180-US-JA-H, VEL30US181-US-JA-H,
VEL30US182-US-JA-H, VEL30US183-US-JA-H, VEL30US184-US-JA-H, VEL30US185-US-JA-H,
VEL30US186-US-JA-H, VEL30US187-US-JA-H, VEL30US188-US-JA-H, VEL30US189-US-JA-H,
VEL30US190-US-JA-H, VEL30US191-US-JA-H, VEL30US192-US-JA-H, VEL30US193-US-JA-H,
VEL30US194-US-JA-H, VEL30US195-US-JA-H, VEL30U2170-US-JA-H, VEL30US196-US-JA-H,
VEL30US197-US-JA-H, VEL30US198-US-JA-H, VEL30US199-US-JA-H, VEL30US200-US-JA-H,
VEL30US201-US-JA-H, VEL30US202-US-JA-H, VEL30US203-US-JA-H, VEL30US204-US-JA-H,
VEL30US205-US-JA-H, VEL30US206-US-JA-H, VEL30US207-US-JA-H, VEL30US208-US-JA-H,
VEL30US209-US-JA-H, VEL30US210-US-JA-H, VEL30US211-US-JA-H, VEL30US212-US-JA-H,
VEL30US213-US-JA-H, VEL30US214-US-JA-H, VEL30US215-US-JA-H, VEL30US216-US-JA-H,
VEL30US218-US-JA-H, VEL30US219-US-JA-H, VEL30US220-US-JA-H, VEL30US221-US-JA-H,
VEL30US222-US-JA-H, VEL30US223-US-JA-H, VEL30US224-US-JA-H, VEL30US225-US-JA-H,
VEL30US226-US-JA-H, VEL30US227-US-JA-H, VEL30US228-US-JA-H, VEL30US229-US-JA-H,
VEL30US230-US-JA-H, VEL30US231-US-JA-H, VEL30US232-US-JA-H, VEL30US233-US-JA-H,
VEL30US234-US-JA-H, VEL30US235-US-JA-H, VEL30US236-US-JA-H, VEL30US237-US-JA-H,
VEL30US238-US-JA-H, VEL30US239-US-JA-H, VEL30US240-US-JA-H, VER30US090-JA, VER30US091-JA,
VER30US092-JA, VER30US093-JA, VER30US094-JA, VER30US095-JA, VER30US096-JA, VER30US097-
JA, VER30US098-JA, VER30US099-JA, VER30US100-JA, VER30US101-JA, VER30US102-JA,
VER30US103-JA, VER30US104-JA, VER30US105-JA, VER30US106-JA, VER30US107-JA, VER30US108-
JA, VER30US109-JA, VER30US110-JA, VER30US111-JA, VER30US112-JA, VER30US113-JA,
VER30US114-JA, VER30US115-JA, VER30US116-JA, VER30US117-JA, VER30US118-JA, VER30US119-
JA, VER30US120-JA, VER30US121-JA, VER30US122-JA, VER30US123-JA, VER30US124-JA,
VER30US125-JA, VER30US126-JA, VER30US127-JA, VER30US128-JA, VER30US129-JA, VER30US130-
JA, VER30US131-JA, VER30US132-JA, VER30US133-JA, VER30US134-JA, VER30US135-JA,
VER30US136-JA, VER30US137-JA, VER30US138-JA, VER30US139-JA, VER30US140-JA, VER30US141-
JA, VER30US142-JA, VER30US143-JA, VER30US144-JA, VER30US145-JA, VER30US146-JA,
VER30US147-JA, VER30US148-JA, VER30US149-JA, VER30US150-JA, VER30US151-JA, VER30US152-
JA, VER30US153-JA, VER30US154-JA, VER30US155-JA, VER30US156-JA, VER30US157-JA,
VER30US158-JA, VER30US159-JA, VER30US160-JA, VER30US161-JA, VER30US162-JA, VER30US163-
JA, VER30US164-JA, VER30US165-JA, VER30US166-JA, VER30US167-JA, VER30US168-JA,
VER30US169-JA, VER30US170-JA, VER30US171-JA, VER30US172-JA, VER30US173-JA, VER30US174-
JA, VER30US175-JA, VER30US176-JA, VER30US177-JA, VER30US178-JA, VER30US179-JA,
VER30US180-JA, VER30US181-JA, VER30US182-JA, VER30US183-JA, VER30US184-JA, VER30US185-
JA, VER30US186-JA, VER30US187-JA, VER30US188-JA, VER30US189-JA, VER30US190-JA,



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number E317867
Report Reference E317867-20200828
Issue Date 2020-December-02

VER30US191-JA, VER30US192-JA, VER30US193-JA, VER30US194-JA, VER30US195-JA, VER30US196-JA, VER30US197-JA, VER30US198-JA, VER30US199-JA, VER30US200-JA, VER30US201-JA, VER30US202-JA, VER30US203-JA, VER30US204-JA, VER30US205-JA, VER30US206-JA, VER30US207-JA, VER30US208-JA, VER30US209-JA, VER30US210-JA, VER30US240-JA, VET30US090C2-JA, VET30US091C2-JA, VET30US092C2-JA, VET30US093C2-JA, VET30US094C2-JA, VET30US095C2-JA, VET30US096C2-JA, VET30US097C2-JA, VET30US098C2-JA, VET30US099C2-JA, VET30US100C2-JA, VET30US101C2-JA, VET30US102C2-JA, VET30US103C2-JA, VET30US104C2-JA, VET30US105C2-JA, VET30US106C2-JA, VET30US107C2-JA, VET30US108C2-JA, VET30US109C2-JA, VET30US110C2-JA, VET30US111C2-JA, VET30US112C2-JA, VET30US113C2-JA, VET30US114C2-JA, VET30US115C2-JA, VET30US116C2-JA, VET30US117C2-JA, VET30US118C2-JA, VET30US119C2-JA, VET30US120C2-JA, VET30US121C2-JA, VET30US122C2-JA, VET30US123C2-JA, VET30US124C2-JA, VET30US125C2-JA, VET30US126C2-JA, VET30US127C2-JA, VET30US128C2-JA, VET30US129C2-JA, VET30US130C2-JA, VET30US131C2-JA, VET30US132C2-JA, VET30US133C2-JA, VET30US134C2-JA, VET30US135C2-JA, VET30US136C2-JA, VET30US137C2-JA, VET30US138C2-JA, VET30US139C2-JA, VET30US140C2-JA, VET30US141C2-JA, VET30US142C2-JA, VET30US143C2-JA, VET30US144C2-JA, VET30US145C2-JA, VET30US146C2-JA, VET30US147C2-JA, VET30US148C2-JA, VET30US149C2-JA, VET30US150C2-JA, VET30US151C2-JA, VET30US152C2-JA, VET30US153C2-JA, VET30US154C2-JA, VET30US155C2-JA, VET30US156C2-JA, VET30US157C2-JA, VET30US158C2-JA, VET30US159C2-JA, VET30US160C2-JA, VET30US161C2-JA, VET30US162C2-JA, VET30US163C2-JA, VET30US164C2-JA, VET30US165C2-JA, VET30US166C2-JA, VET30US167C2-JA, VET30US168C2-JA, VET30US169C2-JA, VET30US170C2-JA, VET30US171C2-JA, VET30US172C2-JA, VET30US173C2-JA, VET30US174C2-JA, VET30US175C2-JA, VET30US176C2-JA, VET30US177C2-JA, VET30US178C2-JA, VET30US179C2-JA, VET30US180C2-JA, VET30US181C2-JA, VET30US182C2-JA, VET30US183C2-JA, VET30US184C2-JA, VET30US185C2-JA, VET30US186C2-JA, VET30US187C2-JA, VET30US188C2-JA, VET30US189C2-JA, VET30US190C2-JA, VET30US191C2-JA, VET30US192C2-JA, VET30US193C2-JA, VET30US194C2-JA, VET30US195C2-JA, VET30US196C2-JA, VET30US197C2-JA, VET30US198C2-JA, VET30US199C2-JA, VET30US200C2-JA, VET30US201C2-JA, VET30US202C2-JA, VET30US203C2-JA, VET30US204C2-JA, VET30US205C2-JA, VET30US206C2-JA, VET30US207C2-JA, VET30US208C2-JA, VET30US209C2-JA, VET30US210C2-JA, VET30US211C2-JA,

VEL36US120-US-JA, VEL36US121-US-JA, VEL36US122-US-JA, VEL36US123-US-JA, VEL36US124-US-JA, VEL36US125-US-JA, VEL36US126-US-JA, VEL36US127-US-JA, VEL36US128-US-JA, VEL36US129-US-JA, VEL36US130-US-JA, VEL36US131-US-JA, VEL36US132-US-JA, VEL36US133-US-JA, VEL36US134-US-JA, VEL36US135-US-JA, VEL36US136-US-JA, VEL36US137-US-JA, VEL36US138-US-JA, VEL36US139-US-JA, VEL36US140-US-JA, VEL36US141-US-JA, VEL36US142-US-JA, VEL36US143-US-JA, VEL36US144-US-JA, VEL36US145-US-JA, VEL36US146-US-JA, VEL36US147-US-JA, VEL36US148-US-JA, VEL36US149-US-JA, VEL36US150-US-JA, VEL36US180-US-JA, VEL36US181-US-JA, VEL36US182-US-JA, VEL36US183-US-JA, VEL36US184-US-JA, VEL36US185-US-JA, VEL36US186-US-JA, VEL36US187-US-JA, VEL36US188-US-JA, VEL36US189-US-JA, VEL36US190-US-JA, VEL36US191-US-JA, VEL36US192-US-JA, VEL36US193-US-JA, VEL36US194-US-JA, VEL36US195-US-JA, VEL36US196-US-JA, VEL36US197-US-JA, VEL36US198-US-JA, VEL36U2170-US-JA, VEL36US199-US-JA, VEL36US200-US-JA, VEL36US201-US-JA, VEL36US202-US-JA, VEL36US203-US-JA, VEL36US204-US-JA, VEL36US205-US-JA, VEL36US206-US-JA, VEL36US207-US-JA, VEL36US208-US-JA, VEL36US209-US-JA, VEL36US210-US-JA, VEL36US211-US-JA, VEL36US212-US-JA,

B. Mahrenholz

Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>

