

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Open Frame Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100 TUSTIN, CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100 TUSTIN, CA 92780 USA

Name and address of the factory

Di Feng Gong Ye Qu 2 Hao Xiasha Liuwu Village, Shipai Town
Dong Guan City
P. R. China

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

I/P: 100-240Vac., 50-60Hz, 5.3-2.2A
O/P: See test report for details

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

ECH450PSxxz
(xx can be 12, 15, 19, 24, 36, 48, 54 or 56 to denote different output voltage; z can be -C (case with no fan), -TF (case with top fan), -EF (case with side fan) or blank (open frame))

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/A11:2017
National Difference specified in the CB Test Report Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

PSE2019-0567 issued on 2019-12-17

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2019-12-23

Signature:

Jan-Erik Storgaard

For full legal entity names see www.ul.com/ncbnames