

0.25-1 Watt	2 Watts	3 Watts	4-5 Watts	6 Watts	8 Watts	10 Watts	12 Watts	15 Watts	20 Watts	30-40 Watts	50-600 Watts	Defense
<b>IK</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>SIP &amp; DIP</li> <li>Single Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>IH</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>SIP &amp; DIP</li> <li>Dual Output</li> <li>1000V Isolation</li> <li>6000V Optional</li> </ul>	<b>IS</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Regulated</li> <li>SIP</li> <li>Single Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>JCA04</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>Compact DIP24</li> <li>Single &amp; Dual Output</li> <li>UL &amp; TUV</li> <li>1500V Isolation</li> </ul>	<b>JCA06</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>Compact DIP24</li> <li>Single &amp; Dual Output</li> <li>UL &amp; TUV</li> <li>1500V Isolation</li> </ul>	<b>JCJ08</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> </ul>	<b>JCJ10</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> <li>High Efficiency</li> </ul>	<b>JCG12</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JCM15</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>1" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JCM20</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>1" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JCK30</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>2" x 2"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JCK60</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>2" x 2"</li> <li>Single Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>MTC05-30</b> <ul style="list-style-type: none"> <li>5-35 Watts</li> <li>15-40VDC Input</li> <li>Single &amp; Dual Output</li> <li>MIL-STD-461E/F</li> <li>MIL-STD-1275A-D</li> </ul>
<b>IA/IB/IE</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>SIP &amp; DIP</li> <li>Single Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>IL</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>SIP</li> <li>Single Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>IR</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Semi-regulated</li> <li>SIP Package</li> <li>Single &amp; Dual Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>JCD04/05</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>3500V Optional</li> </ul>	<b>JCD06</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>3500V Optional</li> </ul>	<b>JTF08</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> </ul>	<b>JCH10</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>2" x 1"</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> </ul>	<b>JTF12</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JCG15</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JCK20</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>2" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JTL30</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>2" x 1"</li> <li>Single, Dual &amp; Triple</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>ICH</b> <ul style="list-style-type: none"> <li>50-150 Watts</li> <li>2:1 &amp; 4:1 Input</li> <li>Half Brick</li> <li>Single Output</li> <li>1500V Isolation</li> <li>High Efficiency</li> </ul>	<b>MTC35/50</b> <ul style="list-style-type: none"> <li>35-50 Watts</li> <li>10-40VDC Input</li> <li>Single &amp; Dual Output</li> <li>-40 °C Operation</li> <li>MIL-STD 461E/F</li> <li>MIL-STD 1275A-D</li> </ul>
<b>IV</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>SIP &amp; DIP</li> <li>Single &amp; Dual Output</li> <li>3000V Isolation</li> <li>6000V Optional</li> </ul>	<b>JAH02</b> <ul style="list-style-type: none"> <li>±10 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1000V Isolation</li> <li>6000V Optional</li> <li>Optional Metal Case</li> </ul>	<b>IZ</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>Regulated</li> <li>SIP</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Optional Metal Case</li> </ul>	<b>JTC04</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1000V Isolation</li> <li>3500V Optional</li> </ul>	<b>JTC06</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> <li>3500V Optional</li> </ul>	<b>JTF10</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> <li>Remote On/Off</li> </ul>	<b>JTF10</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> <li>Remote On/Off</li> </ul>	<b>JTK15</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>2" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>3500V Optional</li> <li>High Efficiency</li> </ul>	<b>JTK20</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>1" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JCK40</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>2" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JFK40</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>2" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>IFH</b> <ul style="list-style-type: none"> <li>200 Watts</li> <li>2:1 Input</li> <li>Full Brick</li> <li>Single Output</li> <li>1500V Isolation</li> <li>Up to 90% Efficiency</li> </ul>	<b>MTC75/150</b> <ul style="list-style-type: none"> <li>75-150 Watts</li> <li>10-40VDC Input</li> <li>Single &amp; Dual Output</li> <li>-55 °C Operation</li> <li>MIL-STD 461E/F</li> <li>MIL-STD 1275A-D</li> </ul>
<b>IC</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>Ultra Slim DIP</li> <li>Single Output</li> <li>1500V Isolation</li> <li>3000V Optional</li> </ul>	<b>IU</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>Regulated</li> <li>SIP &amp; DIP</li> <li>Single &amp; Dual Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>JCA03</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>Compact DIP24</li> <li>Single &amp; Dual Output</li> <li>UL &amp; TUV</li> <li>1500V Isolation</li> </ul>	<b>SMD</b>			<b>JTA10</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>2" x 1"</li> <li>Single &amp; Dual Output</li> <li>Level 'B' EMI</li> <li>UL Approved</li> <li>1500V Isolation</li> </ul>	<b>JTK15</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>1" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JTM20</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>2" x 1"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JTL40</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>2" x 2"</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>QSB</b> <ul style="list-style-type: none"> <li>75-600 Watts</li> <li>2:1 &amp; 4:1 Input</li> <li>1/4, 1/2 &amp; Full Brick</li> <li>Single Output</li> <li>1500V Isolation</li> <li>Up to 90% Efficiency</li> </ul>	<b>MTF50</b> <ul style="list-style-type: none"> <li>-55 °C Operation</li> <li>50 Watt Filter Module</li> <li>10-50VDC Input</li> <li>MIL-STD 461E/F</li> <li>MIL-STD 1275A-D</li> </ul>	<b>DSF100-500</b> <ul style="list-style-type: none"> <li>100, 200 &amp; 500 Watts</li> <li>MIL-STD Filter</li> <li>Up to 28 A Output</li> <li>DEF-STAN 59-41</li> <li>MIL-STD 461E/F</li> <li>MIL-STD 1275A-D</li> </ul>
<b>IF/IQ</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Regulated / Semi</li> <li>SIP &amp; DIP</li> <li>Single &amp; Dual Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>JCA02</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>Compact DIP24</li> <li>Single &amp; Dual Output</li> <li>UL &amp; TUV</li> <li>1500V Isolation</li> </ul>	<b>JCB03</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> <li>3000V Optional</li> <li>Optional Metal Case</li> </ul>	<b>ISG</b> <ul style="list-style-type: none"> <li>±5% Input</li> <li>Regulated</li> <li>Single Output</li> <li>1000V Isolation</li> </ul>	<b>ISL</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>Regulated</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> </ul>	<b>ISQ</b> <ul style="list-style-type: none"> <li>±5% Input</li> <li>Regulated</li> <li>Single Output</li> <li>1000V Isolation</li> </ul>	<b>Medical</b>			<b>JTF15</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>1600V Isolation</li> <li>Remote On/Off</li> <li>High Efficiency</li> </ul>	<b>JTA20</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>2" x 1.6"</li> <li>Single &amp; Dual Output</li> <li>Level 'B' EMI</li> <li>UL Approved</li> <li>1500V Isolation</li> </ul>	<b>DSF100-500</b> <ul style="list-style-type: none"> <li>100, 200 &amp; 500 Watts</li> <li>MIL-STD Filter</li> <li>Up to 28 A Output</li> <li>DEF-STAN 59-41</li> <li>MIL-STD 461E/F</li> <li>MIL-STD 1275A-D</li> </ul>	
<b>IW</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>Regulated</li> <li>SIP &amp; DIP</li> <li>Single &amp; Dual Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>IM</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>Regulated</li> <li>SIP</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> </ul>	<b>IP/IT</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>Regulated</li> <li>SIP</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> </ul>	<b>ISF</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>Single &amp; Dual Output</li> <li>1000V Isolation</li> <li>3000V Optional</li> </ul>	<b>IST</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>Single Output</li> <li>1000V Isolation</li> </ul>	<b>IST</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>Single Output</li> <li>1000V Isolation</li> </ul>	<b>JHM03</b> <ul style="list-style-type: none"> <li>Wide Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>60601 Approved</li> <li>5000 VAC Isolation</li> </ul>	<b>JHM10</b> <ul style="list-style-type: none"> <li>Wide Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>60601 Approved</li> <li>5000 VAC Isolation</li> <li>High Efficiency</li> </ul>	<b>JTH15</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>2" x 1"</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> <li>Remote On/Off Option</li> <li>High Efficiency</li> </ul>	<b>LED Drivers</b>			
<b>SR</b> <ul style="list-style-type: none"> <li>Switching Regulator</li> <li>Wide Input Range</li> <li>3 Pin SIP Package</li> <li>Up to 97% Efficiency</li> <li>Short-circuit Protection</li> </ul>	<b>ISJ</b> <ul style="list-style-type: none"> <li>±10% Input</li> <li>Unregulated</li> <li>Ultra Slim Package</li> <li>Single Output</li> <li>1500V Isolation</li> <li>3000V Optional</li> </ul>	<b>ISP</b> <ul style="list-style-type: none"> <li>2:1 Input</li> <li>Regulated</li> <li>Single &amp; Dual Output</li> <li>1500V Isolation</li> </ul>	<b>JHM06</b> <ul style="list-style-type: none"> <li>Wide Input</li> <li>DIP24</li> <li>Single &amp; Dual Output</li> <li>60601 Approved</li> <li>5000 VAC Isolation</li> </ul>	<b>JTA15</b> <ul style="list-style-type: none"> <li>4:1 Input</li> <li>2" x 1.6"</li> <li>Single &amp; Dual Output</li> <li>Level 'B' EMI</li> <li>UL Approved</li> <li>1500V Isolation</li> </ul>	<b>LDU05/07/08/14</b> <ul style="list-style-type: none"> <li>7-30 VDC Input</li> <li>Constant Current O/P</li> <li>Up to 1000 mA</li> <li>Non Isolated</li> <li>Up to 95% Efficiency</li> <li>Dimming Control</li> </ul>	<b>LDU20/24</b> <ul style="list-style-type: none"> <li>7-30 VDC Input</li> <li>Constant Current O/P</li> <li>Up to 1000 mA</li> <li>Non Isolated</li> <li>Up to 95% Efficiency</li> <li>Dimming Control</li> </ul>	<b>LDU48</b> <ul style="list-style-type: none"> <li>7-60 VDC Input</li> <li>Constant Current O/P</li> <li>Up to 1000 mA</li> <li>Non Isolated</li> <li>Up to 95% Efficiency</li> <li>Dimming Control</li> </ul>	<b>MTH100</b> <ul style="list-style-type: none"> <li>Increase hold up time</li> <li>10 A Output Current</li> <li>10-40VDC Input</li> <li>User Programmable</li> <li>98% Efficiency</li> </ul>				