



Ref. Certif. No.

US-33573-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

Name and address of the factory

8-1 FU KUNG RD FU HSING PARK FU HSING HSIANG
CHANGHUA HSIEN 506
TAIWAN

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

ECL05USXX-Y, ECL10USXX-Y, ECL10US05-XA1176A
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014 / A11:2017;
National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E317867-A6036-CB-1 issued on 2019-04-23

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-04-25

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-33573-UL

Model Details:

ECL05USXX-Y, ECL10USXX-Y, where XX is 03, 05, 09, 12, 15, 24 or 48; Y is E, P or T.

Factories:

1 JING XIANG RD DONGCHENG FOREIGN TRADE INDUSTRIAL PARK ZHUSHAN DONGCHENG DISTRICT
DONGGUAN GUANGDONG 523128
CHINA

Ratings:

Input:

100-240Vac 0.4A 50-60Hz

ECL10USXX-Y Output at an ambient temperature of 50°C (For 70°C ambient, output rating shall be derated to 50%)

ECL10US03-Y 3.3Vdc, 2.6A

ECL10US05-Y and ECL10US05-XA1176A 5Vdc, 2A

ECL10US09-Y 9Vdc, 1.1A

ECL10US12-Y 12Vdc, 0.83A

ECL10US15-Y 15Vdc, 0.67A

ECL10US24-Y 24Vdc, 0.42A

ECL10US48-Y 48Vdc, 0.21A

ECL05USXX-Y Output at an ambient temperature of 70°C

ECL05US03-Y 3.3Vdc, 1.3A

ECL05US05-Y 5Vdc, 1A

ECL05US09-Y 9Vdc, 0.55A

ECL05US12-Y 12Vdc, 0.415A

ECL05US15-Y 15Vdc, 0.335A

ECL05US24-Y 24Vdc, 0.21A

ECL05US48-Y 48Vdc, 0.105A

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2019-04-25

Signature:

Jolanta M. Wroblewska