



Ref. Certif. No.

DE 3 - 501647

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product

Produit

Name and address of the applicant

Nom et adresse du demandeur

Name and address of the manufacturer

Nom et adresse du fabricant

Name and address of the factory

Nom et adresse de l'usine

Ratings and principal characteristics

Valeurs nominales et caractéristiques principales

Trade mark (if any)

Marque de fabrique (si elle existe)

Model/type Ref.

Ref. de type

Additional information (if necessary)

Information complémentaire (si nécessaire)

A sample of the product was tested and found
to be in conformity with

Un échantillon de ce produit a été essayé et a été
considéré conforme à la

as shown in the Test Report Ref. No.

which forms part of this certificate

comme indiqué dans le Rapport d'essais numéro
de référence qui constitue une partie de ce
certificat

Power supplies

XP Power LLC.

15641 Red Hill Avenue, Suite 100

Tustin CA 92780, USA

XP Power LLC.

15641 Red Hill Avenue, Suite 100, Tustin CA 92780, USA

8-1, Fu Kung Rd., Fu Hsing Park,, 506 Fu Hsing Hsiang, Chang
Hua Hsien,, TAIWAN

For further information please see attachment

Input, AC:

100-240 V, 50-60 Hz, 0.6 A

Protection Class:

Class I or Class II at end use

Temperature, Ambient:

50°C with maximum output power

70°C with half maximum output power

Elevation for use:

0-3048 m above sea level

See attachment for further information.

XP

ECL15USxx-y

(xx=03, 05, 09, 12, 15, 24 or 48 for output voltage,

y=E, P, T, S or SD for different connector and

enclosure configurations)

Certificate DE 3 - 59976 issued 2012-11-27 is replaced by this
version due to technical changes.

IEC 60950-1(ed.2);am1;am2

095-72111014101-000

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme National de Certification

Date,

2015-12-18

CB 15 11 57396 368


Adrian Rabago



TÜV SÜD Product Service GmbH · Certification Body · Ridlerstrasse 65 · D-80339 München

Product Service

Additional factory information:

Name and address of the factory <i>Nom et adresse de l'usine</i>	61661 8-1, Fu Kung Rd., Fu Hsing Park, 506 Fu Hsing Hsiang, Chang Hua Hsien, TAIWAN
	77041 No.1 Jing Xiang Rd., DongCheng Foreign Trade Industrial Park, ZhuShan, DongCheng District 523128 Dongguan, PEOPLE'S REPUBLIC OF CHINA

APPROVED MODELS AND RATED OUTPUTS:

Model Number	Output	
	Voltage (VDC)	Current (A)
ECL15US03	3.3	3
ECL15US05	5	3
ECL15US09	9	1.67
ECL15US12	12	1.25
ECL15US15	15	1
ECL15US24	24	0.63
ECL15US48	48	0.32

MODEL NO. SUFFIX:

- P: PCB mount, open frame model, soldering pin input and output power connection.
- T: chassis mount, open frame model, terminal block for input and output connection.
- E: encapsulated, plastic enclosure, soldering pin input and output power connection.
- S: encapsulated, plastic enclosure, screw terminal block for input and output connection.
- SD: DIN rail mounted, clip provided.

Conditions of Acceptability:

When installing the equipment, all requirements of the standards and the manufacturer's specifications must be met.

The models require:

- A suitable electrical and fire enclosure must be provided in the end use equipment.
- If installed in Class I end product, proper bonding to the end-product main protective earthing terminal is required at end use.
- When installed in end product, the clearance and creepage distance between the related circuitry of the power supply and accessible parts shall meet the standard(s) requirements. Hi-pot test, touch current test and ground bond test (for class I end product) shall be conducted at end product.

Date: 2015-11-18
Report No.: 095-72111014101-000
CB 15 11 57396 368
Page 2 of 2



Product Service

TÜV SÜD Product Service GmbH • Certification Body • Ridlerstrasse 65 • D-80339 München