

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Switching Power Supply
Name and address of the applicant	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	XP POWER (KUNSHAN) LTD 230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215300 CHINA <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark / Brand (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	HPA1K5PSXX Where XX can be any number between 12-48. May also be provided with additional suffix "SF" or "-M".
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E139109-A6093-CB-1 issued on 2020-09-18

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-09-18

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36619-UL

Factories:

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN
MY PHUOC 3 INDUSTRIAL PARK
BEN CAT DISTRICT
BINH DUONG BINH DUONG VIETNAM

XP POWER PLC
16 HORESHOE PARK
PANGBOURNE
RG8 7JW UNITED KINGDOM

XP POWER LLC
990 BENECIA AVE
SUNNYVALE CA 94085
UNITED STATES

Ratings:

INPUT:

100 - 180Vac 16A 50/60Hz
180 - 240Vac 10A 50/60Hz

OUTPUT V1 :

Model HPA1K5PS24:

24Vdc, 62.5 A Max, 1500 W (for Input rated: 180-240 Vac)
1400 W (for Input rated: 100-180 Vac)

Model HPA1K5PS48:

48Vdc, 31 A, 1500 W (for Input rated: 180-240 Vac)
1400 W (for Input rated: 100-180 Vac)

All models: Output V2 Standby: 5Vdc, 2A

Additional information (if necessary)



UL (US), 333 Pfinqsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-09-18

Signature:

Jolanta M. Wroblewska