


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Switching Power Supply
Name and address of the applicant	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the factory	XP POWER (KUNSHAN) LTD 230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215300 CHINA <input checked="" type="checkbox"/> Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	P3-MMMM-FFF-OO, P4-MMMM-FFF-OO, P5-MMMM-FFF-OO See Page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include technical modifications. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E139109-A6058-CB-1 issued on 2019-05-24

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnamesDate: 2019-05-28
Original Issue Date: 2018-11-30

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-32852-M1-UL

Model Details:

P3-MMMM-FFF-OO, P4-MMMM-FFF-OO, P5-MMMM-FFF-OO, where M can be a combination of a letter R to U and a number 1-10, F, G, or Z; where F can be a combination of the letter E, F or T and any number 0-9 or blank; where O can be any number 0-9 or blank designating parallel option. Dashes are optional in model designation.

Ratings:

P3-MMMM-FFF-OO:

INPUT ~ 100-240VAC 50/60Hz 3.4A

P4-MMMM-FFF-OO:

INPUT ~ 100-240VAC 50/60Hz 5.5A

P5-MMMM-FFF-OO:

INPUT ~ 100-240VAC 50/60Hz 7.3A

Output rated: See model differences for details.

Factories:

XP POWER (VIETNAM) CO LTD

LOT D - 4Q - CN

MY PHUOC 3 INDUSTRIAL PARK

BEN CAT DISTRICT

BINH DUONG BINH DUONG VIETNAM

XP POWER PLC

16 HOESHOE PARK

PANGBOURNE

RG8 7JW UNITED KINGDOM

XP POWER LIMITED

LIPO BLDG, #05-01

621 ALJUNIED RD

SINGAPORE 389834 SINGAPORE

XP POWER LLC

990 BENECIA AVE

SUNNYVALE CA 94085

UNITED STATES

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

Summary of Modifications:

Updated Technical Considerations, Clauses, and Tables.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-05-28

Original Issue Date: 2018-11-30

Signature:

Jolanta M. Wroblewska