## 



36W

The AKM36 series of desktop adaptors comply with the latest energy efficiency level VI standards with high active mode efficiency and extremely low no load power consumption. Available with a standard jack plug connector these adaptors suit a wide variety of cost sensitive industrial and medical applications while maintaining industry leading performance.

#### AC-DC POWER SUPPLIES



#### **Features**

- Energy efficiency level VI
- European CoC tier 2
- Medical and ITE approvals
- Class II construction
- Optional white versions
- Output voltages from 9V to 36V
- 3 year warranty

#### **Applications**







Analytical Instrumentation

Healthcare

Home Healthcare





Medical Diagnostic

Process

#### **Dimensions**

4.25" x 1.97" x 1.33" (108.0 x 50.0 x 33.8 mm)

### **Models & Ratings**

Model Number(3)	Output Power	Output Voltage	Output Current	Total Regulation <sup>(1)</sup>	Efficiency <sup>(2)</sup>
AKM36US09C2		9.0V	4.0A		88.9%
AKM36US12C2		12.0V	3.0A		89.3%
AKM36US15C2		15.0V	2.4A		88.4%
AKM36US18C2	36W	18.0V	2.0A	5%	89.5%
AKM36US24C2		24.0V	1.5A		89.4%
AKM36US30C2		30.0V	1.2A		89.9%
AKM36US36C2		36.0V	1.0A		89.2%

#### Notes:

- 1. Total regulation includes initial set accuracy, line and load regulation.
- 2. Typical average value measured at 25%, 50%, 75% and 100% at 230 VAC.
- 3. For white case version add suffix '-W' e.g. AKM36US12C2-W. MOQ applies, contact sales for details.

# **← AKM36 Series**

## Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage	90		264	VAC	
Input Frequency	47		63	Hz	
Input Current			1.0	А	90VAC
Inrush Current			70	А	230VAC, cold start at 25°C
Power Factor					EN61000-3-2 Class A
No Load Input Power			75	mW	
Input Protection	Internal fuse in	line			

## Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	9		36	V	See Models and Ratings table
Minimum Load	0			А	No minimum load required
Start Up Delay			4	s	
Start Up Rise Time		30		ms	
Hold Up Time	10			ms	Full load and 100VAC
Total Regulation			5	%	See Models and Ratings table
Transient Response			4	% deviation	Recovery within <1% within 500µs for a 60% step load change at 0.15A/µs
Ripple and Noise			200	mV pk-pk	Measured with 20MHz Bandwidth and 10 $\mu$ F electrolytic in parallel with 0.1 $\mu$ F ceramic capacitor
Short Circuit Protection	Continuous, trip and restart (hiccup mode) with auto recovery				
Temperature Coefficient			0.05	%/°C	

## General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		89.5		%	Typical average of efficiencies measured at 25%, 50%, 75% and 100% load and 115 VAC input
Energy Efficiency					Level VI
Isolation	4000			VAC	Input to Output, 2 x MOPP
Leakage Current			50	μA	264VAC, 60Hz
Switching Frequency	24		70	kHz	Variable
Mean Time Between Failure	200			khrs	MIL-HDBK-217F at 25°C GB
Weight		0.53 (240)		lb (g)	

# **← AKM36 Series**

## **Environmental**

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Operating Temperature	0		+40	°C		
Storage Temperature	-20		+70	°C		
Cooling	Natural convection					
Operating Humidity	5		90	%RH	Non-condensing	
Operating Altitude			5000	m		
Shock	1m drop onto concrete on each of 6 axes, non operating					
Vibration	10		300	Hz	2g, 0.3 decades/min, 15 mins for each of 3 axes	

## **EMC: Emissions**

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55032	Level B	
Radiated	EN55032	Level B	
Harmonic Current	EN61000-3-2	Class A	
Voltage Flicker	EN61000-3-3		

## **EMC: Immunity**


Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Medical Device EMC	IEC60601-1-2	Ed. 4.0: 2014	as below	
Low Voltage PSU EMC	EN61204-3	High severity level	as below	
ESD Immunity	EN61000-4-2	±8kV contact, ±15kV air	А	
Radiated Immunity	EN61000-4-3	10V/m	А	
EFT/Burst	EN61000-4-4	Level 3	Α	
Surge	EN61000-4-5	Level 2	А	
Conducted Immunity	EN61000-4-6	6V	А	
Magnetic Fields	EN61000-4-8	30A/m	А	
		Int: 100% 10ms	А	
	EN61000-4-11	Dip: 30% 500ms	A/B	High Line/Low Line
Dips and Interruptions		Int: 100% 5000ms	В	
		Dip: 30% 25AC cycles	A/B	High Line/Low Line
	EN60601-1-2	Int: 100% 0.5 AC Cycle	А	At 8 angles
		Int: 100% 1 AC Cycle	A/B	High Line/Low Line
		Int.: >95% 5000ms	В	

## 

## **Safety Approvals**

Certification	Safety Standard	Notes & Conditions			
	UL62368-1, CAN/CSA C22.2 No. 62368-1-14	Information Technology			
UL	ANSI/AAMI ES 60601-1	Medical, 2 x MOPP			
TUV	EN62368-1:2014/A11:2017	Information Technology			
100	EN60601-1	Medical, 2 x MOPP			
СВ	IEC60950-1:2005 Ed 2 / IEC62368-1:2014	Information Technology			
СВ	IEC60601-1	Medical, 2 x MOPP			
CSA	CSA C22.2 No. 60601	Medical, 2 x MOPP			
AU/NZ	AU/NZ 60950.1				
CE	Meets all applicable directives				
UKCA	Meets all applicable legislation				

#### **Mechanical Details**



#### Notes:

- 1. Dimensions in inches (mm)
- 2. Weight: 0.53lbs (240g)
- 3. Output plug: ø5.5 x ø2.5 x 11.0mm, centre positive
- 4. The standard IEC320-C7 cable fits the polarised IEC320-C8 (C8P) connector  $\,$