


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Power adapter
Name and address of the applicant	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 USA
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 USA
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	XP POWER (KUNSHAN) LTD 230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215300 CHINA <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	ALM65USXXYY-ZZ##V See Page 2
Additional information (if necessary may also be reported on page 2)	Class I <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1, IEC 60950-1(ed.2);am2
As shown in the Test Report Ref. No. which forms part of this Certificate	E139109-A155-CB-2 issued on 2017-07-12

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2017-07-12

Signature:

For full legal entity names see www.ul.com/ncbnames

Jolanta M. Wroblewska



Ref. Certif. No.

US-30108-UL

Model Details:

ALM65USXXYY-ZZ##V

(where XX is any number between 12-48 designating output voltage and YY can be blank or "C2" designating Class II configuration, and -ZZ can be blank or "-A", "-6", "-6A", "-8", "-8A" designating AC inlet type, and ## can be any alphanumeric or blank designating marketing purposes only, and V can be any alphanumeric or blank designating casing color)

Factories:

XP POWER INC
990 BENECIA AVE SUNNYVALE CA 94085-2804
USA

XP POWER (VIETNAM) CO LTD
LOT D - 4Q – CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIETNAM

Ratings:

Input: 100-240 Vac, 50/60 Hz, 1.4 A

Output:

- ALM65US12: 12 Vdc (10.1 - 13.5 Vdc), 5.4 A max., 65W max.;
- ALM65US15: 15 Vdc (13.5 - 17.0 Vdc), 4.3 A max., 65W max.;
- ALM65US19: 19 Vdc (17.1 - 21.0 Vdc), 3.4 A max., 65W max.;
- ALM65US24: 24 Vdc (21.0 - 26.0 Vdc), 2.7 A max., 65W max.;
- ALM65US48: 48 Vdc (42.1 - 54.0 Vdc), 1.35 A max., 65W max.

Additional Information:

Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2:2013;
National Differences specified in the CB Test Report.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-07-12

Signature:

Jolanta M. Wroblewska