

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER LTD
401 COMMONWEALTH DR
HAW PAR TECHNOCENTRE
LOBBY B, #02-02
SINGAPORE 149598 SINGAPORE

Name and address of the manufacturer

XP POWER LTD
401 COMMONWEALTH DR
HAW PAR TECHNOCENTRE
LOBBY B, #02-02
SINGAPORE 149598 SINGAPORE

Name and address of the factory

Note: When more than one factory, please report on page 2

DONGGUAN CINCONG ELECTRONICS LTD
1 JING XIANG RD DONGCHENG FOREIGN TRADE
INDUSTRIAL PARK ZHUSHAN DONGCHENG DISTRICT
DONGGUAN GUANGDONG 523128
CHINA Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 1

Model / Type Ref.

ASB75USXX-YYYYYY
See Page 2

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E346017-A6009-CB-1 issued on 2021-01-14

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-01-15

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-108769-UL

Model Details:

ASB75USXX-YYYYYY (where XX can be any number between 12 and 48 designating the output voltage, YY can be any Alphanumeric or blank for marketing purposes only)

Factories:

CINCON ELECTRONICS CO LTD
8-1 FU KUNG RD FU HSING PARK FU HSING HSIANG CHANGHUA HSIEN 506
TAIWAN

Ratings:

Input:

100-240 Vac; 1.5 A; 50/60 Hz

Output (ASB75US12):

12 Vdc; 6.25 A

Output (ASB75US15):

15 Vdc; 5 A

Output (ASB75US24):

24 Vdc; 3.12 A

Output (ASB75US36):

36 Vdc; 2.08 A

Output (ASB75US48):

48 Vdc; 1.56 A

Additional Information:

Additionally evaluated to EN 62368-1:2014/ A11:2017; National differences specified in the CB Test Report.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA



UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK



UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN



UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-01-15

Signature:

Jan-Erik Storgaard