

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	AC-DC Power Supply
Name and address of the applicant	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	XP POWER INC 990 BENECIA AVE SUNNYVALE CA 94085 UNITED STATES <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	Input: 200-240 Vac; 3-Phase (3W+PE); 50/60 Hz; 17.5A Max Per Phase Output: See model differences for Output Ratings by Model.
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	HPD4K5TSXXX Series See Page 2
Additional information (if necessary may also be reported on page 2)	<input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E139109-A6008-CB-1 issued on 2018-08-01

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-08-03
Original Issue Date: 2018-04-25

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-31639-A1-UL

Model Details:

HPD4K5TSXXX Series, where XXX can be 025, 050, 075 or 150.

Factories:

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215321
CHINA

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIETNAM

XP POWER PLC
HORESHOE PARK PANGBOURNE RG87 JW
UNITED KINGDOM

Additional Information:

The original report was modified to include the following changes/additions:

- 1 - Correction - added the previously omitted Condition of Acceptability that a suitable 20 A 250 V fuse must be provided as part of the end product installation
- 2 - Correction - added the previously omitted Condition of Acceptability that states a suitable transformer shall be provided outside of the US/Canada in order to provide the correct voltage to the device
- 3 - Correction - revised Clause 5.6.4.3 to state that two 20 fuses are provided on each of the previously certified component power supplies utilized
- 4 - Correction - revised the frequency on the Minimum Clearance/Creepage table from 0.006 to 0.06 kHz.
- 5 - Correction - revised the voltage on the Earthed Accessible conductive part table from 528Vac to 264Vac
- 6 - Correction - revised the photos of the unit due to a publishing error, the photos now represent the EUT.
- 7 - Correction - revised the critical components table due to various errors
- 8 - Correction - revised report to say additional evaluated to EN 62368-1:2014/ A11:2017
- 9 - Correction – Added missing enclosures

Additionally evaluated to EN 62368-1:2014/ A11:2017.

National Differences specified in the CB Test Report.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-08-03
Original Issue Date: 2018-04-25

Signature:
Jolanta M. Wroblewska