

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEMESYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC**CB TEST CERTIFICATE****CERTIFICAT D'ESSAI OC**Product
Produit

Component Power Supply DC-to-DC Converter

Name and address of the applicant
Nom et adresse du demandeurXP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USAName and address of the manufacturer
Nom et adresse du fabricantXP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USAName and address of the factory
Nom et adresse de l'usine9 Keji 2nd Rd Technology Industrial Park
Tainan 70955 TAIWAN

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} page

 Additional Information on page 2Ratings and principal characteristics
Valeurs nominales et caractéristiques principalesInput: 4.5-5.5VDC, 10.8-13.2VDC, 13.5-16.5VDC, 21.6-26.4VDC.
See GPI model differences for output ratings.Trademark (if any)
Marque de fabrique (si elle existe)Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais
constructeur

CTF Stage 3

Model / Type Ref.
Ref. De typeIMA01xxDyyy, IMA01xxSyyy
See Page 2

Additional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,,
peuvent être indiqués sur la 2^{ème} page

Additionally evaluated to EN 60601-1:2006 / A1:2013 / A12:2014;
National Differences specified in the CB Test Report. Additional Information on page 2

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60601-1(ed.3), IEC 60601-1(ed.3);am1

As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

E321744-D1014-1/A0/C0-ULCB issued on 2016-10-20

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**




- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2016-10-25

Signature:



Jolanta M. Wroblewska

Model Details:

IMA01xxDyyy, IMA01xxSyyy (where xx is 05, 12, 15 or 24 representing input voltage; yyy is 03, 3V3, 05, 09, 12 or 15 representing output voltage)

Additional Information:

The Risk Management requirements of the standard were not addressed.

Additional information (if necessary)**Information complémentaire (si nécessaire)**

- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbnames

Date: 2016-10-25

Signature:



Jolanta M. Wroblewska