

420W Fan cooled

350W Conduction cooled

280W Convection cooled

AC-DC power supplies



The CCR420 series of compact medical AC-DC power supplies are designed to operate in convection cooled, conduction cooled, and fan cooled applications with power ratings from 280 to 420W. CCR420 offers high efficiency and high power density in a low profile, baseplate cooled design that ensures effective thermal management and quiet operation for noise sensitive applications.

Featuring Class B conducted and radiated emissions, worldwide industrial and medical safety approvals, 2 x MOPP isolation and low leakage currents, the CCR420 is designed for easy integration into a wide range of BF rated medical applications including respiratory care, imaging, patient monitoring, patient treatment, and industrial applications such as process control, test & measurement, and industrial printing.



Features

- ▶ 420W fan cooled, 350W conduction cooled
- ▶ Universal, single phase input: 85 to 264VAC
- ▶ 129.4 x 83.5mm footprint, 25.4mm profile
- ▶ High efficiency, up to 94%
- ▶ Low earth leakage <300µA
- ▶ Low patient leakage <75µA
- ▶ Medical (BF) & ITE safety approvals
- ▶ Class B conducted and radiated emissions
- ▶ 3 year warranty

Applications



Healthcare



Instrumentation



Process control



Robotics



Technology

Dimensions

129.4 x 83.5 x 25.4mm (5.09" x 3.29" x 1.00")

More resources

Click the link or scan the code

→ xppower.com



Models & ratings

Model number	Output voltage	Output current			Efficiency ⁽³⁾
		Convection cooled	Conduction cooled ⁽²⁾	Fan cooled ⁽¹⁾	
CCR420PS12	12.0V	23.33A	29.17A	35.00A	92.5%
CCR420PS15	15.0V	18.67A	23.33A	28.00A	93.0%
CCR420PS24	24.0V	11.67A	14.58A	17.50A	94.0%
CCR420PS28	28.0V	10.00A	12.50A	15.00A	94.0%
CCR420PS30	30.0V	9.33A	11.67A	14.00A	94.0%
CCR420PS36	36.0V	7.78A	9.72A	11.67A	94.0%
CCR420PS48	48.0V	5.83A	7.29A	8.75A	94.0%
CCR420PS54	54.0V	5.19A	6.48A	7.78A	94.5%

Notes:

1. Requires 37m³/h (22CFM)

2. Thermal resistance for conduction cooling ≤1.6°C/W.

3. Typical value at 230VAC input and 420W load.



Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Input voltage - operating	85 ⁽¹⁾	115/230	264	VAC	Derate output linearly – Fan cooled
					Derate output linearly from 350W at 115VAC to 290W at 85VAC – conduction cooled
					Derate output linearly from 225W at 115VAC to 180W at 85VAC – convection cooled
Input frequency	47	50/60	63	Hz	Agency approval, 47-63Hz
Power factor		>0.95			230VAC, 100% load
Input current - full load			4.5/2.5	A	115/230VAC
Inrush current		30		A	240VAC cold start, 25°C
Earth leakage current			300	µA	264 VAC/60Hz
No load input power			0.5	W	
Input protection	T6.3A/250V Internal fuse fitted in line and neutral.				

⁽¹⁾ Agency approval, 90-264VAC

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Output voltage	12		54	VDC	See models and ratings table
Initial set accuracy			±1	%	50% load, 115/230VAC
Minimum load	No minimum load required				
Start up delay			2	s	115/230VAC full load
Hold up time	8			ms	115VAC full load at 25°C
Drift			±0.02	%	After 20 min warm up
Line regulation			±0.5	%	
Load regulation			±1.0	%	0-100% load
Transient response			4	%	Recovery within 1% in less than 500µs for a 50-75% and 75-50% load step
Output voltage adjustment		±5		%	115VAC Full load
Ripple & noise			1	%	Measured at 20MHz bandwidth and 10µF electrolytic capacitor in parallel with 0.1µF ceramic capacitor at 25°C
Remote sense	Compensates for 5% drop of nominal output voltage				
Overvoltage protection	110		150	%	Vnom, recycle input to reset, 54V model OVP <63V
Overload protection	110		170	%	Inom, constant current and auto recovery
Short circuit protection	Trip & restart				
Temperature coefficient			0.02	%/°C	
Overtemperature protection	Measured internally, auto resetting				

General


Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Efficiency		94		%	See models and ratings table
Isolation: input to output input to ground output to ground	4000			VAC	2 x MOPP
	1800			VAC	1 x MOPP
	1500			VAC	1 x MOPP
Switching frequency		65		kHz	Main converter (varies with load)
	70		140	kHz	PFC (varies with load)
Power density			1.5	W/cm ³	Fan cooled
Patient leakage current			75	μA	
Mean time between failure		400		khrs	MIL-HDBK-217F, 25°C GB.
Weight		470 (1.036)		g (lb)	

Environmental


Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Operating temperature	-40		+80	°C	See derating curve, safety approved to 50°C
Storage temperature	-40		+85	°C	
Cooling	37 (22)			m ³ /h (CFM)	For fan cooled operation
Humidity	5		95	%RH	Non-condensing
Operating altitude			4000 / 5000 (2000)	m	Medical/ITE OVC II (OVC III)
Vibration	Single axis 10-500Hz at 2g sweep and endurance at resonance in all 3 planes. Conforms to EN60068-2-6				
Shock	±3 x 30g shocks in each plane, total 18 shocks. 30g = 11ms (±0.5msecs), half sine. Conforms to EN60068-2-27				
Baseplate temperature			95	°C	When using conduction cooling, max baseplate temperature (measured at the center) is 95°C but some components are not thermally connected to the baseplate. The temperatures of these components may not exceed temperatures shown in the thermal considerations section on page 5.

Derating curve

Input derating curve



Thermal derating curve



- Fan cooled with 37m³/h air flow at 230VAC
- Fan cooled with 37m³/h air flow at 115VAC
- Conduction cooled @ 230VAC
- Conduction cooled @ 115VAC
- Convection cooled @ 230VAC
- Convection cooled @ 115VAC

Emissions - EMC

Phenomenon	Standard	Test level	Notes & conditions
Conducted	EN55032/EN55011	Class B	
Radiated	EN55032/EN55011	Class B	
Harmonic currents	EN61000-3-2	Class A, C & D	Class C \geq 150W
Voltage flicker	EN61000-3-3		

Emissions - immunity

Phenomenon	Standard	Test level	Criteria	Notes & conditions
Medical device EMC	IEC60601-1-2	Ed.4.0 : 2014	as below	
Low voltage PSU EMC	EN55035		as below	
ESD immunity	EN61000-4-2	4	A	\pm 15kV air, \pm 8kV contact
Radiated immunity	EN61000-4-3	10V/m	A	
EFT/burst	EN61000-4-4	\pm 2kV	A	
Surge	EN61000-4-5	Installation class 4	A	\pm 2kV line to line, \pm 4kV line to earth
Conducted	EN61000-4-6	6V	A	
Magnetic field	EN61000-4-8	30A/m	A	
Dips and interruptions	EN55035 (115VAC)	Dip 100% (0VAC), 10ms	A	
		Dip 100% (0VAC), 20ms	A	
		Dip 30% (80.5VAC), 500ms	B	
		Dip 60% (46VAC), 100ms	B	
		Dip 100% (0VAC), 5000ms	B	
	EN55035 (230VAC)	Dip 100% (0VAC), 10ms	A	
		Dip 100% (0VAC), 20ms	A	
		Dip 30% (181VAC), 500ms	A	
		Dip 60% (92VAC), 100ms	A	
		Dip 100% (0VAC), 5000ms	B	
	EN60601-1-2 (100VAC)	Dip 100% (0VAC), 10ms	A	
		Dip 100% (0VAC), 20ms	A	
		Dip 30% (70VAC), 500ms	B	
	EN60601-1-2 (240VAC)	Dip 100% (0VAC), 5000ms	B	
		Dip 100% (0VAC), 10ms	A	
		Dip 100% (0VAC), 20ms	A	
Dip 30% (168VAC), 500ms		A		
		Dip 100% (0VAC), 5000ms	B	


Safety approvals

Certification	Standard	Notes & conditions
CB report	IEC62368-1	Audio/video, information and communication technology equipment
	IEC60601-1	Medical
UL	UL62368-1	Audio/video, information and communication technology equipment
	ANSI/AAMI ES60601-1 & CSA C22.2 No.60601-1	Medical
EN	EN62368-1	Audio/video, information and communication technology equipment
	EN60601-1	Medical
CE	Meets all applicable directives	
UKCA	Meets all applicable legislation	

Isolation	Standard	Notes & conditions
Primary to Secondary	2 x MOPP (Means of Patient Protection)	
Primary to Earth	1 x MOPP (Means of Patient Protection)	
Secondary to Earth	1 x MOPP (Means of Patient Protection)	



Mechanical details



AC input connector (CN1): ECE ETB22

Pin connections		
Pin	Function	Mating wire range
1	ACL	14-18AWG
2	ACN	

Max torque: 0.4 N-m (3.5 lb-in)

Remote sense (CN2): TKP 8822-02-NHB or equivalent

Pin connections			
Pin	Function	Mating housing	Terminal
1	Rs+	JST XHP-2 or equivalent	JST SXH-001T-P0.6N or equivalent
2	Rs-		


Notes:

- All dimensions shown in mm (inches). Tolerance: ± 0.5 (0.02).
- Weight: Standard versions: 470g (1.036lbs) approx.

- DC output terminal screws are M4. Max torque: 0.7N-m (6.2lb-in)

Thermal considerations

Temperature measurements (at maximum ambient)	
Component	Max temperature °C
L1	130°C
F1	125°C
C27	125°C
C37	125°C
Cover (above T3)	100°C
Baseplate	95°C



In order to ensure safe operation of the PSU in the end-use equipment, the temperature of the components listed in the table must not be exceeded.

Temperature should be monitored using K type thermocouples placed on the hottest part of the component (out of direct air flow).