AC-DC Power Supplies



240 Watts

- Ultra Slim Design 45 mm
- 150% Peak Load for 3 seconds
- Ambient Operation from -25 °C to +70 °C
- Full Load at 60 °C
- High Efficiency Up to 94%
- Volt-Free Contact for DC OK
- Selectable Parallel Operation
- 85 to 264 VAC Operation, 130 to 350VDC
- 3 Year Warranty





DSR240:

1.77 x 4.88 x 4.69" (45.0 x 124.0 x 119.0 mm)

Models & Ratings

Output Voltage	Output Power	Output Voltage Trim ⁽³⁾	Output Current	Peak Current ⁽²⁾	Typical Efficiency ⁽¹⁾	Model Number
24 V	240 W	24.0-28.0 V	10.0 A	15.0 A	94%	DSR240PS24
48 V	240 W	48.0-56.0 V	5.0 A	7.5 A	93%	DSR240PS48


Notes

1. Typical efficiency at 230 VAC and full load.

2. Peak current is for a maximum of 3 s, see Application Notes. Average power is not to exceed nominal output power.

3. Output current should be limited so that nominal output power is not exceeded.

Mechanical Details



	Pin Connector					
Conn	Pin	Designation				
AC	1	Ground				
I/P	2	N				
	3	L				
	1	DC OK				
	2	DC OK				
DC	3	+Vout				
O/P	4	+Vout				
	5	-Vout				
	6	-Vout				

Notes

1. All dimensions in inches (mm)

2. Weight: 1.68 lbs (760g)

3. Tolerance: ±0.02 in (±0.5 mm)



Input

Minimum	Typical	Maximum	Units	Notes & Conditions
85		264	VAC	Alternatively 130 to 350VDC ⁽¹⁾
47	50/60	63	Hz	
	0.95			At 230 VAC. Conforms to EN61000-3-2 Class A
	2.3/1.13		A	115/230 VAC
		20/40	A	At 115/230 VAC. Cold start, 25 °C
		1.0	mA	At 264 VAC, 60 Hz
T5.0 A / 250 V internal in-line fuse				
	85 47	85 9,000 47 50/60 0.95 2.3/1.13	85 264 47 50/60 63 0.95 2.3/1.13 20/40 1.0 1.0 1.0	85 264 VAC 47 50/60 63 Hz 0.95

Note

1. DC input voltage was not assessed as part of the safety certification process.

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage - V1	24		48	VDC	See Models and Ratings table
Initial Set Accuracy			±1	%	At 100% load
Output Voltage Adjustment				%	See Models and Ratings table
Minimum Load	0			A	No minimum load required
Start Up Delay			2	S	
Hold Up Time	20			ms	At full load
Line Regulation			±0.5	%	
Load Regulation			±1	%	
Transient Response - V1			5	%	Recovery within 1% in less than 200 μs for a 50% step load change at 0.2 A/μs
			240/480		24 V/48 V models. Measured at 20 MHz bandwidth 0-70°C
Ripple & Noise			480/480	- mV pk-pk	24 V/48 V models. Measured at 20 MHz bandwidth -25-0°C
	29		33	V	24 V model
Overvoltage Protection	58		65	V	48 V model
Overload Protection	110		150	%	Trip & restart. See application note.
Short Circuit Protection					Trip & restart (hiccup mode), auto recovery
Thermal Protection		105 ±10		°C	Measured internally auto recovery
Temperature Coefficient			0.03	%/°C	

General						
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Efficiency		93		%	See Models & Ratings table	
Isolation: Input to Output	3000			VAC		
Input to Ground	2500			VAC		
Output to Ground	500			VAC		
Switching Frequency		65		kHz	PFC, fixed	
Switching Frequency	60		300	kHz	Main converter, variable	
DC OK Signal	Volt free contacts rated at 60 VDC/0.3 A, 30 VDC/1.0 A or 30 VAC/0.3 A (resistive load)					
Output LED	Green LED to inc	dicate output on.				
Mean Time Between Failure	300			kHrs	MIL-HDBK-217F, +25 °C GB	
Weight		1.68 (760)		lb (g)		



Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-25		+70	°C	See derating curve in Application Notes
Storage Temperature	-40		+85	°C	
Cooling					Natural convection
Operating Humidity	20		95	%RH	Non-condensing
Operating Altitude			5000	m	
Shock		4		g	IEC68-2-27, 22 ms half sine, 3 times in each of 6 axes
Vibration		2		g	IEC68-2-6, 10-500 Hz, 10 mins/sweep. 60 mins for each of 3 axes

EMC: Emissions

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Conducted	EN55032	Class B		
Radiated	EN55032	Class B		
Harmonic Current	EN61000-3-2	Class A		
Voltage Fluctuations	EN61000-3-3			


EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
ESD Immunity	EN61000-4-2	6 kV	Cont	Contact
ESD Immunity	EN01000-4-2	8 kV	A	Air Discharge
Radiated Immunity	EN61000-4-3	10 V/m	A	
EFT/Burst	EN61000-4-4	3	A	
Surges	EN61000-4-5	Installation class 3	A	
Conducted	EN61000-4-6	10 V	A	
Magnetic Fields	EN61000-4-8	4	A	
		Dip: 30%, 10 ms	A	
Dips and Interruptions	EN55035	Dip: 60%, 100 ms	A/B	High Line/Low Line
		Dip: 100%, 5000 ms	В	

Safety Approvals

Safety Agency	Safety Standard	Notes & Conditions
UL	UL508/UL60950	Industrial Control Equipment/Information Technology
TUV	EN62368-1	Information Technology
CE	Meets all applicable directives	
UKCA	Meets all applicable legislation	





Notes


1. All dimensions in inches (mm)

2. Weight: 1.68 lbs (760g)

3. Tolerance: ±0.02 in (±0.5 mm)

Application Notes

Derating Curves




AC-DC Power Supplies



Application Notes

Derating Curves


DSR240PS48



AC-DC Power Supplies

XP Power

DC OK




Open = Output fail, if voltage drops below 80% of nominal Closed = Output good

Contact Rating: 0.3 A at 60 VDC, 1.0 A at 30 VDC, 0.5 A at 30 VAC. 500 VDC isolation to output.

Peak Load and Overload

A peak load can be used for a certain period after which the output goes into overload mode. Overload operation is trip and restart. The peak load duration depends on the value of the load, e.g. a peak load of 150% can be taken for approximately 3s. After this time the output will turn off for approximately 7s before turning back on.

If the load has reduced to 100% or less than normal operation is resumed. If the load remains at 150% then the output is maintained for a further 3s before turning off for 7s. See example plot below.



If the peak load is less than 150%, the duration of the peak can be longer than 3s before the output turns off, for example, a peak load of 130% could typically be taken for up to 13s and a peak load of 140% could typically be taken for up to 5s. The off duration is always approximately 7s.

Average power is not to exceed nominal output power.