

AC-HVDC POWER SUPPLIES

750W RACK MOUNT

Designed for electrical design engineers and system integration engineers in a wide range of industries including ion implant, e-beam welding and e-beam additive manufacturing and many other application specific markets, the FT series addresses challenges engineers face with limited high voltage integration experience and tight time lines.

The FT series offers a wide range of standard outputs up to 60kV at 750W in a light form factor with various output control options, input voltages, and low output discharge currents allowing for extremely simple integration into a new system or tool.

Showcasing high quality, high performance, high reliability and high stability with air insulation, the FT series facilitates a low cost of ownership with the excellence and technical support of XP Power engineering.

As with all our products the FT Series is designed with maximum flexibility in mind so can easily be adapted to your requirements in this voltage and power level, please do contact us for derivative requests.





Dimensions

1.72" x 19.0" x 23.86" (43.7 x 482.6 x 606.4mm) 1U 19" rack mount

Features

- 0 to 100% programmable voltage and current
- Air insulated
- Local, analog, RS232/USB digital control. Ethernet is optional
- Voltage and current monitor outputs
- Short circuit, arc and overload protection
- 90VAC to 264VAC PFC input
- Efficiency >85%
- Low ripple <0.025% RMS of rated voltage at full load
- UKCA and CE marked for EMC, low voltage (LVD) and ROHS directives
- 1 year warranty

Benefits

- Allows maximum flexibility and control
- Lighter than competing products and easier to maintain
- Ensures safe operation providing maximum protection to the PSU, the load and the user
- · High efficiency drives towards carbon neutral goals
- Low cost of ownership

Input

Characteristic	Minimum	Typical	Maximum	timum Units Notes & Conditions		
Input Voltage	90		264	VAC	47-63Hz	
Power Factor		0.95			At full load at nominal AC line	
Input Connector	IEC60320 C20 receptacle. AC power cord not included					

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Output Voltage Range	0		60	kV	See Models and Ratings	
Output Current Range	13		750	mA	See Models and Ratings	
Polarity	Available with	n either positive	e, negative or rev	ersible polarit	y with respect to chassis ground	
Output Control	0 to rated vol	Itage or curren	t via rotary dials,	analog, RS23	2, USB or optional ethernet	
Static Voltage Regulation	±0.005			%	For specified line variations	
Static voltage negulation	±0.005			%	+0.5mV/mA for no load to full load variations	
Dynamic Voltage Regulation	Typical deviation <2%. Load transients from 10% to 99% and 99% to 10 Recovery to <1% in 500μs and recovery to <0.1% in 1ms					
Stability		0.01		04 /br	After 30 min. warm up	
Stability		0.05		70/TH	Over 8 hours under constant conditions after 30 min. warm up	
Temperature Coefficient		0.01		%/°C		
Voltage Rise/Decay		50		ms	Rise time constant	
Time Constant		50		ms	Decay time constant, 15% resistive load required	
Voltage Ripple	0.025 % +0.5V RMS at full load					
Arc Quench	Inhibits HV output for 20ms after an arc (optional 1kV to 6kV models, standard on 8kV to 60kV models)					
Arc Count	Consecutive	arcs > 1 arc/se	ec for 5 arcs will	result in outpu	t being disabled for 5 seconds	
HV Output Connection	Mating HV connector and 10ft (3m) shielded coaxial cable supplied					

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions					
Efficiency		85		%	At full load					
HV Insulating Medium	Outputs are a	Outputs are air insulated								
External Interlock	Open = off, closed = on. Normally latching except for blank front panel version where it is non-latching									
Remote HV Enable/Disable	0-1.5V = Off, 2.5-15V = On									
Voltage Accuracy	0.5% of setting + 0.2% of rated									
Voltage Monitor	0 to +10V equivalent to 0 to rated voltage. Accuracy: 0.5% of reading +0.2% of rated. Impedance is $10K\Omega$									
Current Monitor	0 to +10V eq	uivalent to 0 to	rated current. A	accuracy: 1% o	f reading + 0.1% of rated. Impedance is $10K\Omega$					
Resolution0.025% of full scale for both the voltage and the 0.1% of full scale for both the voltage and the cr					n the voltage and the current programs ne voltage and the current monitors					
RS232/USB/Ethernet Programming	Remote setti	ng accuracy	Voltage setti	ng accuracy is	better than 0.5% of setting +0.2% rated					
	Remote read	ling accuracy	cy Voltage reading accuracy is 0.5% of reading + 0.2% of rated Current reading accuracy is 1% of reading + 0.1% of rated							

Notes:

1. Specifications apply from 5% to 100% rated voltage. Operation is guaranteed down to zero voltage with a slight degradation of performance.

Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions		
Ambient Temperature	-20		+40	°C	Operating		
Ambient Temperature	-40		+85	°C	Storage		
Cooling	Forced air co	Forced air cooling with fan assist					
Protection	Overload, short circuit, arc, over temperature and surge protection						
RoHS	Restriction of the use of Hazardous Substances						

EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted Emissions	EN61000-6-4	Class A	CISPER 11
Radiated Emissions	EN61000-6-4	Class A	CISPER 11
Line Harmonics	EN61000-3-2	Class A	

EMC: Immunity

Phenomenon	Standard	Performance Criteria	Notes & Conditions
ESD Immunity	EN61000-4-2	В	
Radiated Immunity	EN61000-4-3	А	
EFT/Burst	EN61000-4-4	В	
Surge	EN61000-4-5	В	
Conducted	EN61000-4-6	А	
Voltage Dips & Interruptions	EN61000-4-11	B & C	

Safety Approvals

Safety Agency	Standard	Test Level	Notes & Conditions					
EN	EN61010/IEC61010	-	Safety					
CE	Meets all applicable directive	Meets all applicable directives						
UKCA	Meets all applicable legislation							

Notes:

1. Specifications apply from 5% to 100% rated voltage. Operation is guaranteed down to zero voltage with a slight degradation of performance.



Models & Ratings

Model Number	Polarity	Output Voltage	Output Current	Max Stored Energy	Output Cable
FT001P750	Positive	0 to +1kV			RG-58U
FT001N750	Negative	0 to -1kV	0 - 750mA	0.70J	RG-58U
FT001R750	Reversible	0 to 1kV			RG-58U
FT1.5P500	Positive	0 to +1.5kV			RG-58U
FT1.5N500	Negative	0 to -1.5kV	0 - 500mA	0.80J	RG-58U
FT1.5R500	Reversible	0 to 1.5kV			RG-58U
FT002P375	Positive	0 to +2kV			RG-58U
FT002N375	Negative	0 to -2kV	0 - 375mA	0.60J	RG-58U
FT002R375	Reversible	0 to 2kV			RG-58U
FT003P250	Positive	0 to +3kV			RG-58U
FT003N250	Negative	0 to 3kV	0 - 250mA	1.20J	RG-58U
FT003R250	Reversible	0 to -3kV			RG-58U
FT005P150	Positive	0 to +5kV			RG-8U
FT005N150	Negative	0 to -5kV	0 - 150mA	1.30J	RG-8U
FT005R150	Reversible	0 to 5kV			RG-8U
FT006P125	Positive	0 to +6kV			RG-8U
FT006N125	Negative	0 to -6kV	0 - 125mA	1.90J	RG-8U
FT006R125	Reversible	0 to 6kV			RG-8U
FT008P094	Positive	0 to +8kV			RG-8U
FT008N094	Negative	0 to -8kV	0 - 94mA	0.32J	RG-8U
FT008R094	Reversible	0 to 8kV			RG-8U
FT010P075	Positive	0 to +10kV			RG-8U
FT010N075	Negative	0 to -10kV	0 - 75mA	0.50J	RG-8U
FT010R075	Reversible	0 to 10kV			RG-8U
FT012P063	Positive	0 to +12kV			RG-8U
FT012N063	Negative	0 to -12kV	0 - 63mA	0.72J	RG-8U
FT012R063	Reversible	0 to 12kV			RG-8U
FT015P050	Positive	0 to +15kV			RG-8U
FT015N050	Negative	0 to -15kV	0 - 50mA	0.56J	RG-8U
FT015R050	Reversible	0 to 15kV			RG-8U
FT020P038	Positive	0 to +20kV			RG-8U
FT020N038	Negative	0 to -20kV	0 - 38mA	1.00J	RG-8U
FT020R038	Reversible	0 to 20kV			RG-8U
FT025P030	Positive	0 to +25kV			RG-8U
FT025N030	Negative	0 to -25kV	0 - 30mA	0.83J	RG-8U
FT025R030	Reversible	0 to 25kV			RG-8U
FT030P025	Positive	0 to +30kV			RG-8U
FT030N025	Negative	0 to -30kV	0 - 25mA	1.20J	RG-8U
FT030R025	Reversible	0 to 30kV			RG-8U
FT040P019	Positive	0 to +40kV			RG-8U
FT040N019	Negative	0 to -40kV	0 - 19mA	1.60J	RG-8U
FT040R019	Reversible	0 to 40kV			RG-8U
FT050P015	Positive	0 to +50kV			RG-8U
FT050N015	Negative	0 to -50kV	0 - 15mA	2.00J	RG-8U
FT050R015	Reversible	0 to 50kV			RG-8U
FT060P013	Positive	0 to +60kV			RG-8U
FT060N013	Negative	0 to -60kV	0 - 13mA	2.40J	RG-8U
FT060R013	Reversible 0 to 60kV				RG-8U

Notes:

1. For reversible polarity units two high voltage assemblies will be supplied. Cover must be removed to change polarities.

2. Add suffix "A" for arc count (1-6kV only) e.g. FT001P750A.

3. Add suffix "B" for blank front panel (power switch only) e.g. FT001P750B.

4. Add suffix "E" for ethernet control e.g. $\ensuremath{\mathsf{FT001P750E}}$.

5. Please consult sales for special requirements.

Mechanical Details

Front View



Key	Function	Key	Function
1	Power On Indicator	10	Fault
2	Power On Switch	11	Preset and Indicator
3	Current Display	12	Voltage Display
4	Current Mode	13	Voltage Mode
5	HV On and Indicator	14	Control Lock and Indicator
6	Current Adjust	15	Voltage (Slope) Adjust
7	Standby	16	SS Slope
8	Remote/Local and Indicators	17	Fine Adjust and Indicator
9	Polarity		

Notes:

1. All dimensions are in inches (mm).

Signals & Controls

	Function	Function				
Front Panel Control	HV On/Off	f, rotary dials for voltage and current adjust, fine adjustment 0.025%, 0.25% coarse adjustment				
Front Panel Indicators	3.5 digit d remote en	3.5 digit digital meters, AC power, current mode, voltage mode, pol+, pol-, fault, fine adjustment, preset, control lock, remote enable, remote program, HV On				
Rear Panel Control	AC power connector	AC power entry connector, fuses, power on indicator, ground stud, HV output connector, remote interface connector, RS232/USB connectors				
	Inputs	Safety interlock, output voltage and current program signals, high voltage enable and remote HV On				
Interface Signals	Outputs	Output voltage and current monitor signals, HV status, fault status, I/V mode status, arc status and a +10V reference source				
External Interlock	Open = O	Open = Off, closed = On. Normally latching except for blank front panel version where it is non-latching				
Remote HV Enable/Disable	0 - 1.5V =	Off, 2.5 - 15V = On				

Mechanical Details

Rear View



R	S232 Interface - J1	USB Interface - J2			Analog Interface - J3				
Pin	Function	Pin	Function	Pin	Function	Pin	Function	Pin	Function
1	DCD	1	+5V	1	Ground	10	Current Monitor	19	Reserved
2	RX	2	D-	2	Common	11	Common	20	HV Enable
3	ТХ	3	D+	3	Safety Interlock	12	Reference	21	HV Status
4	DTR	4	Common	4	Reserved	13	Reserved	22	Fault Status
5	Common			5	Reserved	14	Reserved	23	Mode Status
6	DSR			6	Voltage Program	15	Remote HV On	24	Arc Status
7	RTS			7	Current Program	16	Remote HV On	25	Ground
8	CTS			8	Common	17	CL/CT		
9	N/C			9	Voltage Monitor	18	CL/CT		

U1 Option								
Pin	Function	Pin	Function					
1	TXD+	5	E Power+					
2	TXD-	6	RXD-					
3	RXD+	7	E Power-					
4	E Power+	8	E Power-					

AC Input - J4		
Pin	Function	
1	Line	
2	Neutral	
3	Ground	

HV	Output	- JHV1
	Output	21147

1kV to 3kV KINGS SHV 1704-1 or equivalent
5kV to 60kV AMPHENOL 83-1R-RFX or equivalent



Mechanical Details

Top & Side View



Notes:

1. All dimensions are in inches (mm) 2. Weight: 14lbs (6.5kg)

6